ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50RB E50 Surface Mount Receptacle

Eaton Corp

Catalog Number	E50RB
Manufacturer	Eaton Corp
Description	Limit Switch Receptacle, E50 Heavy Duty Plug In Series, Die Cast Zinc Material, -40 °F Operating Temperature, +250 °F Operating Temperature, 2.92 In (L) X 1.54 In (W) X 1.06 In (H), Surface Mount, 0.1100 LB/Ea
Weight per unit	0.1100 (lbs/each)
Product Category	Limit Switch Accessories

Features

connection	Screw Terminal

Descriptions

Description	E50 SURFACE MOUNT RECEPTACLE
extra long description	ETN E50RB E50 SURFACE MOUNT RECEPTA

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113290737
UPC	782113290737

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Water and Wastewater Systems - Water and Wastewater Systems - OtherStationary Mach Equip In Factory - Machine Tools: CuttingStationary Mach Equip In Factory - Machine Tools: Forming
Mounting	SURFACE
Operating Temperature	-40
standard	UL Recognized,CSA Certified,RoHS Compliant