Powering Business Worldwide

pe.eaton.com



Premium+ Inductive Proximity Sensor

E57-18LE20-AA

UPC:782113933436

Dimensions:

- **Height:** .71 IN
- **Length:** 2.74 IN
- **Width:** .71 IN

Warranties:

- 1 year

Specifications:

- **Type:** Premium+ Inductive Proximity Sensor
- **Accuracy:** <3% sensing range
- **Connection:** Dual key micro
- **Contact Rating:** 250 mA at 250V
- **Contact Configuration:** 2-wire AC, NO
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 20-132V
- **Led Indicators:** 360° viewable LED
- **Maximum Ac Current:** 250 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Non-embeddable
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Series:** E57

Supporting documents:

- Eatons Volume 8-Sensing Solutions
- Eaton Specification Sheet - E57-18LE20-AA

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.