



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F64T12CWHO 80W T12 64" Cool White High Output 62 Cri R17D

*Sylvania-Ledvance*

|                  |   |
|------------------|---|
| Catalog Number   | F64T12CWHO  |
| Manufacturer     | Sylvania-Ledvance   |
| Description      | OBS25352 80W, 64" Mol, T12 Ho (800 Ma) Rapid Start<br>Fluorescent Lamp, Cool White Phosphor, 4200K Color<br>Temperature, 60 Cri |
| Weight per unit  | 0.9200 (lbs/each)   |
| Product Category | Lighting  |

### Features

|                           |                                     |
|---------------------------|-------------------------------------|
| amperage rating           | Ballast Dependent                   |
| average life              | 12000                               |
| Base                      | Recessed Double Contact             |
| lumens                    | 5750 Initial Lumens at 25 Degrees C |
| Shape                     | T12                                 |
| start type                | Rapid Start                         |
| total harmonic distortion | Ballast Dependent                   |
| Voltage Rating            | Ballast Dependent                   |
| Wattage                   | 80                                  |

### Material, Color, and Finish

|                             |                 |
|-----------------------------|-----------------|
| color rendering index (cri) | 60              |
| color temperature           | 4200            |
| Finish                      | Phosphor Coated |

### Dimensions and Weight

|          |        |
|----------|--------|
| Diameter | 1.5 in |
|----------|--------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 80W T12 64" COOL WHITE HIGH OUTPUT 62 CRI R17D  |
| extra long description | SYL F64T12/CW/HO/25352 F64T12CWHO 3   |
| Long Description       | OBS25352 80W, 64" MOL, T12 HO (800 mA) rapid start<br>fluorescent lamp, Cool White phosphor, 4200K color<br>temperature, 60 CRI |
| Product Type           | F64T12CWHO 30/CS 1/Sku  |
| Special Features       | COOL WHITE  |

### Manufacturer Information

|                           |                    |
|---------------------------|--------------------|
| Brand                     | SYLVANIA           |
| GTIN                      | 00046135253522     |
| Manufacturers Part Number | F64T12/CW/HO/25352 |
| UPC                       | 046135253522       |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 30

Weight Per each ..... 0.92

## Uses, Certifications, and Standards

Application ..... Commercial/Residential