



Pass and Seymour
Flexcor® Turnlok® EHU Strain Relief Grips, Cable Diameter 0.52 - 0.73 in.
Part No. FC52GL

FC52GL: Extra-Hard Use, Closed Mesh, Cable Diameter 0.52 - 0.73 inches,
Mesh Length 6.5-in



Features & Benefits

EHU wire mesh grips provide additional strain-relief for wiring device plugs and connectors used on portable equipment in commercial and institutional applications, and industrial plant and construction site areas, which incur abnormally high abuse. Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information. Mesh Length: 9.00

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007998795
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Support Grip		

Dimensions

Product Width US	0.73 in	Product Depth US	6.5 in
Product Height US	0.73 in	Mesh Length	6.5 in
Cable Diameter Range	0.520-0.730 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range	0.52 in	Minimum Cable Range	0.73 in
---------------------	---------	---------------------	---------

Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
Mounting	Consult the Factory for Mounting Recommendations		