Product specifications

Eaton GUA067



Catalog Number: GUA067

Eaton Crouse-Hinds series Condulet GUA dome cover, 3" cover opening diameter, 2" exterior depth, Copper-free aluminum, 12 thread pitch

General specifications

Product Name	**Catalog Number**
Eaton Crouse-Hinds series Condulet GUA dome cover	GUA067
	UPC
	782274458908
Product Length/Depth	**Product Height**
3.75 in	3.5 in
Product Width	**Product Weight**
3.5 in	0.83 lb

Powering Business Worldwide

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Product specifications

Cover opening diameter

3"

Exterior depth

2"

Thread pitch

12

Material

Copper-free aluminum

Resources

Catalogs

Crouse-Hinds series GUA Conduit Outlet Boxes catalog page

Certification reports

Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification

Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification (Cover)

Condulet GUA and GUR Explosionproof Conduit Outlet Boxes Canadian certification (Cover)

Installation instructions

IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes

Specifications and datasheets

Eaton Specification Sheet - GUA067

Technical service bulletins

Industrial Fittings Bend Radius and Cubic Capacity Chart

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.