




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED13T860P1S840D 5' 13W Led Signhero 40K 180DEG Ballast Bypass *Keystone Technologies*

Catalog Number	LED13T860P1S840D
Manufacturer	Keystone Technologies
Description	Key KT-LED13T8-60P1S-840-D /G2 60in
Weight per unit	1.3 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	180
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
Lamp Type	T8
lumens	1625
Nominal Length	60 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	13
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	5' 13W LED SIGNHERO 40K 180DEG BALLAST BYPASS
Long Description	Key KT-LED13T8-60P1S-840-D /G2 60In
Product Type	60IN Led Sign Tube, 4000K, Single Sided Output and Rotatable

Manufacturer Information

Brand	Keystone
GTIN	00843654132716
Manufacturers Part Number	KT-LED13T8-60P1S-840-D /G2
UPC	843654132716

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
----------------------	-------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
--------	---

Package	9
---------	---

Weight Per each	1.28
-----------------	------

Uses, Certifications, and Standards

Energy Star	N
-------------	---