Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED17T8L48FGIS85 17W Led T8 48" 50K Glass

Sylvania-Ledvance

Catalog Number	LED17T8L48FGIS85
Manufacturer	Sylvania-Ledvance
Description	OBS40099 4FT Substitube Led T8 Value Instant Start Only, Frosted Glass, 17W, 82CRI, 2200 Lumen, 5000K, 36000 Life
Weight per unit	0.6090 (lbs/each)
Product Category	Lighting

Features

average life	36000
Base	G13
dimmable	No
Lamp Type	LED T8 VALUE INSTANT START ONL
Shape	T8
Wattage	17.00

Material, Color, and Finish

color rendering index (cri)	82
color temperature	5000
Style	Tube, double-ended

Dimensions and Weight

Size	1.02

Descriptions

Description	17W LED T8 48" 50K GLASS
extra long description	SYL LED17T8L48FGIS850SUBG8/40099 LE
Long Description	OBS40099 4ft SubstiTUBE LED T8 VALUE Instant Start Only, frosted glass, 17W, 82CRI, 2200 Lumen, 5000K, 36000 life
Product Type	LED17T8L48FGIS850SUBG8 10/CS 1/Sku

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135400995
Manufacturers Part Number	LED17T8L48FGIS850SUBG8/40099
sub brand	SubstiTUBE
UPC	046135400995

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS

Packaging

Carton	1
Package	10
Weight Per each	0.609

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard	FCC