

Product Number: 79748

Order Abbreviation: LED25T5HO/L48/FG/841/SUB/G6

General Description: 4ft SubstiTUBE LED T5HO, frosted glass, 25W, 82CRI, 3500 Lumen, 4100K, 50000 life

Product Information

Life Time (L70)	50000
Operating Temperature (°C)	-20 to 50
Abbrev. With Packaging Info.	LED25T5HOL48FG841SUBG6 10/CS 10/SKU
Average Rated Life (hr)	50000
Bulb	T5
Family Brand Name	SubstiTUBE
Color Temperature/CCT (K)	4100
Color Rendering Index (CRI)	82
Lumens	3500
Approx. Lumens	3500
Nominal Voltage (V)	120.00
Nominal Wattage (W)	25.00
Language Strategy	ENGLISH/FRENCH/SPANISH
Ordering Abbreviation	LED25T5HO/L48/FG/841/SUB/G6
UPC Code	UPC046135797484
Lamp Finish	Frosted



Product Number: 79748

Order Abbreviation: LED25T5HO/L48/FG/841/SUB/G6

General Description: 4ft SubstiTUBE LED T5HO, frosted glass, 25W, 82CRI, 3500 Lumen, 4100K, 50000 life

Product Information

Life Time (L70)	50000
Operating Temperature (°C)	-20 to 50
Abbrev. With Packaging Info.	LED25T5HOL48FG841SUBG6 10/CS 10/SKU
Average Rated Life (hr)	50000
Bulb	T5
Family Brand Name	SubstiTUBE
Color Temperature/CCT (K)	4100
Color Rendering Index (CRI)	82
Lumens	3500
Approx. Lumens	3500
Nominal Voltage (V)	120.00
Nominal Wattage (W)	25.00
Language Strategy	ENGLISH/FRENCH/SPANISH
Ordering Abbreviation	LED25T5HO/L48/FG/841/SUB/G6
UPC Code	UPC046135797484
Lamp Finish	Frosted