

Incandescent


Universal Light Kit Alabaster Glass Shades

Ceiling Fans

Type -09 -20 -30 -33 P26

|--|

Catalog No.	Finish					
	Brushed	Antique		Cobble-	Dimensions (Inches)	
	Nickel	Bronze	White	stone	A B	
P2643	-09	-20	-30	-33	13-5/8" 7"	



Specifications:

General

- Four alabaster glass shades
 - 5-3/8" x 4-7/8" ht., 1-5/8" dia. center hole
- Pull chain on Brushed Nickel (-09) is chrome with a maple fob, White (-30) finish is chrome with a white fob, and on the rest are antique brass with a medium oak fob.
- Utilizes (4) 40-watt candelabra based lamps, included.
- Brushed Nickel (-09) is plated finish
- Steel construction

Mounting

• Universal -use with any indoor fan with 1/8" IPS light kit adapter

Electrical

- Four ceramic candelabra based sockets
- Quick connect wiring to fan
- Prewired
- 190-watt limiter

Labeling

• UL listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607