


Type _____
-104

- P7077
- P7078
- P7086

Catalog No.	Finish		Lamping	Dimensions (Inches)		
	Polished Nickel			A	B	C
P7077	-104		1 (m) 100w	11-3/8	12	78
P7078	-104		1 (m) 100w	16	16-3/4	82
P7086	-104		2 (m) 100w	27-3/4	28-7/16	94



Specifications:

General

- Etched Opal glass shade
- Plated Polished Nickel (-104) finish
- Steel construction
- One 6", four 12" lengths of stem included
- 6 links of 9 gauge chain supplied.
- Companion Hall and Foyer, Pendant, fixtures are available

Mounting

- Ceiling stem mounted with 6 links of chain mount
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included

Electrical

- Medium base ceramic socket
- 10 feet of wire supplied
- Pre-wired

Labeling

- UL-CUL Dry location listed