



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

500 Rapides Drive
71457-0000, LA Natchitoches
Phone: 318-352-7414
Fax: 318-352-4100



PN148FM 16-14AWG #8STD Insld Fork TRML *Panduit Corporation*

Catalog Number	PN148FM
Manufacturer	Panduit Corporation
Description	Fork Terminal, Nylon Insulated, 16- 14 Awg, #8 Stud Size, Bulk Package.
Weight per unit	0.0024 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#8
------	----

Descriptions

Description	16-14AWG #8STD INSLTD FORK TRML
extra long description	PAN PN14-8F-M Pan-Term® PN14-8F-M L
Long Description	Fork Terminal, nylon insulated, 16- 14 AWG, #8 stud size, bulk package.
Product Type	Pan-Term® PN14-8F-M Loose Piece Forks

Manufacturer Information

Brand	Panduit®
GTIN	00074983803118
Manufacturers Part Number	PN14-8F-M
UPC	074983803118

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Fork Terminal

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Weight Per each	0.0024



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

500 Rapides Drive
71457-0000, LA Natchitoches
Phone: 318-352-7414
Fax: 318-352-4100

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	7/32
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)