

GE Lighting

20832 - Q50MR16/C/WFL55

GE ConstantColor® Precise™ MR16







GENERAL CHARACTERISTICS

Lamp Type	Halogen - MR
Bulb	MR16
Base	2-Pin (GX5.3)
Filament	C-6
Rated Life	6000.0 hrs
Lamp Enclosure Type (LET)	Open or enclosed fixtures

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	825.0
Center Beam Candlepower (CBCP)	900.0
Color Temperature	3050.0 K
Beam Spread	5.0 °

ELECTRICAL CHARACTERISTICS

Wattage	50.0
Voltage	12.0

DIMENSIONS

Maximum Overall Length (MOL)	1.8750 in(47.6 mm)
Bulb Diameter (DIA)	2.000 in(50.8 mm)

PRODUCT INFORMATION

Product Code	20832
Description	Q50MR16/C/WFL55
ANSI Code	FNV
Standard Package	BUNDLE
Standard Package GTIN	00043168208321
Standard Package Quantity	20
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
UPC	043168991216

CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
  - Dispose of lamp in a closed container.
  - Do not use lamp if outer glass is scratched or broken.

Warning


- Risk of Burn
  - Allow lamp/fixture to cool before handling.
  - Turn power off before installing lamp.
- Risk of Fire
  - Keep combustible materials away from lamp.
  - Use in enclosed fixture rated for this product-- see instructions.
- Pressurized lamp--unexpected rupture may cause injury, fire, or property damage
  - Do not touch glass with bare hands.
  - Do not use lamp if outer glass is scratched or broken.
  - Use eye protection when handling lamp.
  - Use in enclosed fixture rated for this product.


GE Lighting

20832 - Q50MR16/C/WFL55

GE ConstantColor® Precise™ MR16







GENERAL CHARACTERISTICS

Lamp Type	Halogen - MR
Bulb	MR16
Base	2-Pin (GX5.3)
Filament	C-6
Rated Life	6000.0 hrs
Lamp Enclosure Type (LET)	Open or enclosed fixtures

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	825.0
Center Beam Candlepower (CBCP)	900.0
Color Temperature	3050.0 K
Beam Spread	5.0 °

ELECTRICAL CHARACTERISTICS

Wattage	50.0
Voltage	12.0

DIMENSIONS

Maximum Overall Length (MOL)	1.8750 in(47.6 mm)
Bulb Diameter (DIA)	2.000 in(50.8 mm)

PRODUCT INFORMATION

Product Code	20832
Description	Q50MR16/C/WFL55
ANSI Code	FNV
Standard Package	BUNDLE
Standard Package GTIN	00043168208321
Standard Package Quantity	20
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
UPC	043168991216

CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
  - Dispose of lamp in a closed container.
  - Do not use lamp if outer glass is scratched or broken.

Warning

- Risk of Burn
  - Allow lamp/fixture to cool before handling.
  - Turn power off before installing lamp.
- Risk of Fire
  - Keep combustible materials away from lamp.
  - Use in enclosed fixture rated for this product-- see instructions.
- Pressurized lamp--unexpected rupture may cause injury, fire, or property damage
  - Do not touch glass with bare hands.
  - Do not use lamp if outer glass is scratched or broken.
  - Use eye protection when handling lamp.
  - Use in enclosed fixture rated for this product.