SATCO' NUVO

Project Name

Location

Prepared By



SATCO S29919

40T8/LED/96-850/BP/FA8

Notes

General Status Active Watts 40W 59W Fluorescent Equivalent Volts 120V-277V Ballast Type Туре В Shape Τ8 Single Pin Base ANSI Base FA8 Nominal Length 96.00 Finish White CCT (Kelvin) 5000 Temperature Natural Light CRI 82 Lumens 5500L Beam Spread 210 Dimmable Non-Dimmable Hours Rated 50000 Lamp Type Linear Technology LED Electrical **Ballasting Requirements** Ballast Bypass Power Factor 0.9 THD 25% -20C (-4F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 94.00 MOD 1.00 Material Glass White Lens Finish Weight (lb.) 0.88 Additional Information Suitable for Emergency Lighting Additional Info only with Satco EM Driver #S8002 Shatter-Proof Type PET Coated Warranty 5 Year Limited - T8 LED Bulbs Compliance Safety Listing cULus Location Rating Damp No Energy Star **DLC Approved** Yes DLC ID PLZR8CUD8VL7 Lawful for sale in California California Status **RoHS** Compliant Yes FCC Compliant Yes **NSF** Approved Yes