Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S39391 22W Led Hid RPLCMNT 50K Med Base 3080LM

Satco

Catalog Number	S39391
Manufacturer	Satco
Description	Satco S39391 22W/Led/Hid/5000K/100-
Weight per unit	0.9646 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

average life	50000
Base	Medium
beam angle	300
dimmable	No
lumens	3.08k
Material	Plastic; Aluminum
Shape	Corncob
surge protection	Built-in surge protection - 2.5KV
Voltage Rating	277
Warranty	5 Year Limited - Hi-Pro
Wattage	22

Material, Color, and Finish

color temperature	5000

Dimensions and Weight

Diameter	2.38
Length	5.69

Descriptions

Description	22W LED HID RPLCMNT 50K MED BASE 3080LM
Long Description	SATCO S39391 22W/LED/HID/5000K/100-
Product Type	22W/Led/Hid/5000K/100-277V/E26
Special Features	Warranty: 5 Year Limited ; Country of origin: China ; IP65 rated: Yes ; CEC: Lawful for sale in California ; Operating Temp: -20C (-4F) to a maximum of +40C (+104F) ; Safety Listing: cULus - Listed ; Beam spread: 300 degrees ; Burning position: Universal ; Color temp: Natural Light ; Incandescent equivalent: 150W ; Fluorescent equivalent: 40W ; HID equivalent: 100W ; Voltage:100-277V

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923303913
Manufacturers Part Number	S39391
sub brand	Satco
UPC	045923303913

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	HID Replacements

Availability

Manufacturer Status	Inactive

Packaging

Carton	1
Weight	0.68
Weight Per each	0.9646

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)