S3952

60A19/F/VS
60 watt A19 Incandescent; Frost; 2500 average rated hours; 580 lumens; Medium base; 130 volts; 2/Pack

Features
- General Service Incandescent
- Household or Commercial use
- Vibration Service
- Long Life
- 130 volt



S3952

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3952	045923039522	60	A19	Medium	E26	60A19/F/VS	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost	4 1/8"	2.38"	C-9	580	2500	120	2pk

RoHS Compliant
Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas, Washington, California, Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051

S3952

60A19/F/VS
60 watt A19 Incandescent; Frost; 2500 average rated hours; 580 lumens; Medium base; 130 volts; 2/Pack

Features
- General Service Incandescent
- Household or Commercial use
- Vibration Service
- Long Life
- 130 volt



S3952

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3952	045923039522	60	A19	Medium	E26	60A19/F/VS	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost	4 1/8"	2.38"	C-9	580	2500	120	2pk

RoHS Compliant
Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas, Washington, California, Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051