

Stainless Steel X Condulet

Features:

- The four-hub "X" configuration limits the amount of additional fittings needed on a project as wires can be fed through and then out in several directions to simplify installation.
- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Solid stainless construction permits easy installation using ordinary hand tools
- · The flat back design allows extra wiring capacity
- No package qty. required
- · Cover & Gasket set included
- Form 8 Style

Certifications and Compliances:

Manufactured to comply with UL514A Standards

Material:

Material: Body CF8M- 316SS

Gasket - Neoprene Cover & Screws: 316SS


Applications:

To connect and change direction of conduit runs
Can be used as pulling fittings
Accessible wiring chamber provides a spacious location to make splices

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical Operations
- Marine & Coastal Facilities
- Pulp and Paper Mills
- Along with other corrosive environments





Size	Part Number	A	В	С	а	Cubic Inches	Weight (ea) per lb.
1/2"	S60500XB00	5.640"	2.630"	2.050"	4.320"	5"	1.36
3/,"	S60700XB00	6.200"	3.070"	2.300"	4.940"	9"	1.86
1"	S61000XB00	7.300"	3.540"	2.330"	5.650"	13"	2.77
1-1/2"	S61500XB00	9.810"	4.500"	3.060"	7.810"	35"	5.24
2"	S62000XB00	12.250"	5.810"	3.700"	10.000"	77"	9.63

All dimensions are for informational purposes only *Tolerances +/- 5%