



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S811+V36N3S Soft Starter 290MM 360A W/ Opt Inside The Delta

Eaton Corp

Catalog Number	S811+V36N3S
Manufacturer	Eaton Corp
Description	Eaton S811+ Soft Starter, Non-Combination Soft Starter, Frame Size 290 MM, 360 A, 600 V, Three-Pole
Weight per unit	108.0 (lbs/each)
Product Category	Soft Start Controllers & Start

### Features

media	Yes
Poles	3
Voltage Rating	600 V

### Dimensions and Weight

Depth	16.57
Height	7.35
Width	11.05

### Descriptions

Description	SOFT STARTER 290MM 360A W/ OPT INSIDE THE DELTA
extra long description	ETN S811+V36N3S RVSS 290MM 360A W/O
Features	Advanced intelligence. Compact footprint. The S811+/S801+ line of intelligent technologies soft starters is designed to be the smallest, most compact soft starter in the market today. With this small size, it can easily fit in place of existing soft starter designs, wye-delta starters or across-the-line NEMA and IEC starters. This feature allows easy retrofits of existing motor control centers or enclosures and saves the expense of replacing existing structures or adding a new one to house a soft starter.
Long Description	Eaton S811+ soft starter, Non-combination Soft Starter, Frame size 290 mm, 360 A, 600 V, Three-pole
Product Type	RVSS 290MM 360A W/Opt Inside The Delta

### Manufacturer Information

Brand	Eaton
GTIN	00786685559094
Manufacturers Part Number	S811+V36N3S
UPC	786685559094

### Taxonomies, Classifications, and Categories

Category Description	DRIVES
----------------------	--------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	108

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	IEC 60947-4-2, EN 60947-4-2, UL Listed, CSA Certified, CE Marked