



S9841

9.5A19/OMNI/220/LED/35K/GU24
9.5 watt; A19 LED; 3500K; GU24 base; 220' beam spread; 120 volts

Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable



S9841

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9841	045923098413	120	9	60W	0.88	A19	GU24
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
9.5A19/OMNI/220/LED/35K/GU24	Dimmable	Frosted	4 3/16"	2 3/8"	845	25000	3500
Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	Fixture Type	UL or ETL Listed
Neutral White	80	220	24	Box	Yes	Enclosed Rated	Yes
UL Classification						Warranty	
cULus - Damp Location Rated						3 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

