



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

SBL4LP840 4' Led Wrap 40K 4000LM

Lithonia Lighting - Acuity

Catalog Number	SBL4LP840
Manufacturer	Lithonia Lighting - Acuity
Description	Led - Static, 32 W, 3194.1 LM Brightness (Lumens), 4 FT Length, +25 °C Operating Temperature, 5 Yr Warranty, 15.0 LB/Ea
Weight per unit	8.8 (lbs/each)
Product Category	Lighting

Features

dimensions	48 x 8.625 x 2.625
Fixture Type	Wraparound
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	4000
Material	Steel
pallet quantity	75
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Wattage	32 W

Material, Color, and Finish

Color	White
Finish	Gloss
Lens Color	Clear
Style	Traditional

Dimensions and Weight

Height	2.625
Width	8.625

Descriptions

Description	4' LED WRAP 40K 4000LM
extra long description	LITH SBL4 LP840 4FT LED wrap, 80+ C
Long Description	LED - Static, 32 W, 3194.1 lm Brightness (Lumens), 4 FT Length, +25 °C Operating Temperature, 5 yr Warranty, 15.0 lb/EA

Manufacturer Information

GTIN	00190887819434
UPC	190887819434



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED ARCHITECTURAL & SPECIFICATION LIGHTING

Type Wraparound

Trade Size

aperture size 1x4

Packaging

Carton 1

Weight Per each 8.77

Uses, Certifications, and Standards

environmental conditions Indoor

Mounting Surface,Suspended

standard CSABAA and BABA,DLC Standard