



Trademaster Wall Plate Jumbo 2-gang 2-duplex

Features & Benefits

- Molded of rugged, practically indestructible self-extinguishing nylon. ['TP' series only.]
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Nominal thickness, .070 inch.
- Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007025521
Country Of Origin	Mexico	Material	Nylon
Construction	Plastic	Wall Plate Size	Trademaster Jumbo
Wall Plate Type	Duplex Receptacle	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

Dimensions

Product Width US	5.125 in	Product Depth US	0.25 in
Product Height US	5.0625 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.07 in	Number of Gangs	2
-----------	---------	-----------------	---

Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
----------------	--------	---------------	---------------

Orientation	Vertical
-------------	----------
