

FEATURES

- Trim, low-profile design, only 1-3/16" deep.
- Flattened knockouts for cleaner appearance.
- Snap-fit channel cover attachment. No tools required for wireway access.
- Hinged, removable channel cover allows hands-free wiring and quick installation.
- Factory-installed starters on all preheat models.
- Romex/BXR conduit connector provided with each fixture.
- · Optional instant-on electronic start magnetic ballast for flicker-free lamp start.
- · Low-brightness, linear prismatic diffuser provides improved visual comfort.
- 15% DR acrylic and snap-fit diffuser design for improved shatter-resistant and positive attachment.
- Optional task diffuser with clear linear prismatic bottom and opaque front for maximum illumination without direct edge glare.
- Five fixture lengths available.
- Available with factory-installed lamp, switch, cordset and convenience outlet options.
- Certain airborne contaminants can diminish integrity of acrylic. <u>Click</u> <u>here for Acrylic Environmental Compatibility table for suitable uses.</u>

SPECIFICATIONS

 ${\sf BALLAST}$ — Normal power factor reactor type ballast standard. Others available (See ordering information).

WIRING & ELECTRICAL — Fixture conforms to UL 1570 and is suitable for damp locations. AWM, TFN or THHN wire used throughout, rated for required temperatures.

MATERIALS — Metal parts precision roll-formed from 20 gauge cold rolled steel. FINISH — Five-stage iron-phosphate pre-treatment ensures superior paint adhesion and rust resistance. Painted parts finished with polyester powder paint.

 $\mbox{LISTING}$ — UL listed and labeled. Listed and labeled to comply with Canadian and Mexican Standards.

NOTE: Specifications subject to change without notice.

ORDERING INFORMATION

. . .

UC								
Series	Fixture length/ballast type			Diffuser		Voltage		Options
UC Undercabinet	12E			(blank)	Standard, milk-	120	GLR	Internal fast-blow fuse
light		electronic			white, DR acrylic		GMF	Internal slow-blow fuse
	21E	(1) 13W T5, instant start electronic	OP	Opaque-front, clear bottom DR		CSW	6-foot, 3-wire, grounded cordset, right end	
		(2) 8W T5, instant start electronic			acrylic		LPWW	Warm white 3000K T5 lamp(s); factory supplied
	33E	(1) 8W and 13W T5, instant start electronic				PAF	White powder paint finish after fabrication	
	42E	42E (2) 13W T5, instant start electronic					CO	Grounded convenience outlet. Installed, bottom right, 120V only
							SWR	Rocker switch, installed bottom right, 120V only
							CSA	Listed and labeled to comply with Canadian Standards
							NOM	Listed and labeled to comply with Mexican Standards

1" Wrap-Front Lens

Catalog Number


Notes

Fluorescent

Туре


Undercabinet Light

Example: UC 33E OP 120



MOUNTING DATA

For unit or row mount installation, surface mounting only.



DIMENSIONS

Inches (centimeters). Subject to change without notice.

PHOTOMETRICS

Photometry derived in accordance with IESNA LM41 procedure. Vertical and horizontal illuminance is calculated with fixture mounted 15" from work surface. Full photometric data available upon request.

Initial Point Illumination on horizontal work surface. (fc)

В


Coordinates are on 6" centers.

UC 24

Report	LTL	6349)			
	1	2	3	4	5	6
Α	7	9	9	7	5	3
B C	13	19	18	13	8	4
C	21	30	29	19	10	6
D	26	38	36	23	12	6 7
Ē F	26	38	36	23	12	7
F	21	30	29	19	10	6
G	13	18	18	13	8	4
H	7	9	9	7	5	4 3

UC 42

UC 42 Report LTL 6447									
	1	2	3	4	5	6			
Α	22	31	31	21	13	7			
B C D E F G H	32 37 40 40 37 32 22	46 54 58 58 54 46 31	44 52 56 52 44 31	30 35 37 37 35 30 21	17 19 21 21 19 17 13	9 11 12 12 11 9 7			





An Scuity Brands Company

Lithonia Lighting

Fluorescent One Lithonia Way, Conyers, GA 30012 Phone: 800-858-7763 www.lithonia.com