ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UC36T8125LP41 36" 1 Lamp 30W T8 120V Undercounter 4100K

Cooper Lighting Solutions

Catalog Number	UC36T8125LP41
Manufacturer	Cooper Lighting Solutions
Description	Under Cabinet Lamp, Computer Stations;Displays;Kitchens;Offices;Study Areas Application, Electronic Ballast Type, T8 Bulb Shape, 3000 K Color Temperature, Energy Star, White Fabrication Finish, 3-7/8 In Height, Cold Rolled Steel Housing Material, 25 W Lamp Wattage, 36-1/8 In Length, Keyhole Mount Mounting Type, 1 - Lamps, Keyhole Mounting Slots Are Located On Top Of Housing For Ease Of Installation;Rounded Corners and No Exposed Fasteners Special Features, Ul Listed, Electronic Instant Start Type, 120 V Vo
Weight per unit	4.0 (lbs/each)
Product Category	Fluorescent Track, Rail, Task

Features

amperage rating	0.20A at 277V
Lamp Type	Fluorescent
Wattage	28W

Material, Color, and Finish

Style	(blank)

Descriptions

Description	36" 1 LAMP 30W T8 120V UNDERCOUNTER 4100K
extra long description	CLS UC36T8125-LP41 6", 1 LMP T8, 25

Manufacturer Information

Brand	METALUX
GTIN	00080083708949
Manufacturers Part Number	UC36T8125-LP41
UPC	080083708949

Taxonomies, Classifications, and Categories

Category Description	Under Counter Fixtures
Type	Undercabinet

Packaging

Carton	1
Weight Per each	4

Uses, Certifications, and Standards

Mounting	Recessed
standard	UL Listed - Damp Location