Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding USB Charger Receptacles

Features

- High Power 5 Amp, 5 Volt USB Output
- Two Type A USB Ports
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

Ordering Information

DescriptionColorTamper Resistant 20A/125VLight AlmondDuplex, 5 Amp, 5 Volts USBPorts

UPC Number Catalog Number 883778306976 USB20A5LA


Listings

cULus Listed to UL498, UL1310

Specifications

Face Base LED Contacts Clamp Terminal Screws Mounting Strap Mounting Screws USB Port RTP RTP Green Indicator Plated Steel Plated Steel Idted Steel .040" Zinc Plated Steel Zinc Plated Steel Stainless Steel





20A STANDARD GRADE DEVICE

Online Resources

eCatalog

Performance

Electrical **Current Inturrupting** Certified for current inturrupting at full rated current Withstands 2,000V minimum **Dielectric Voltage** Complies with USB BC1.2 Battery Charging and 3.0 Power Delivery Specifications Mechanical Product Identification Ratings are a permanent part of the device **Terminal Accommodation** #14-#10 AWG copper stranded or solid conductor only **Terminal Identification** Terminals identified in accordance with UL 498 and CSA **USB** Ports Stainless steel rated for 10,000 plug incertions and removal

Environmental

Flammability Operating Temperature UL 94V-2 Maximum continuous 75°C, minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



Wiring Device-Kellems

HUBBELL