



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



W201 Wedge CLMP 1/0-4 Acsr Al

Nsi Industries

Catalog Number	W201
Manufacturer	Nsi Industries
Description	Aluminum Service Wedge Clamp For 1/0 - 4 Acsr - 1 Count Aluminum Service Wedge Clamps Are Used For Dead-Ending Self Supporting Drop Wire. Saves Conductor- Drop Wire May Be Cut to Exact Length. Can Be Attached to Bare Neutral In Any Point In The Span. Adjustment In Drop Wire Sag Are Easily Made. Grips Acsr, Aaac or Aluminum Conductor. Temperature Rating 90 Degrees C. Rated For 600V (2000V Max. Per UL486B). UL486A/B Listed Wire Connector.
Weight per unit	0.2700 (lbs/each)
Product Category	Miscellaneous Hand Tools

Features

Cable Size	1/0-4(ACSR) - 2/0 STR-2 SOL(Aluminum)
Material	Aluminum
Warranty	1 YEAR

Material, Color, and Finish

Color	Aluminum
Finish	Aluminum

Dimensions and Weight

Size	L=12 - Diameter=2.375
------	-----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	WEDGE CLMP 1/0-4 ACSR AL
extra long description	NSI W20-1 Wedge Clmp 1/0-4 Acsr Al
Features	Aluminum Service Wedge Clamp for 1/0 - 4 ACSR - 1 Count Aluminum Service Wedge Clamps are used for dead-ending self supporting drop wire. Saves conductor- drop wire may be cut to exact length. Can be attached to bare neutral in any point in the span. Adjustment in drop wire sag are easily made. Grips ACSR, AAAC or aluminum conductor. Temperature rating 90 degrees C. Rated for 600V (2000V max. per UL486B). UL486A/B Listed Wire Connector.
Long Description	Aluminum Service Wedge Clamp for 1/0 - 4 ACSR - 1 Count Aluminum Service Wedge Clamps are used for dead-ending self supporting drop wire. Saves conductor- drop wire may be cut to exact length. Can be attached to bare neutral in any point in the span. Adjustment in drop wire sag are easily made. Grips ACSR, AAAC or aluminum conductor. Temperature rating 90 degrees C. Rated for 600V (2000V max. per UL486B). UL486A/B Listed Wire Connector.
Product Type	Wedge CLMP 1/0-4 Acsr Al
Special Features	Saves Conductor - Drop Wire May Be Cut to Exact Length

Manufacturer Information

Brand	Nsi Industries
GTIN	00662381082817
Manufacturers Part Number	W20-1
UPC	662381082817

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Wedge Clamps

Packaging

Carton	1
Weight Per each	0.27

Uses, Certifications, and Standards

Application	Dead Ending Self Supporting Drop Wire
-------------	---------------------------------------