Product specifications

Eaton CE15DNS3AB

Catalog Number: CE15DNS3AB

Eaton XT IEC contactor, 18A, 110-120 Vac, 50-60 Hz, 1NO, 18A, Frame D, 55 mm, 50-60 Hz, 1 hp, Side, Three-pole, Non-reversing, No overload relay, Freedom, Contactor



General specifications

Product Name
Eaton XT IEC contactor

Catalog Number
CE15DNS3AB

UPC
782113778785

Product Length/Depth
3.25 in

Product Height
2.96 in

Product Width
1.8 in

Product Weight
1.01 lb

Warranty
Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances
ISO 9000
DIN VDE 0600

Certifications
IEC Rated
CSA Certified
UL Listed

Catalog Notes
No enclosure

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Amperage Rating

18A

HP rating - max

1 hp

Number Of Poles

Three-pole

Type

Contactor

Frequency rating

50-60 Hz

Frame size

55 mm

Coil voltage

110-120 Vac, 50-60 Hz

Contact configuration

1 NO

Continuous ampere rating

18 A

Relay

No overload relay

Series

Freedom

Operation

Non-reversing

Mounting method

Side

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Motor Starters and Contactors — Low Voltage Catalog

Specifications and datasheets

Eaton Specification Sheet - CE15DNS3AB



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia