Product specifications

# Eaton E50KL537



## Catalog Number: E50KL537

Limit Switch Lever, E50, Accessory, Adjustable roller, 3.10 in-oz min. return, Used with side rotary, Nylatron

### General specifications

**Product Name**
Eaton E50 NEMA heavy duty plug-in limit switch operator

**Catalog Number**
E50KL537

**UPC**
782113290904

**Product Length/Depth**
4.6 in

**Product Height**
1.52 in

**Product Width**
0.75 in

**Product Weight**
0.15 lb

**Warranty**
1 year

**Compliances**
RoHS Compliant

**Certifications**
UL Listed
CSA Certified
CE

Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Type

Accessory

### Used with

Used with side rotary

### Actuator

Adjustable roller

### Torque rating

3.10 in-oz min return

### Series

E50

### Operating temperature - max

200 °F

### Operating temperature - min

10 °F

### Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 13, IP67

### Material

Nylatron

## Resources

### Catalogs

Eaton's Volume 8—Sensing Solutions

### Specifications and datasheets

Eaton Specification Sheet - E50KL537

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia