Product specifications

Eaton CHF140

Catalog Number: CHF140

Eaton CH thermal magnetic circuit breaker,Type CHF 3/4-Inch standard circuit breaker,40 A,10 kAIC,Single-pole,120/240V,CHF,Trip flag, common breaker trip,#14-2 AWG Cu/Al,CHF,Type CH Loadcenters



General specifications

Product Name
Eaton CH thermal magnetic circuit breaker

Catalog Number
CHF140

UPC
786685532134

Product Length/Depth
3 in

Product Height
3 in

Product Width
0.75 in

Product Weight
0.25 lb

Warranty
Limited lifetime residential, 1 year commercial

Compliances
HACR Rated

Certifications
UL 489

Catalog Notes
HACR Rated, Single-Pole Requires One 2/4-Inch Space, With Trip Indication.

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Type CHF 3/4-Inch standard circuit breaker

Amperage Rating

40 A

Voltage rating

120/240 V

Trip Type

Trip flag

Circuit breaker type

CHF

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CHF

Wire size

#14-2 AWG Cu/Al

Number of poles

Single-pole

Resources

Brochures

Loadcenters and Circuit Breakers

Type CH Circuit Breakers and Loadcenters

Eaton's CHF Circuit Breaker with Trip Flag

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CHF140

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia