Product specifications

Eaton T20P11S10CU

Catalog Number: T20P11S10CU

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 240 X 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, 10 kVA, Cu windings , Frame: 815, uses WS15



Photo is representative

General specifications

Product Name	**Catalog Number**
Eaton General purpose ventilated transformer	T20P11S10CU
	UPC
	786680065156
Product Length/Depth	**Product Height**
15.82 in	30.25 in
Product Width	**Product Weight**
16.87 in	182 lb
Warranty	**Certifications**
Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Contact Manufacturer

Powering Business Worldwide

Physical Attributes

Coil material

Copper

Design

DS-3

Frame

815

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

10 kVA

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Miscellaneous

Weathershield

WS15

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - T20P11S10CU

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia