Product specifications

Eaton URS101BCH

Catalog Number: URS101BCH

Eaton meter socket, 1-pos resi service, 125A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, Three-wire, Ringless, 600 Vac



General specifications

Product Name
Eaton meter socket

Catalog Number
URS101BCH

UPC
782114003985

Product Length/Depth
3.5 in

Product Height
10.88 in

Product Width
8 in

Product Weight
7 lb

Warranty
Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications
UL Listed

Catalog Notes
Suitable for either top or bottom service cable entry, Iowa approved

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Single-position residential service

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Line

#8-2/0 AWG

Load

#8-2/0 AWG

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Security

Ringless

Voltage rating

600 V

Number of sockets

1

Resources

Brochures

Single Meter Sockets

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT 125A 1P HO

Specifications and datasheets

Eaton Specification Sheet - URS101BCH

Metering Equipment - Utilities Servicing Upstate New York

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia