Product specifications

Eaton BR120

Catalog Number: BR120

Eaton BR thermal magnetic circuit breaker,Type BR 1-Inch plug-on circuit breaker,20 A,10 kAIC,Single-pole,120/240V,BR,#14-4 AWG Cu/Al,Q1,BR,Type BR loadcenters



General specifications

Product Name
Eaton BR thermal magnetic circuit breaker

Catalog Number
BR120

UPC
786676362108

Product Length/Depth
2.5 in

Product Height
3 in

Product Width
1 in

Product Weight
0.3 lb

Warranty
Limited lifetime residential, 1 year commercial

Compliances
Federal Specifications Classification W-C375

Certifications
UL 489

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

20 A

Voltage rating

120/240 V

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Single-pole

Quantity

1

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Type BR, BD, BQ, BQC,BRH, GFCB, GFCBH, 10-70Amp 1-Pole - Curve

Specifications and datasheets

Eaton Specification Sheet - BR120

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia