Product specifications

Eaton FH28

Catalog Number: FH28

Eaton A200/B100 heater, Used with Starter Sizes 0,1, and 2, A200/B100 Heater, NEMA, Ambient 2.84-3.11, 3.29-3.60A, Non-Comp 2.64-2.89, 3.22-3.53A, Used with Starter Sizes 0,1, and 2, Type A and B, Thermal and Fast Trip



Photo is representative

General specifications

Product Name
Eaton A200/B100 heater

Catalog Number
FH28

UPC
782114166963

Product Length/Depth
2.1 in

Product Height
0.8 in

Product Width
1.3 in

Product Weight
0.02 lb

Warranty
Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications
UL Listed
CSA Certified

Catalog Notes
Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Used with Starter Sizes 0,1, and 2

Type

A200/B100 Heater

Used with

Used with Starter Sizes 0,1, and 2

Design

NEMA

Full load current range

Ambient 2.84-3.11, 3.29-3.60 A, Non-Comp 2.64-2.89, 3.22-3.53 A

Overload relay

Type A and B

Trip type

Thermal and fast trip

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Installation instructions

Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers

Specifications and datasheets

Eaton Specification Sheet - FH28

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia