Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F32T8SPP50EC0 32W T8 48" 5000K 80 Cri

Ge By Current Lamps

Catalog Number	F32T8SPP50EC0
Manufacturer	Ge By Current Lamps
Description	Linear Fluorescent Lamp, Pin/Plug-In G13 Base, T8 Bulb Shape, 80, 30000 H Average Life, 5000 K, 32 W, 2900 LM Brightness (Lumens), Soda Lime Glass Housing Material, 1.0 In Diameter, 48.0 In Length, Instant;Rapid, +10 °C Operating Temperature, 0.55 LB/Ea
Weight per unit	0.5600 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
lumens	2900.0
Wattage	32.0

Material, Color, and Finish

color rendering index (cri)	80.0

Dimensions and Weight

Length	48.0

Descriptions

Description	32W T8 48" 5000K 80 CRI
extra long description	GEL F32T8/SPP50/ECO 66350 SLIM LINE

Manufacturer Information

Brand	GE Current
GTIN	00043168663502
sub brand	GE?®
UPC	043168663502

Taxonomies, Classifications, and Categories

Category Description	Fluorescent

Availability

minimum qty	36

Packaging

Carton	1
Package	36
Weight Per each	0.56