



C
Lighting & Lighting Controls

SECTION



Lighting & Lighting Controls

Lighting & Lighting Controls

Cooper Lighting Solutions Fixtures

LED Lay-ins, Flat Panels, Strip Lights, Wrap	
Arounds.....	C4
LED Vaportite.....	C4
LED Surface Mount, Disk Lights.....	C5
LED Recessed Trims, Gimbals.....	C5
LED Recessed Housings.....	C6
Traditional Recessed Housings & Trims.....	C6-C7
LED Floodlights.....	C8
LED High Bays.....	C8
LED Wall Packs.....	C8
LED Wall Lights, Area Lights, Security Floods.....	C9
LED Emergency Lighting.....	C10
LED Undercabinet.....	C10
LED Bluetooth Shoplight.....	C10
Traditional Troffers, Strip Lights, Wrap	
Arounds.....	C11
Traditional Vaportight.....	C11
Traditional High Bays.....	C11
Traditional Undercabinet.....	C11

Lithonia Lighting Fixtures

LED Lay-ins, Flat Panels, Strip Lights, Wrap	
Arounds.....	C12
LED Vaportite.....	C13
LED Shoplight.....	C13
LED High Bays.....	C13
LED Downlights.....	C14
LED Undercabinet.....	C14
LED Emergency Lighting.....	C14
LED Vaporproof.....	C14
LED Wall Packs.....	C15
LED Floodlights.....	C15
LED Area Lights.....	C15
Traditional Troffers, Strip Lights, Wrap Arounds.....	C16
Traditional High Bays.....	C16

RAB Products

LED Floodlights, Area Lights.....	C17
Poles.....	C17
LED High Bays.....	C18
LED Wall Packs, Garage Lights.....	C18
LED Washdowns.....	C18
Traditional Wall Packs.....	C18
LED Compact Floodlights, Spotlights.....	C19
LED Wrap Arounds.....	C19
LED Vaporproof.....	C19
Mighty Posts.....	C19
LED Lamps.....	C20

Lamp Accessories

Lamp Accessories.....	C21
Temporary Lighting.....	C21

GE Lamps

LED Tubes.....	C22
LED A-Line, PAR, Reflector.....	C22
LED HID Replacements.....	C23
LED CFL Plug-in Replacements.....	C23
LED Decorative.....	C23
LED Compact PAR.....	C24
LED Directional.....	C24
LED Candle, Vintage.....	C24
Traditional A-Line, PAR, Reflector.....	C25
Traditional Exit Sign, Quartz, Appliance.....	C25
Traditional Halogen.....	C25
Traditional Tubes.....	C26

GE Lamps (Continued)

Metal Halide.....	C27
High Pressure Sodium.....	C27
Biax.....	C27

Sylvania Lamps

LED A-Line, PAR.....	C28
LED Tubes.....	C28
LED Reflector, MR16.....	C29
LED Filament, Vintage.....	C29
LED HID Replacements.....	C30
LED U-Shaped, TT5, Pin Base.....	C30
Traditional: A-Line, PAR, Reflector.....	C31
Traditional: Halogen, Decorative.....	C31
Traditional Tubes.....	C31
Metal Halide.....	C32
High Pressure Sodium.....	C32
Biax.....	C32
Traditional U-shaped, Circline, T5.....	C32

Keystone Products

LED Tubes.....	C33
LED Strips.....	C33
LED HID Replacement.....	C34
LED PLL, CFL Replacement.....	C34
LED High Bay Replacement.....	C34
LED A-Line, PAR, Reflector, MR16.....	C35
LED Decorative.....	C35

Tape Lights

LED Tape Lights.....	C36
----------------------	-----

Ballasts & Drivers

Ballasts.....	C37
Programmable Drivers.....	C37

Satco Lamps

LED HID Replacements.....	C38
LED Filament.....	C38
LED PAR, Reflector.....	C38
LED Miniature Lamps.....	C38

Lutron Products

Dimmers, Fan Controls.....	C39
Sensors.....	C40
Vive Hubs.....	C40
Radio Powr Wireless Sensors.....	C40
RF Receptacles.....	C40
Maestro Wireless, Powpak Controls.....	C41
Remote Controlled Shades.....	C41
Vive Wireless.....	C41
Ra2 Products.....	C42
Caseta Wireless.....	C42

Tork Products

Photocontrols.....	C43
Time Clocks.....	C44

Builder Products

Fan Units.....	C45
Chime Kits.....	C45
Smoke Alarms.....	C46
Area Heaters.....	C46
Vinyl Ducting.....	C46

Lighting Showroom



In the Lighting Showroom, we have some of the most knowledgeable lighting specialists in East Texas, and no one can beat our total value of service and price. Located in Nacogdoches, Texas, we offer the highest level of service and appreciation for every sale from a simple lightbulb to a large lighting project.

With our up-to-date lighting knowledge, the Lighting Showroom can help you find the right light for any space. Our mission is to provide customers of Elliott Electric Supply the best buying experience as well as the latest information in lighting and lighting products.

What We Offer

The Lighting Showroom offers the widest array of lighting options in the area and we are ready to help with all of your lighting needs, whether it's a remodel or new construction. Come in or contact us today to learn how we can help you save!

- Free lighting design and consultations
- Free delivery based on your location.
- Discount prices for building contractors and whole home orders

Online Showroom



Contact Us

Elliott Electric Supply
Lighting Showroom
2310 N. Stallings Dr.
Nacogdoches, TX
75964

(936) 569-7941

LED LAY-INS



GR Series

RTC

Skyridge

The GR Series is a recessed lensed LED troffer optimal performance and energy efficiency compatible with all of today's popular ceiling systems and is available with a number of shielding options and accessories.

The RTC lensed troffer series provides performance, reliability and flexibility with a housing optimized for shallow plenums. These center illuminated troffers provide numerous options for color, lumens, controls and sensing.

The SkyRidge™ Series offers an aesthetically pleasing, yet affordable LED alternative to fluorescent fixtures. WaveStream™ technology provides unmatched optical performance, efficiency and unique visual style.

Vendor Code: ETL

Catalog Number	Lumens	Kelvin	Watts	Size	Price Each
GR SERIES					
22GR3240D	3,200	4,000K	33	2' x 2'	111.18
24GR4240D	4,200	4,000K	37	2' x 4'	144.64
RTC					
22RTC3440	3,523	4,000K	29	2' x 2'	158.40
24RTC4840	4,775	4,000K	38	2' x 4'	106.54
SKYRIDGE					
22SRLED229CUNVL84	2,900	4,000K	23.4	2' x 2'	295.96
24SRLED248CUNVL84	4,800	4,000K	38.2	2' x 4'	306.07

Other Color Temperatures are Available. Replace the Black Numbers with 35 for 3,500K or 40 for 4,000K.


LED FLAT PANELS
FPANEL LED PANEL SERIES

FPANEL LED panel series provide premium performance and pleasing aesthetics. The luminaire is optimized for shallow plenum grid ceilings but may also be surface or suspension mounted. These panels are ideal for both new construction and renovation of existing fluorescent troffers. The panel's refined visual optics and integrated grid retention clips provide the features needed for installation, speed and flexibility. LED FPANELS are an excellent lighting solution for commercial office spaces, schools, healthcare facilities and retail merchandising areas.

Vendor Code: ETL

Catalog Number	Lumens	Color	Watts	Size	Price Each
22FP3240C*	3,560	4,000K	30	2' x 2'	57.43
24FP4740C*	4,858	4,000K	40	2' x 4'	89.91
FLAT PANEL SURFACE MOUNTING KITS					
FPSURF22	2' x 2' Mounting Kit				35.69
FPSURF24	2' x 4' Mounting Kit				45.55

*Replace 40 with 35 for 3,500K or 50 for 5,000K.

LED STRIP LIGHTS
ST2 STRIP SERIES

Vendor Code: ETL

Catalog Number	Length	Lumens	Color	LPW	Price Each
2ST2L2040R	2'	2,298	4,000K	121	60.00
4ST2L4040R	4'	4,433	4,000K	114	85.97

Only Available in 4,000K

LED CLASSIC WRAP AROUNDS
WNLED SERIES

Vendor Code: ETL

Catalog Number	Length	Lumens	Color	LPW	Price Each
4WNLEDD440SLFUN	4'	4,062	4,000K	113	174.21

2' Lengths Also Available.


Also Available in 3,000K, 3,500K and 5,000K.

LED WRAP AROUNDS
CWPLD SERIES

Vendor Code: ETL

Catalog Number	Length	Lumens	Color	LPW	Price Each
4CWPLD4040C	4'	4,200	4,000K	92	117.48

VAPORTITE LED SERIES



Vendor Code: ETL

Catalog Number	Length	Lumens	Color	LPW	Price Each
4VT2LD46DRUNVL84	4'	6,000	4,000K	105	229.50

Other Color Temperatures are Available. Replace the Black Number with 3 for 3,000K and 5 for 5,000K.

LED Products (Surface Mount · Ultra Thin Downlights · Retrofit Adjustable Gimbals)

LED SURFACE MOUNT BLD SERIES



BLD606930WH




BLD406930WH

Vendor Code: **ETL**

Catalog Number	Size	CRI	Color	Lumens	LPW	Price Each
BLD606930WHR	6"	90	3,000K	700	85	24.69
BLD406930WHR	4"	90	3,000K	690	84	32.46

Other Color Temperatures are Available. Replace the Two Black Numbers with **27** for 2,700K, **40** for 4,000K, or **50** for 5,000K.

LED DISK LIGHT



Vendor Code: **ETL**


Catalog Number	Size	Watts	Color	Lumens	CRI	Price Each
HLC6099301EWH12X	6"	15	3,000K	900	92	10.72
HLC4079301EWH12X	4"	15	3,000K	750	92	10.72

Also Available in 4,000K and 5,000K.


ULTRA THIN LED DOWNLIGHT FIELD SELECTABLE CCT



HLB and Connector
(Round)




HLB and Connector
(Square)



New Construction
Mounting Frames

• The SeleCCTable technology puts flexibility at your fingertips. By using the switch located on the driver junction box, the user can choose from a range of five color temperatures 2,700K - 5,000K.




Vendor Code: **ETL**


Catalog Number	Size	CRI	Color	Lumens	LPW	Price Each
ROUND						
HLB6099FS1EMWR	6"	90	2,700K-5,000K	1,061	66	28.00
HLB4069FS1EMWR	4"	90	2,700K-5,000K	723	60	28.00
SQUARE						
HLB6099FS1EMWR	6"	90	2,700K-5,000K	975	71	32.32
HLB4069FS1EMWR	4"	90	2,700K-5,000K	696	69	45.60
MOUNTING FRAMES TO RESERVE SPACE						
HL6RSMF	6" New Construction Mounting Frame					5.42
HL4RSMF	4" New Construction Mounting Frame					5.42

Lumens and LPW Data is Based on 3,000K Selection
Direct Mount - Does Not Require Recessed Housing or Junction Box

LED RECESSED RETROFIT TRIMS DIMMABLE LED MODULES



LT460WH6930




LT560WH6930

Vendor Code: **ETL**


Catalog Number	CRI	Color	Lumens	LPW	Price Each
4" LED RETROFIT DOWNLIGHT					
LT460WH6930R	90	3,000K	554	69.25	15.48
5" OR 6" LED RETROFIT DOWNLIGHT					
LT560WH6930R	90	3,000K	683	68.3	13.66

Other Color Temperatures are Available. Replace the Two Black Numbers with **27** for 2,700K, **30** for 3,000K, **40** for 4,000K, or **50** for 5,000K.

LED RETROFIT ADJUSTABLE GIMBALS



LA4069301EWH



LA56069301EWH

Vendor Code: **ETL**

Catalog Number	CRI	Color	Lumens	LPW	Price Each
4" LED RETROFIT ADJUSTABLE GIMBAL					
LA4069301EWH	90	3,000K	613	71	41.49
RA4069S1EWHR	90	2,700K - 5,000K	615	88	43.92
5 OR 6" LED RETROFIT ADJUSTABLE GIMBAL					
LA56069301EWH	90	3,000K	637	73	41.49
RA56069S1EWHR	90	2,700K - 5,000K	670	90	40.54

*Field Selectable Color Temperatures are 2,700K, 3,000K, 3,500K, 4,000K, or 5,000K. Specs listed are based on 3,000K.

120V LED SURFACE MOUNT



Round Direct Mount



Square Non-Direct Mount

Vendor Code: **ETL**


Catalog Number	Shape	Size	CRI	Color	Lumens	LPW	Price Each
INSTALLS IN RECESSED HOUSINGS OR JUNCTION BOX							
SMD6R6930WH	Round	6"	92	3,000K	758	79	30.58
SMD6S6930WH	Square	6"	92	3,000K	790	80	31.27
SMD4R6930WH	Round	4"	93	3,000K	700	72	30.58
SMD4S6930WH	Square	4"	92	3,000K	790	80	31.27
DIRECT MOUNT W/CLIPS (NO HOUSING OR JUNCTION BOX REQUIRED)							
SMD6R6930WHD	Round	6"	92	3,000K	758	79	36.65
SMD6S6930WHD	Square	6"	92	3,000K	790	80	36.65
SMD4R6930WHD	Round	4"	93	3,000K	700	72	36.65
SMD4S6930WHD	Square	4"	92	3,000K	790	80	36.65

Other Color Temperatures are Available. Replace the Two Black Numbers with **27** for 2,700K, **40** for 4,000K, or **50** for 5,000K.
Junction Box Must be 2-1/8" Deep.


Lighting & Lighting Controls

LED Recessed Housings · Shallow Downlight Housings · Recessed Trims

LED 6" RECESSED HOUSINGS



E750ICAT




E750RICAT


Vendor Code: **ETL**

Catalog Number	Description	Price Each
E750ICAT	20W Max, Airtight Insulation Contact	15.53
REMODEL HOUSINGS		
E750RICAT	20W Max, Airtight Insulation Contact	16.52

LED 4" RECESSED HOUSINGS



H995ICAT




H995RICAT


Vendor Code: **ETL**

Catalog Number	Description	Price Each
H995ICAT	15W Max, Airtight Insulation Contact	31.19
REMODEL HOUSINGS		
H995RICAT	15W Max, Airtight Insulation Contact	34.36

4" HOUSINGS AND TRIMS FOR LED MR16 LAMPS



E44MR16ICAT



E44MR16RICAT



1431WBWF



1432MWWF




1433MWWF


Vendor Code: **ETL**

Catalog Number	Description	Price Each
E44MR16ICAT	10W Max, Airtight Insulation Contact	32.99
REMODEL HOUSINGS		
E44MR16RICAT	10W Max, Airtight Insulation Contact	42.70
4" TRIMS FOR LED MR16 HOUSINGS		
1431WBWF	Conical Baffle, White Trim Ring with White Baffle	16.75
1432MWWF	Angle Cut Reflector with Lens Wall Wash, White	29.82
1433MWWF	Conical Reflector with Diffuse Lens, White	25.25

6" RECESSED INCANDESCENT OR LED



New Construction




Remodel

Vendor Code: **ETL**


Catalog Number	Description	Carton Quantity	Price Each
E7TAT	150W Max., Airtight No Insulation Contact	6	15.91
E7ICAT	90W Max., Airtight Insulation Contact	6	14.95
REMODEL HOUSINGS			
E7RTAT	150W Max., Airtight No Insulation Contact	6	17.66
E7RICAT	90W Max., Airtight Insulation Contact	6	23.15

Popular Fixtures Indicated in Bold.

6" SHALLOW DOWNLIGHT HOUSINGS



New Construction



Remodel

Vendor Code: **ETL**

Catalog Number	Description	Carton Quantity	Price Each
E27TAT	100W Max., Airtight No Insulation Contact	6	26.94
E27ICAT	75W Max., Airtight Insulation Contact	6	15.97
REMODEL HOUSINGS			
E27RTAT	75W Max., Airtight No Insulation Contact	6	18.17
E27RICAT	75W Max., Airtight Insulation Contact	6	16.11

6" RECESSED TRIMS



70PS



300P/301P



6100BB/6100WB



401P



6101BB/6101WB



6106SC


Vendor Code: **ETL**

Catalog Number	Description	Price Each
70PS	Albalite Lens Shower Light, White Trim	38.63
300P	Open, White Trim, Socket Bracket	10.15
301P	White Open Trim	9.12
6100BB	White Trim with Black Metal Baffle	4.13
6100WB	White Metal Trim Ring and White Baffle	3.76
401P	White Open Trim	10.96
6101BB	Black Metal Baffle with White Trim (Narrow and Wide)	3.63
6101WB	White Metal Baffle with White Trim (Narrow and Wide)	3.76
6103BB	Black Metal Baffle with White Trim	8.65
6103WB	White Metal Baffle with White Trim	2.67
6106SC	White Self-Flange Trim, Clear Specular Reflector	13.76
6110WB	White Perflex Baffle, White Self-Flange Trim	5.80

Popular Fixtures Indicated in Bold.

Recessed Housings · Low Voltage Downlight Housings


6" RECESSED HOUSINGS AND TRIMS NO SOCKET BRACKET


 Vendor Code: **ETL**

Catalog Number	Description	Price Each
ET1CATNB	90W Max., Airtight Insulation Contact	20.37
SOCKET SUPPORTING TRIMS FOR HOUSINGS		
6130WH	White Adjustable Eyeball	9.63
6125BB	White Self-Flange Trim Ring and Black Baffle	5.25
6125WB	White Self-Flange Trim Ring and White Baffle	5.25
6150WH	Frost Dome Lens Shower Light, White Trim	21.69

Popular Fixtures Indicated In Bold.


4" DOWNLIGHT HOUSINGS AND TRIMS


 Vendor Code: **ETL**

Catalog Number	Description	Price Each
5-1/2" NEW CONSTRUCTION		
E4TATSB	50W Max., Airtight No Insulation Contact	13.89
5-1/2" REMODEL HOUSINGS		
E4RTATSB	50W Max., Airtight No Insulation Contact	13.89
5-7/8" HOUSINGS		
E4ICATSB	50W Max., Airtight Insulation Contact	18.83
TRIMS FOR 4-1/2" HOUSINGS		
4001BB	Plastic Step Baffle, White Trim Ring with Black Baffle	8.11
4001WB	Plastic Step Baffle, White Trim Ring with White Baffle	8.11
4002WH	Eyeball - 30° Tilt, White Trim Ring with White Eyeball	12.44

Popular Fixtures Indicated In Bold.


SLOPED CEILING RECESSED INCANDESCENT DOWNLIGHT HOUSINGS AND TRIMS


 Vendor Code: **ETL**

Catalog Number	Description	Price Each
HOUSINGS 6-1/2" DIAMETER, 7-3/8" DEPTH		
H645IC	AIR-TITE™ Sealed, 2/12-12/12 Pitch	30.89
TRIMS FOR H645IC		
456W	White Trim with White Coilex Baffle	25.87
456P	White Trim with Black Coilex Baffle	42.91
HOUSINGS 5-1/4" DIAMETER, 6-1/2" - 8-3/4" ADJUSTABLE DEPTH		
H471CAT	AIR-TITE™ Insulation Contact, 2/12-12/12 Pitch	52.11
TRIMS FOR H471CAT		
498P	White Trim with Black Baffle	54.09
78P	Eyeball - 30° Tilt, White Trim with White Eyeball	35.28
170PS	White Trim with Frosted Albalite Lens	45.41

Popular Fixtures Indicated in Bold.


4" LOW VOLTAGE DOWNLIGHT HOUSINGS WITH INTEGRAL TRANSFORMER


 Vendor Code: **ETL**

Catalog Number	Description	Price Each
4-1/2" DIAMETER, 7-1/4" DEEP, NEW CONSTRUCTION HOUSINGS		
H1499ICAT	Airtight Insulation Contact	103.54
4-1/2" DIAMETER, 7-1/4" DEEP, REMODEL HOUSINGS		
H1499RTAT	Airtight, No Insulation Contact	74.97
TRIMS FOR LOW VOLTAGE HOUSINGS		
1420P	White Trim, Adjustable Slot Aperture, 35° Tilt	26.52
1421C	White Trim w/Clear Specular Reflector, 35° Tilt	64.10
1493W	White Trim w/Black Foilex Baffle, 35° Tilt	17.22



LED FLOODLIGHTS
NIGHT FALCON™




Night Falcon - Small Knuckle Mount Night Falcon Slipfitter Mount Night Falcon - Large Trunnion Mount

Whether the project is lighting a sign, building facade or parking lot, the Night Falcon™ LED floodlight series makes the choice easy. Combining value and performance in a robust design, the Night Falcon LED floodlight series offers two distributions that deliver superior uniformity and excellent illumination to the targeted application. With lumen packages ranging from 2,700 to 33,100 lumens, the Night Falcon LED floodlights are the ideal solution for replacing legacy metal halide solutions ranging from 70 to 1000 watts.

Vendor Code: **ETL**

Catalog Number	Mounting	Lumens	Color	Watts	Price Each
NIGHT FALCON - SMALL					
NFFLDSC15TUNV	Trunnion	5,900	4,000K	51	303.33
NFFLDSC15KNCUNV	Knuckle	5,900	4,000K	51	303.33
NIGHT FALCON					
NFFLDC25S	Slipfitter	10,530	4,000K	85	482.16
NFFLDC40S	Slipfitter	16,932	4,000K	128	586.00
NFFLDC25T	Trunnion	10,530	4,000K	85	463.33
NFFLDC40T	Trunnion	16,932	4,000K	128	569.73
NIGHT FALCON - LARGE					
NFFLDLC100S	Slipfitter	33,900	4,000K	252	1244.10
NFFLDLC100T	Trunnion	33,900	4,000K	252	1209.40
NIGHT FALCON - ACCESSORY					
RABBZ	Right Angle Wall Mount Bracket for Slipfitter				167.12

LED HIGH BAY LUMINAIRES




HBLED Series VHBLED Series

Vendor Code: **ETL**

Catalog Number	Watts	Lumens	Color	LPW	Price Each
HBLED SERIES					
HBLEDLD512SEWUNV	75	11,456	5,000K	153	372.85
HBLEDLD524SEWUNV	149.5	22,339	5,000K	149	521.71
VHBLED SERIES*					
VHBLEDLD12WUNV	100	13,009	5,000K	130	110.78
VHBLEDLD18WUNV	160	19,263	5,000K	120	141.53
VHBLEDLD124WUNV	213	24,000	5,000K	112	167.68

*Accessories Also Available Including an Installed 180° or 360° Motion Sensor and LumaWatt Wireless Sensor System. Ask Your Sales Representative for More Details.

LED ROUND HIGH BAYS



Vendor Code: **ETL**

Catalog Number	Watts	Voltage	Lumens	Price Each
FIXTURES				
RHB12UNVL850CDU	114	120-277	12,000	245.00
RHB18UNVL850CDU	154	120-278	18,000	280.00
RHB24UNVL850CDU	194	120-279	24,000	350.67

Vendor Code: **ETL**


Catalog Number	Description	Price Each
REFLECTORS/LENS		
RHBFRR	16" Frosted Reflector	54.17
RHBCLR	16" Clear Reflector	41.67
RHBALR	16" Aluminum Reflector	41.67
RHBGGL	16" Clear Glass Shield	41.67

INDUSTRIAL ACCESSORIES

Vendor Code: **ETL**

Catalog Number	Description	Price Each
FH1	Fixture Hook (2-1/2")	15.20
SHK	Fixture Hook with Safety Screw (2-1/2")	21.70
FL1	Fixture Loop (2-1/2")	22.59

LED WALL PACKS



XTOR Crosstour™ XTOR Crosstour™ Maxx Wal-Pak


Vendor Code: **ETL**

Catalog Number	Watts	Lumens	LPW	Price Each
XTOR CROSSTOUR™ LED				
XTOR1B	12	1,418	118	131.12
XTOR2B	18	2,135	119	157.98
XTOR3B	26	2,751	106	225.09
XTOR4B	38	4,269	112	239.55
XTOR CROSSTOUR™ MAXX LED WITH REFRACTIVE LENS				
XTOR6BRL	58	6,225	107	283.66
XTOR8BRL	81	8,635	107	398.60
WAL-PAK WITH REFRACTIVE LENS				
WPL3B	27	3,333	123	335.93
WPL4B	32	4,199	131	376.94
WPL6B	46	5,883	128	435.02




Lighting & Lighting Controls

ALL-PRO™ LED AREA WALL LIGHT



AL3050LPCGY




EA24

Vendor Code: **ETL**


Catalog Number	Watts	Lumens	Color	HID Equivalent	Price Each
AL3050LPCGY*	34	3,300	5,000K	175W	127.53
EA24	24" Mounting Arm for Pole Mount				28.23

*Comes Standard with 12,000 Cycle Rated Integrated Photocontrol.
*Catalog Number Listed has a Gray (GY) Finish. For a Bronze Finish, Change the **GY** to **BR**.

LED AREA LIGHT CARETAKER™



CTKRV1B




SRCARETAKER

Vendor Code: **ETL**


Catalog Number	Watts	Lumens	Color	HID Equivalent	Price Each
CTKRV1B	29	4,515	4,000K	100-150W	151.94
SRCARETAKER	Small Acrylic Refractor				32.73

CTKRV1A Comes Standard with NEMA 3-Pin Twistlock Photocontrol for Dusk-to-Dawn Operation.

REVOLVE™ LED DUSK TO DAWN



REV21835MW



REV32735MW

The patents-pending Revolve™ LED outdoor security product line by All-Pro™ combines advanced LED technology and industry-leading optic design to bring you a low-profile fixture with uncompromising performance. An integral photo control provides nighttime ON, daytime OFF functionality. Refractive optics eliminate the need for bulky reflectors, while allowing you to easily aim the light precisely where you need it by simply rotating the optic. The end result is a sleek, aesthetically appealing LED fixture that remains virtually unnoticeable when not in use.


Vendor Code: **ETL**

Catalog Number	Watts	Lumens	Color	Price Each
DOUBLE HEAD WITH 180° MOTION RANGE				
REV21850M	27	2,150	5,000K	152.98
TRIPLE HEAD WITH 270° MOTION RANGE				
REV32750M	32	2,400	5,000K	165.79


White Finish

For a Bronze Finish, Remove the **W** from the End of the Catalog Number.

HALO HOME SMART LED SECURITY FLOODS



MST20C



FTS20C

The HALO Home smart LED motion sensor flood incorporates Bluetooth® Mesh technology into a durable, twin head design for an advanced outdoor lighting solution built for high performance. The MST20C does not require a hub and can be wirelessly controlled directly from any compatible smart device utilizing the HALO Home app, or any HALO Home wireless switch or dimmer.


The HALO Home smart LED floodlight incorporates Bluetooth® Mesh technology into a durable, twin head design for an advanced outdoor lighting solution built for high performance. The FTS20C does not require a hub and can be wirelessly controlled directly from any compatible smart device utilizing the Halo Home app, or any Halo Home wireless switch or dimmer.

Vendor Code: **ETL**


Catalog Number	Finish	Lumens	Color	Price Each
TWIN HEAD SQUARE FLOOD WITH 180° MOTION SENSOR				
MST20C18B	Bronze	2,034	3,000K - 5,000K	171.53
TWIN HEAD SQUARE FLOOD (NO SENSOR)				
FTS20CB	Bronze	2,034	3,000K - 5,000K	160.33

For a White Finish, Replace the **B** with a **W** at the End of the Catalog Number.

ALL-PRO™ LED SECURITY FLOODS



MST18R17L



FTR1740L

The All-Pro™ LED Twin Head Round Motion Fixtures as well as the All-Pro™ LED Twin Head Round Flood Fixtures utilize the latest in LED technology for maximum light output in a low-profile, compact housing. This design is ideal as a direct replacement for traditional styles, producing the equivalent of a 150W incandescent fixture. Available in white or bronze, they can be wall or eave mounted for a wide range of applications.

Vendor Code: **ETL**

Catalog Number	Finish	Delivered Lumens	Color Temp.	Price Each
TWIN HEAD ROUND FLOOD W/ 180° MOTION SENSOR				
MST18R17L	Bronze	1,600	5,000K	129.92
TWIN HEAD ROUND FLOOD (NO SENSOR)				
FTR1740L*	Bronze	1,600	5,000K	122.20


For a White Finish, Add **W** to the End of the Catalog Number.

*For Integrated Photoctrl, Add **PC** to the End of the Catalog Number. For Integrated Photoctrl and White Finish Add **PCW** to the End of Catalog Number.




Lighting & Lighting Controls


LED EMERGENCY LIGHTING



APEL



SEL17


SELW25
(Wet Location)Vendor Code: **ETL**

Catalog Number	Description	Price Each
APEL	Two Long Life LED Emergency Heads	28.75
SEL17	LED Emergency Light with 17" Coverage	60.64
SELW25*	Sure-Lites Wet Location Emergency Light	142.67

120/277V

*Catalog Number Listed Above is Silver in Color. Add Suffix **BK** for Black, **BZ** for Bronze, or **WH** for White.

LED EMERGENCY BATTERY PACKS



EBPLED7W


Vendor Code: **ETL**

Catalog Number	Description	Price Each
EBPLED14W	LED Emergency Battery Pack with 14W Output	337.61

LED EMERGENCY EXIT LIGHTS



APX Series




APC Series

Vendor Code: **ETL**

Catalog Number	Description	Price Each
APX7R	Self-Powered LED, Red Letters, Universal Mounting, 120/277V	29.20
APC7R	Self-Powered Dual LED Heads, Red Letters, 120/277V	56.92

Add **BK** at the End of the Catalog Number for Black Housing. Change **R** to **G** for Green Lettering.

LED BLUETOOTH SHOPLIGHT




The SHP BTS is a fully integrated LED shoplight with Bluetooth wireless speakers. The SHP BTS speakers provide clear, balanced sound that can fill an entire workspace. Easily listen to your favorite music or podcast wirelessly in your home or workshop. This rugged, lightweight, portable and slim profile shoplight combines a polycarbonate housing body and lens with LEDs rated for 50,000 hours of life. Typical applications include workshops, garages, sheds and utility rooms.

Vendor Code: **ETL**


Catalog Number	Length	Lumens	Color	LPW	Price Each
4SHP3240BTS	4'	3,782	4,000K	122	91.58

Only Available in 4,000K


HU10 LED UNDERCABINET LIGHTS



HU1018D930P



HU103P



HU109P

Ideal for task, accent, office, cove, utility, under and above cabinet lighting display, the Halo Undercabinet low-profile design delivers maximum energy savings and life with easy installation. The integrated driver allowing 120V direct to the fixture for easy installation. Fixtures are available in 9, 18, 24, 36, or 48 inch lengths, the Halo system can be configured to fit almost anywhere. Smooth dimming down to 5% using a standard dimmer. Connector cables in a variety of different lengths make it easy to link one unit to another. Each unit has an integrated on-off switch.

Vendor Code: **ETL**

Catalog Number	Description	Price Each
HALO INTEGRATED DRIVER UNDERCABINET		
HU1018D930P*	18" Dimmable Fixture, 90 CRI, 3,000K, White Finish	84.27
HU1024D930P*	24" Dimmable Fixture, 90 CRI, 3,000K, White Finish	85.90
HU1036D930P*	36" Dimmable Fixture, 90 CRI, 3,000K, White Finish	115.58
CONNECTORS		
HU103P*	24" Daisy Chain Connector, White Finish	41.35
HU109P*	Splice Box, White Finish	52.59

Replace **P** with **MB** for **Matte Black**.

ALL PRO FLUORESCENT LENSED TROFFERS



Vendor Code: **ETL**

Catalog Number	Number of Lamps	Lamp Type	Length	Price Each
APT2U6T8	2	F32T8U	2' x 4'	117.53
APT332L735	3	F32T841K*	2' x 4'	106.20
APT432L741	4	F32T841K*	2' x 4'	149.70
REPLACEMENT LENS				
A12100242GU	-	-	-	23.48

120/277V

*Lamps Included.

ALL PRO FLUORESCENT STRIP LIGHTS



Vendor Code: **ETL**

Catalog Number	Number of Lamps	Lamp Type	Length	Price Each
STANDARD BODY 120-277V				
SF2323UNVEB81U	2	F32T8	4'	78.02
APS8WS232	4	F32T8	8'	86.46
HIGH OUTPUT 120V				
SF296H0120VEB21**	2	F96T12H0	8'	258.77
WIRE GUARD				
WGSSF4FTB	-	-	4'	23.05

*120V Only.

** Low Power Factor Ballast

ALL PRO FLUORESCENT WRAP AROUND FIXTURES




Vendor Code: **ETL**

Catalog Number	Number of Lamps	Lamp Type	Length	Price Each
APWGPW232	2	F32T8	4'	66.69
APWGPW432	4	F32T8	4'	85.17

120/277V



FLUORESCENT INDUSTRIAL VAPORTIGHT



The VT3 Series is a contemporary looking energy efficient industrial Vaportite fixture that features rugged and durable construction. The VT3 incorporates a full metal gear tray inside a reinforced fiberglass housing with a high impact diffuser. This Vaportite series is suitable for interior and exterior applications and can be surface or chain mounted. The VT3 Series has been designed for maximum operation in commercial institutional and industrial environments where weathering, high temperature, humidity and dust or corrosive fumes are present.

Vendor Code: **ETL**

Catalog Number	Number of Lamps	Lamp Type	Length	Price Each
VT3232DRUNVEB81W	2	F32T8	4'	171.77

120/277V

FLUORESCENT HIGH BAY (F-BAYS)



APHL series is ideal for industrial or retail applications. Optical designs provide ideal performance from either T5 or T8 lamps. Uplight component produces excellent ceiling uniformity. APHL's high lumen package allows the benefits of fluorescent to be applied at high mounting heights that were traditionally exclusive to H.I.D. Benefits include exceptional color rendering, high system efficacy, long lamp life, instant on/instant re-strike, and uniform APHL applications include retail, shopping malls, light industrial and recreational environments.


Vendor Code: **ETL**

Catalog Number	Description	Price Each
APHL654SNUPLL850	2' x 4', 6-54W T5H0 with 5,000K Lamps	193.56

Popular Fixtures Indicated in Bold.

120/208/240/277V

FLUORESCENT UNDERCABINET LIGHTS




Vendor Code: **ETL**

Catalog Number	Length	Number of Lamps	Lamp Type	Price Each
UC12T518LP41	12"	1	T5	30.00
UC18T8115LP41	18"	1	T8	38.98
UC24T8117LP41	24"	1	T8	39.00
UC36T8125LP41	36"	1	T8	60.45


Lighting & Lighting Controls

LED Products (Lay-Ins · Flat Panels · Strip Lights · Wrap Arounds)

LED LAY-INS
BLT SERIES

The BLT Series offers a clean design, shallow fixture-depth for easy installation, plug-n-play or wireless control options. An extensive selection of configurations and options make the BLT the perfect choice for many lighting applications including schools, offices and other commercial spaces, retail, hospitals and healthcare facilities. The low profile BLT design (2-3/8") also makes it an excellent choice for renovation projects.

GTL SERIES



The GTL Series LED recessed troffer's economical, solid-state lighting is ideal for new construction, renovation and retrofit opportunities. It is ideal for the broad range of applications where general-purpose fluorescent lighting currently prevails including offices, schools and commercial general-ambient applications.

Vendor Code: **LIT**

Catalog Number	Size	Watts	Lumens	LPW	Kelvin	Price Each
BLT SERIES						
2BLT233LADPLP840*	2' x 2'	30	3,313	111	4,000K	140.31
2BLT446LADPLP840*	2' x 4'	38	4,620	120	4,000K	196.79
GTL SERIES						
2GTL2120LP840	2' x 2'	18	2,223	124	4,000K	117.50
2GTL4120LP840	2' x 4'	29	3,980	137	4,000K	136.42

*BLT Series Catalog Numbers Listed Above are 4,000K (40). Replace 40 with 30 for 3,000K, 35 for 3,500K, and 50 for 5,000K.

LED FLAT PANELS



The EPANL is a visually stunning, low profile, easy to install luminaire. The fully luminous lens provides a glare free solution creating a very comfortable environment. With a depth of only two inches, restricted plenum space is no longer a concern. The EPANL is available in two lumen packages and three sizes with multiple configurations for a versatile solution that is DLC qualified (Standard and Premium) and eligible for utility rebates.

Vendor Code: **LIT**

Catalog Number	Size	Watts	Lumens	LPW	Kelvin	Price Each
EPANL2440L40K	2' x 4'	39	4,351	112	4,000K	110.99
EPANL2234L40K	2' x 2'	31	3,479	112	4,000K	100.87

LED STRIP LIGHTS
MNSL SERIES


The basic, non-dimming, damp location MNSL strip lights mount individually or in continuous rows to the ceiling or wall, both horizontally or vertically.

- Diffuse acrylic lens providing a single smooth line of light shaped to resemble a fluorescent tube
- Quick and simple to install with the snap-lock tool-less channel cover
- Ideal choice for commercial task lighting, restrooms, under/over cabinet, storage closets and displays


Vendor Code: **LIT**

Catalog Number	Size	Watts	Lumens	LPW	Kelvin	Price Each
MNSLL482LMV0LT4	4'	50	4,500	90	4,000K	64.25
MNSLL962LMV0LT4	8'	90	8,200	91	4,000K	133.09

LED WRAP AROUNDS



SBL Series



FMLWL Series

The SBL LED wrap around provides a digital lighting platform to deliver general ambient lighting for surface-mount applications. The LED system delivers long life and excellent color to ensure a quality, low-maintenance lighting installation. Ideal for closets, storage rooms, hallways, and offices.

The FMLWL Series LED Linear Flush Mount provides up to 50,000 hours of energy-saving LED lighting. Low-profile, linear fixture with decorative plastic end caps and white, acrylic diffuser for wide spread, uniform illumination.

Vendor Code: **LIT**

Catalog Number	Size	Watts	Lumens	LPW	Kelvin	Price Each
SBL SERIES						
SBL2LP840	2'	17	1,967	116	4,000K	140.47
SBL4LP840	4'	32	3,994	125	4,000K	128.54
FMLWL SERIES						
FMLWL24840**	2'	20	1,200	60	4,000K	90.96
FMLWL48840**	4'	40	2,380	60	4,000K	98.45

*Available in 3,000K and 4,000K

**Available in 2,700K, 3,000K, 3,500K, 4,000K

LED WET LOCATION VAPOR TIGHT XVML



These fully-gasketed, wet-location, and code-compliant vapor-tights are DLC® listed and IP65 and IP66 rated. They can be surface mounted on the ceiling or wall and are designed for continuous row mounting. The XVML vapor-tights are ideal for outdoor venues, canopies and locker rooms.


- The fully gasketed, polycarbonate housing with ten polycarbonate captive latches provides a water-tight seal and stands up to dust and dirt with its IP65 and IP66 ratings
- Provides the performance you need with the UV-stabilized, high-impact, frosted polycarbonate lens for uniform light output and high impact-resistance
- Quick and simple to install with the snap-lock tool-less access

Vendor Code: **LIT**

Catalog Number	Size	Watts	Lumens	Color	Price Each
XVMLL483500LMMV	4'	33	3,558	4,000K	124.59
XVMLL485000LMMVO	4'	49	5,000	4,000K	149.83

Also Available in 5,000K

LED SHOPLIGHT



The stylish LED Shoplight provides general illumination and is constructed of a metal housing with decorative end caps and a rocker switch for easy on/off operation. It is ideal for workshops, game rooms, utility rooms and garages.


- The white polycarbonate lens provides even illumination on surfaces where tasks are performed
- LEDs have a 35,000 hour L70 rated life
- Provides a cool color temperature of 4,000K with a CRI of 80
- Switch is located on the end

Vendor Code: **LIT**

Catalog Number	Size	Watts	Lumens	Color	Price Each
SHLP48IN40K80CRI	4'	36	3,200	4,000K	27.38



LED HIGH BAYS I-BEAM IBE SERIES



The right selection for your basic, affordable warehouse lighting - the I-BEAM® IBE LED luminaire gives budget-conscious customers a reliable LED solution featuring 6kV surge protection standard. The I-BEAM® IBE LED is designed to meet the challenges of warehouse and light industrial applications.


- Robust 6kV surge protection standard, meeting the ANSI standard for Industrial Environments
- UL listed to 45°C ambient with a thermal management system allowing for safe operation during times when temperatures rise up to 55°C*
- Save up to 60% in energy and maintenance costs over traditional sources
- Compact 2' housing

Vendor Code: **LIT**

Catalog Number	Watts	Lumens	Color	Price Each
IBE12LMMVOLT40K	83	12,000	4,000K	191.86
IBE18LMMVOLT40K	136	18,000	4,000K	259.47
IBE22LMMVOLT40K	165	22,000	4,000K	289.36

Catalog Numbers Listed are 4,000K (40). Replace 40 with 50 for 5,000K.

LED ROUND HIGH BAYS JEBL SERIES



The JEBL is built to last with 6kV surge protection standard, 55°C ambient temperature rating, and IP65 rated for elimination of dust, moisture and airborne contaminants. The unique, quick-connect driver-to-optical assembly interface allows for quick and easy maintenance for applications including warehousing, gymnasiums, manufacturing and outdoor canopies.

- Robust 6kV surge protection standard, meeting the ANSI standard for Industrial environments
- Mounting heights up to 30 feet. It is listed for wet locations and IP65 rated to help protect against dust, and airborne contaminants from indoor and outdoor environments
- The removeable quick-disconnect driver housing that allows for easy field replacement of the LED driver, eliminating the need to replace the entire fixture


Vendor Code: **LIT**

Catalog Number	Watts	Lumens	Color	Price Each
JEBL12L50K80CRIW	92	13,190	5,000K	195.18
JEBL18L50K80CRIW	136	19,770	5,000K	241.19
JEBL24L50K80CRIW	191	26,189	5,000K	298.37


Catalog Numbers Listed are 5,000K (50). Replace 50 with 40 for 4,000K.

Lighting & Lighting Controls

LED DOWNLIGHTS



Wafer LED



E Series

The 4" and 6" Wafer™ LED Downlight with Switchable White provides high-quality light output and efficiency featuring a switch for easy color temperature adjustment - while eliminating the need for recessed housings. The innovative, slim design allows for easy retrofit, remodel or new construction installation from below the ceiling. The Wafer LED downlight is wet location listed – making it ideal for use in a breadth of outdoor residential, hospitality, commercial and multifamily applications.


Combining dependable performance, low cost and the energy-saving benefits of as much as 35,000 hour-life LED, E Series LED recessed modules offer an optimal value for a variety of residential and light commercial applications. With 4" to 6" coverage available in multiple color temperatures, the cost and flexibility of E Series makes it the perfect LED option for high-volume projects and everyday stock business.

Vendor Code: **LIT**

Catalog Number	Size	Watts	Lumens	Kelvin	Price Each
WAFER LED					
WF4LED30K40K50K9*	4"	10	810	3,000K-5,000K	27.97
WF6LED30K40K50K9*	6"	13	1,190	3,000K-5,000K	31.90
E SERIES LED RECESSED MODULES					
4BEMWLED40K90CRI**	4"	10	720	4,000K	16.01
6SBEMWLED40K90CRI**	6"	12	845	4,000K	16.01

*Lumen Output Based on 4,000K Selection.
 **Catalog Numbers Listed are 4,000K (40). Replace 40 with 27 for 2,700K, 30 for 3,000K, and 50 for 5,000K.

LED UNDERCABINET LIGHTS



LED undercabinet lighting can be used as a source of task or accent lighting in new construction and retrofit applications. Smooth illumination lenses make the UCCEL ideal for use under and over cabinets, display cases, task lighting, office lighting, cover and utility/ work areas in commercial, retail, hospitality and residential applications.

- Available in 12", 24" and 36" lengths.
- Produces 388 - 1,162 lumens.
- Features an on/off rocker switch

Vendor Code: **LIT**


Catalog Number	Size	Watts	Lumens	Kelvin	Price Each
UCEL12IN30K90	12"	6	385	3,000K	57.23
UCEL24IN30K90	24"	10	740	3,000K	86.15
UCEL36IN30K90	36"	15	1,160	3,000K	82.92
UCEL48IN30K90	48"	20	1,600	3,000K	152.08

Catalog Numbers Listed are 3,000K (30). Replace 30 with 35 for 3,500K, and 40 for 4,000K.

LED EMERGENCY LIGHTING



EU2LM12




EU2CM6

Vendor Code: **LIT**


Catalog Number	Description	Price Each
EU2LM12	Two .75W LED Heads	34.86
EU2CM6	Two 1W LED Heads, CA Certified	35.20

120/277V

LED EXIT LIGHTS



ECRLEDM6



EXRLEDELM6

Vendor Code: **LIT**

Catalog Number	Description	Price Each
ECRLEDM6	Dual Heads, Red Letters	75.29
ECBRLEDM6	Red Letters w/ Battery Backup	162.15

120/277V

LED VAPORPROOF FIXTURES



OLVTCMM6



OLVTWMM6

Vendor Code: **LIT**

Catalog Number	Watts	Lumens	Kelvin	Price Each
OLVTCMM6	15	600	4,000K	210.92
OLVTWMM6	15	600	4,000K	282.30


120/277V
 50,000 Hours



Lighting & Lighting Controls

LED Products (Wall Packs · Tall Packs · Flood Lights · Canopy Lights · Area Lights)

LED TRADITIONAL WALL PACKS



TWR1LEDAL050KMV




TWR2LEDAL050KMV0

Vendor Code: **LIT**

Catalog Number	Watts	Lumens	Color	HID Equivalent	Price Each
TWR1LEDAL050KMV	9-51	1,100-6,200	5,000K	70w-250w	157.99
TWR2LEDAL050KMV0	21-87	3,050-11,800	5,000K	150w-400w	305.38

Catalog Number Listed is 5,000K (50). Replace 50 with 40 for 4,000K.

LED TALL PACKS



TWSLEDP150KMV0LT

Vendor Code: **LIT**

Catalog Number	Watts	Lumens	Color	HID Equivalent	Price Each
TWSLEDP150KMV0LT	28	2,100	5,000K	100w	137.23

LED FLOOD LIGHTS



Knuckle Mounting




Slipfitter Mounting

Vendor Code: **LIT**


Catalog Number	Watts	Lumens	Color	Mounting	Price Each
OFL1LEDP150KMV	21	2,333	5,000K	Knuckle	179.99
OFL1LEDP250KMV0L	45	4,466	5,000K	Knuckle	233.33
OFL2LEDP250KMV0L	114	12,154	5,000K	Slipfitter	407.69
OFL2LEDP350KMV0L	151	16,261	5,000K	Slipfitter	423.08

Catalog Number Listed is 5,000K (50). Replace 50 with 40 for 4,000K

LED SECURITY FLOOD LIGHTS



OFL2RH40K120BZ



OFL2RH40K120M0BZ


Vendor Code: **LIT**

Catalog Number	Watts	Lumens	Color	Finish	Price Each
OFL2RH40K120BZ	25	2,160	4,000K	Bronze	95.60
OFL2RH40K120M0BZ	25	2,160	4,000K	Bronze	121.73

Replace BZ with WH for White Finish.

*Includes Motion Sensor

LED CANOPY




Vendor Code: **LIT**

Catalog Number	Watts	Lumens	Color	HID Equivalent	Price Each
CNYLEDP150KMV0LT	35	4,500	5,000K	150w	157.42

Catalog Number Listed is 5,000K (50). Replace 50 with 40 for 4,000K
Also Available with White Finish.

LED AREA LIGHT



TDD2LEDP150K120

Vendor Code: **LIT**

Catalog Number	Watts	Lumens	Color	HID Equivalent	Price Each
TDD2LEDP150K120	41	4,700	5,000k	175w	164.44


Catalog Number Listed is 5,000K (50). Replace 50 with 40 for 4,000K
Also Available with White Finish



Lighting & Lighting Controls

Fluorescent Products (Wrap Around Fixtures · Lensed Troffers · High Bays)

FLUORESCENT GENERAL-PURPOSE STRIP LIGHTS



TC232MV

Vendor Code: **LIT**


Catalog Number	Number of Lamps and Type	Length	Price Each
C232MV	2: F32T8	4'	66.54
C296T8MV	2: F96T8	8'	97.08
TC232MV	4: F32T8	8'	102.40

WIREGUARD

WGCUNNST	C & UN Series	4'	31.86
-----------------	---------------	----	-------

Lamps Not Included
Electronic, Instant Start Ballasts
Popular Fixtures Indicated in Bold.

FLUORESCENT SQUARE-BASKET WRAP AROUND FIXTURES




Vendor Code: **LIT**

Catalog Number	Number of Lamps and Type	Length	Price Each
SB232MV	2: F32T8	4'	80.92
SB432MV	4: F32T8	4'	128.90

Lamps Not Included
Electronic, Instant Start Ballasts
Popular Fixtures Indicated in Bold.

FLUORESCENT LENSED TROFFERS



GT2UMV

Vendor Code: **LIT**

Catalog Number	Number of Lamps and Type	Price Each
GT2MV	2: F32T8	98.00
GT3MV	3: F32T8	125.15
GT4MV	4: F32T8	136.46

Lamps Not Included
Electronic, Instant Start Ballasts

FLUORESCENT EMERGENCY BATTERY PACK



PSQ500QD

Factory - or field-installed inside or outside (field only) a fluorescent fixture to operate lamp(s) at an initial output of 10% to 95% of rated lamp lumens, providing optimum glare-free illumination for a minimum of 90 minutes upon interruption of normal power.

Vendor Code: **LIT**

Catalog Number	Description	Price Each
QUICK MOUNT BATTERY PACK		
PSQ500QDMV0LT	500 Lumen Output	192.76
PS1400QDM8	1,400 Lumen Output	290.54

FLUORESCENT HIGH BAYS



The IBZ fluorescent high bay is ideal for new construction and renovation projects. It is a one-for-one replacement of common metal halide high bay systems. The unique Cool Running Plus™ technology provides industry-leading, trouble-free operation in ambient temperatures up to 155°F (68°C). Applications include manufacturing, warehousing, commercial and industrial facilities. The IBZ fixture performs well at mounting heights from 15'-40'.

Vendor Code: **LIT**


Catalog Number	Description	Price Each
IBZ654L	2' x 4', 6-54W T5 Univ. with 4,100K Lamps	256.62

Electronic, Programmable Rapid Start Ballasts
Popular Fixtures Indicated in Bold.




Lighting & Lighting Controls

LED FLOODLIGHTS FFLED™



FFLED18

FFLED39



FXLED78/FXLED150
Trunnion Mount


FXLED78/FXLED150
Slipfitter Mount

Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Mount	Price Each
FFLED18	18	2,310	Swivel Arm	271.20
FFLED39	39	5,666	Swivel Arm	416.79
FXLED150SF	150	20,868	Slip Fitter	815.58
FXLED150T	150	20,868	Trunnion	786.03
FXLED300SF	300	45,171	Slip Fitter	1591.57
FXLED300T	300	45,171	Trunnion	1639.48


The Catalog Numbers Listed Above are 5,000K. Also Available in 3,000K and 4,000K.

LED SLIM FLOODLIGHTS X34



X3416L120

X3435L120




X3465L120

Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Mount	Price Each
X3416L120	15	1,600	Knuckle	51.58
X3435L120	35	3,500	Knuckle	90.83
X3465L120	64	6,500	Knuckle	142.39

The Catalog Numbers Listed Above are 5,000K. Also Available in 3,000K.

LED ECONOMY FLOODLIGHTS PIP™




Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Mount	Price Each
PIP15D10	15	2,091	Knuckle	120.66
PIP30D10	30	4,162	Knuckle	154.75
PIPX170SFD10	70	10,601	Slip Fitter	327.36
PIPX1100SFD10	100	15,839	Slip Fitter	397.55

Bronze Finish
The Catalog Numbers Listed Above are 5,000K. Also Available in 3,000K and 4,000K. 70w and 100w Also Available with Trunnion Mount.

LED AREA LIGHTS ALED™




- Replaces up to 400W MH
- For use in parking lots, roadways, pathways and general area lighting.
- Mounts to 4" square steel poles at 15-25'.

Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Distribution	Price Each
ALED2T105	105	13,213	Type II	1081.67
ALED3T150	150	16,839	Type III	1090.06
ALED4T150	150	18,464	Type IV	1090.06

The Catalog Numbers Listed Above are 5,000K. Also Available in 3,000K and 4,000K.

LED AREA LIGHTS YARDBLASTER



YBLED26


YBLED26ARM

Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Price Each
YBLED26	26	3,685	207.69
YBLED26ARM*	26	3,685	232.33

*Includes Arm Mount

POLE ACCESSORIES




Bull4

MCB

Vendor Code: **RAB**

Catalog Number	Description	Price Each
BULL2	Two Light Bullhorn, Bronze	253.30
BULL2W	Two Light Bullhorn, Galvanized Steel	280.14
BULL3	Three Light Bullhorn, Bronze	375.24
BULL4	Four Light Bullhorn, Bronze	1147.46
BWC12	Angle Bracket for Wood, Galvanized Steel	196.46
MCB	Curved Wall Mount Bracket, Bronze	139.53
MAB	Right Angle Wall Mount Bracket, Bronze	126.31

POLES




PS41125WT

PS41125D2

Vendor Code: **RAB**

Catalog Number	Shaft	Gauge	Height	Price Each
TENON TOP POLES				
PS41115WT	4"	11	15'	1198.72
PS41120WT	4"	11	20'	1373.95
PS41125WT	4"	11	25'	1744.32
PS40725WT	4"	7	25'	2033.58
PS50725WT	5"	7	25'	2759.86
PS50730WT	5"	7	30'	3303.46
DRILLED POLES				
PS41115D2	4"	11	15'	1198.72
PS41120D2	4"	11	20'	1373.95
PS41125D2	4"	11	25'	1977.30
PS40725D2	4"	7	25'	2262.05
PS50725D2	5"	7	25'	4320.99
PS50730D2	5"	7	30'	3303.46

LED HIGH BAYS
AEROBAY™




Vendor Code: **RAB**

Catalog Number	Watts	Lumens	LPW	Price Each
ARBAY290	90	11,812	134	187.72
ARBAY2125	125	17,462	136	221.81
ARBAY4175	175	23,960	136	285.99
ARBAY4260	260	36,224	137	393.75

White Finish
The Catalog Numbers Listed Above are 5,000K.
Add **N** to End of Catalog Number for 4,000K.

LED HIGH BAYS
HAYBAY™




Vendor Code: **RAB**

Catalog Number	Watts	Lumens	LPW	Price Each
HAYBAY150ND10	150	18,816	125	438.82
HAYBAY180ND10	180	21,242	118	461.23

White Finish
The Catalog Numbers Listed Above are 5,000K.
Also Available in 4,000K.

LED GARAGE LIGHTS




Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Color Temp.	Price Each
GLED52W*	52	4,975	5,100K	675.84
IVGT570L750ZU	69	7,000	5,000K	759.32

*White Color
Add **Y** to end of Catalog Number for 3,000K or **N** to End of Catalog Number for 4,000K.
For Catalog Number GLED52W, the Color Change Options are added before the letter

LED WALL PACKS
LPACK®



Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Color Temp.	Price Each
WPLED10	10	1,208	5,000K	235.39
WPLED18*	18	2,508	5,000K	353.52
WPLED26*	26	3,475	5,000K	423.05
WPLED104	104	13,129	5,000K	706.16

*WPLED Models 13, 18, and 26 Include Two Mounting Options: Surface Plate and Junction Box. The Catalog Numbers Listed Above are 5,000K.
Add **Y** to end of Catalog Number for 3,000K or **N** to End of Catalog Number for 4,000K.

Wattages	Can be Used as a Substitute for
18W	100-175W Metal Halide Wallpacks
26W	150 - 200W Metal Halide Wallpacks
52W	250W HID Wallpacks
104W	400W Metal Halide Wallpacks

LED WASHDOWNS
SHARK™




- SHARK™ is ideal for car washes, tunnels, stairwells and other hard-to-reach areas where relamping is difficult and costly.
- Two sizes and four power packages available: 50W (4 ft), 36W (4 ft), 25W (2 ft), 18W (2 ft)
- At up to 100 lm/W, SHARK provides an energy efficient replacement for fluorescent tubes, reducing energy consumption by over 40%.

Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Price Each
4' LENGTH			
SHARK450WD10	50	5,161	273.85
8' LENGTH			
SHARK8100WD10	100	13,429	476.64

Catalog Numbers Listed are 5,000K.
Also Available in 3,000K, 3,500 or 4,000K.

WALL PACKS
TRADITIONAL




Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Color Temp.	Price Each
WP1LED30	30	3,060	5,000K	189.99
WP2LED37	37	4,329	5,000K	218.65
WP3LED55	55	6,645	5,000K	339.02
WP3LED65	65	7,559	5,000K	399.20
WP3LED82	82	9,280	5,000K	514.11
WP3LED110	110	15,113	5,000K	539.62

Bronze Color
The Catalog Numbers Listed Above are 5,000K.
Add **Y** to End of Catalog Number for 3,000K or **N** to End of Catalog Number for 4,000K.

WALL PACKS
W34



Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Color Temp.	Price Each
W3430L	30	3,105	5,000K	117.82
W3455L	51	5,375	5,000K	135.15
W34150L	136	14,845	5,000K	344.44


The Catalog Numbers Listed Above are 5,000K.
Add **830** to End of Catalog Number for 3,000K.



Lighting & Lighting Controls



LED ECONOMY COMPACT FLOODS LESLIE



LES13Y

- Equivalent to 75W halogen BR30 wide flood
- Wide 6H x 6V distribution

LES2X13Y


- Equivalent to two 75W halogen BR30 wide floods
- Wide 6H x 6V distribution

Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Finish	Price Each
SINGLE HEAD				
LES13Y	13	1,169	Bronze*	77.32
DUAL HEADS				
LES2X13Y	26	2,090	Bronze*	179.66

Catalog Numbers Listed Above are 3,000K. Change **Y** to **N** for 4,000K, Remove **Y** for 5,000K. *For Black Finish Add **B** at End, for Verde Green Add **VG**, for White Add **W**.

LED COMPACT FLOODS LFLED




LFLED5A/LFLED8YA

Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Color Temp.	Price Each
LFLED5A	5	299	5,000K	117.98
LFLED5YA	8	511	3,000K	117.98

Bronze Finish


LED SPOTLIGHT



Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Price Each
HSLED13A	13	1,502	384.38

LED BULLET™ FLOODS



BULLET12A

- 12W LED equivalent to 75W BR30/halogen/wide flood
- Mount as an uplight or downlight on a RAB Mighty Post or junction box

HBLED13A

- 80% energy savings vs. PAR floods
- Mount on junction box or on RAB Mighty Post

BULLET2X12NA

- Two adjustable 12W LED floodlights
- Equivalent to 2x75W BR30/halogen/wide floods

SMSBULLET2X12NA


- Two adjustable 12W LED floodlights
- Sensor with 180° detection pattern at up to 30 ft.

Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Price Each
SINGLE HEAD			
BULLET12A	12	1,240	119.85
HBLED13A	13	1,799	346.35
DUAL HEADS (2 X 12W)			
BULLET2X12A	24	2,528	278.13
DUAL HEADS (2 X 12W) W/MOTION SENSOR			
SMSBULLET2X12NA	24	2,528	265.62

Bronze Finish


FLOODLIGHT KITS AND SENSORS



Vendor Code: **RAB**

Catalog Number	Description	Price Each
FLOODLIGHTKITSW/OCCUPANCYSENSOR		
LU300	300W, 120V, Bronze	51.53
LU300W	300W, 120V, White	51.53
SENSORS ONLY		
LS300	Sensor for LU300	46.10
LS300W	Sensor for LU300W	46.10

LED WRAP AROUNDS GUS




Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Color Temp.	Price Each
2' LENGTH				
GUS225NWD10	25	2,757	4,000K	156.55
4' LENGTH				
GUS450NWD10	45	5,456	4,000K	177.60

The Catalog Numbers Listed Above are 4,000K. 3,000K, and 3,500K are Also Available.


LED VAPORPROOF FIXTURES



Vendor Code: **RAB**

Catalog Number	Watts	Lumens	Price Each
VXLED13DG	13	729	259.59
VXLED26DG	26	2,004	362.50

MIGHTY POSTS



Vendor Code: **RAB**

Catalog Number	Description	Price Each
MP19B	19" Black Mounting Post	52.82



Lighting & Lighting Controls

LED A-LINE LAMPS




Vendor Code: **RAB**

Catalog Number	Watts	Color	Lumens	CRI	Price Each
DIMMABLE					
A196E26930DIM	6	3,000k	450	90	4.51
A199E26930DIM	9	3,000k	800	90	4.95
A1913E26830DIM	13	3,000k	1,100	80	5.48
NON-DIMMABLE					
A196E26830ND	6	3,000k	480	80	2.65
A199E26830ND	9	3,000k	800	80	2.62

Catalog Numbers Listed are 3,000k (30). Replace 30 with 27 for 2,700k or 50 for 5,000k.

LED REFLECTOR LAMPS



Vendor Code: **RAB**

Catalog Number	Watts	Color	Lumens	CRI	Price Each
R20					
R207830DIM	7	3,000k	525	80	6.80
BR30					
BR3010930DIM	10	3,000k	700	90	9.49
BR40					
BR4011930DIM	11	3,000k	900	90	10.52

Catalog Numbers Listed are 3,000k (30). Replace 30 with 27 for 2,700k, 40 for 4,000k, or 50 for 5,000k.

LED PAR LAMPS




Vendor Code: **RAB**

Catalog Number	Watts	Color	Lumens	CRI	Price Each
PAR20					
PAR20793040DDIM	7	3,000k	550	90	8.77
PAR30					
PAR30L1193035DDI	11	3,000k	900	90	9.14
PAR38					
PAR381583040DDIM	15	3,000k	1,050	80	14.19
PAR381583025DDIM	15	3,000k	1,050	80	14.19

Catalog Numbers Listed are 3,000k (30). Replace 30 with 27 for 2,700k, 40 for 4,000k, or 50 for 5,000k.

*40° Beam Angle
**25° Beam Angle

LED MR16 LAMPS




Vendor Code: **RAB**

Catalog Number	Watts	Color	Lumens	Beam Angle	Price Each
MR16683035DDIM	6.5	3,000k	450	35°	7.72
MR16993025DDIM	9	3,000k	565	25°	10.87
MR16993035DDIM	9	3,000k	565	35°	10.87

Catalog Numbers Listed are 3,000k (30). Replace 30 with 27 for 2,700k, 40 for 4,000k, or 50 for 5,000k.

LED DECORATIVE LAMPS




Vendor Code: **RAB**

Catalog Number	Watts	Color	Lumens	Base	Price Each
GLOBES					
G16.53E12927FC	3.8	2,700k	350	Candelabra	4.40
G253E26927FC	3.8	2,700k	350	Medium	4.16
STRAIGHT TIP B11					
B113E26927FC	3.3	2,700k	300	Medium	3.85
BENT TIP BA11					
BA115E12927FC	5.5	2,700k	500	Candelabra	4.23
EDISON					
ST193E26927FC	3.8	2,700k	350	Medium	3.73




Lighting & Lighting Controls

LAMP SOCKETS


 Vendor Code: **EWD**

Catalog Number	Description	Price per 100 pcs.
MEDIUM-BI-PIN, FLUORESCENT QUICKWIRE		
2509WB0X	White, Tall	317.58
2510WB0X	White, Short	326.18
SLIMLINE FLUORESCENT		
2507WB0X	Plunger End	610.37
2506WB0X	Fixed End	572.96
800 & 1500MA, 2 TERM (HO, SHO & VHO)		
2500WB0X	Fixed End	1066.41
2501WB0X	Plunger End	1121.55

STRIP CONVERSION KITS


 Vendor Code: **EPC**

Catalog Number	Converts To:	Price Each
14050	4 Lamp T8	22.96

*Lamps and Ballast Not Included.
Converts from 8" to 4".

PLASTIC FLUORESCENT TUBE GUARDS


 Vendor Code: **EPC**

Catalog Number	Description	Price per 100 pcs.
T12 TUBE GUARDS		
17060	4' Tube Guard	380.01
17090	8' Tube Guard	858.04
T8 TUBE GUARDS		
17000	4' Tube Guard	556.25
17030	8' Tube Guard	837.24

Includes Black Plastic End Caps

LAMP GUARDS



 Vendor Code: **EPC (Engineered Prod. Co. - EPCO)**

Catalog Number	Description	Carton Quantity	Price per 100 pcs.
16100	Yellow Plastic	10	645.35

 Vendor Code: **EWD (Eaton Wiring Devices)**

Catalog Number	Description	Carton Quantity	Price per 100 pcs.
469BB0X	Wire Guard	60	18.57

LIGHT RECEPTACLES


 Vendor Code: **EPC**

Catalog Number	Description	Price per 100 pcs.
16502	Porcelain Lamp Holder: Pull Chain	665.46
16500	Porcelain Lamp Holder: Keyless	427.30
16512	Plastic Lamp Holder: Pull Chain	712.00
16510	Plastic Lamp Holder: Keyless	394.00

	Price Each	
16531	LED GU24: Keyless	29.33

Popular Fixtures Indicated in Bold.

TEMPORARY LIGHTING STRING


 Vendor Code: **COR**


Catalog Number	Description	Price Each
7145SW	14/2, 100' String	118.53

BUTTON SWITCH


 Vendor Code: **LCP**

Catalog Number	Description	Price Each
8410K1	Closest Door Switch	8.86

SOCKETS


 Vendor Code: **EWD (Eaton Wiring Devices)**

Catalog Number	Description	Ctn. Qty.	Price Each
MEDIUM BASE			
969B0X	Porcelain	25	8.33
610B0X	Porcelain Sign Receptacle	25	5.49
145B0X	Weatherproof Rubber	25	6.22
SOCKET ADAPTERS			
1054B0X	Socket Extension	25	8.83
332B0X	Mogul to Medium	25	7.58

 Vendor Code: **PAS (Pass and Seymour Legrand)**

Catalog Number	Description	Ctn. Qty.	Price per 100 pcs.
43308	Temporary Lighting Device	25	588.80

GENERAL DUTY TOGGLE SWITCHES


 Vendor Code: **CHC**

Catalog Number	Amps	Poles	Position Types	Throw Type	Price Each
E10T115AS	15	Single	On/Off	Single	8.97
E10T106DS	6	Single	On/Off/On	Double	11.45
E10T115DS	15	Single	On/Off/On	Double	11.04
E10T106ES	6	Single	On/On	Double	12.56
E10T215DS	15	Double	On/Off/On	Double	12.71
E10T215ES	15	Double	On/On	Double	10.59

LED REPLACEMENT TUBES
BALLAST COMPATIBLE



T8



U BEND T8

Vendor Code: GEL

Catalog Number	Watts	Size	Lumens	Kelvin	Rated Life (h)	Price Each
GLASS, ECONOMY LINEAR T8 (NON-DLC)						
LED15ET8840V6P	15	48"	1,800	4,000K	36,000	11.63
LED15ET8835V6P	15	48"	1,800	3,500K	36,000	11.63
LED15ET8850V6P	15	48"	1,800	5,000K	36,000	11.63
GLASS, LINEAR T8						
LED15ET8G4830	15	48"	1,800	3,000K	50,000	19.64
LED15ET8G4835	15	48"	1,800	3,500K	50,000	18.70
LED15ET8G4840	15	48"	1,800	4,000K	50,000	18.70
LED15ET8G4850	15	48"	1,800	5,000K	50,000	19.64
PLASTIC, U BEND T8						
LED13ET8U6835	13	22.5"	1,850	3,500K	50,000	32.45
LED13ET8U6840	13	22.5"	1,900	4,000K	50,000	31.65
LED13ET8U6850	13	22.5"	1,900	5,000K	50,000	32.45

80+ CRI

DOUBLE ENDED DIRECT WIRE 120-277V

Vendor Code: GEL

Catalog Number	Watts	Size	Lumens	Kelvin	Rated Life (h)	Price Each
LED14BDT8G4830	14	48"	1,700	3,000K	50,000	12.02
LED14BDT8G4835	14	48"	1,750	3,500K	50,000	12.02
LED14BDT8G4840	14	48"	1,800	4,000K	50,000	12.02
LED14BDT8G4850	14	48"	1,850	5,000K	50,000	12.02

LED PAR LAMPS



PAR30



PAR38

Vendor Code: GEL

Catalog Number	Watts	Lumens	Color	CRI	Rated Life (h)	Price Each
PAR30						
LED12DP30RW82740	12	1,000	2,700K	80	25,000	29.10
PAR 38						
LED18D380W383025	18	1,550	3,000K	81	25,000	27.02
LED18D380W383040	18	1,550	3,000K	81	25,000	27.02

LED A-LINE LAMPS



GE offers dimmable LED A-Line lamps as excellent replacements for standard 25-watt, 40-watt, 60-watt, 75-watt and 100-watt incandescent lamps.

- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent or halogen light sources.
- Dims from 100% to as low as 10%.
- Available with a CRI of 78 - 84.

Vendor Code: GEL

Catalog Number	Watts	Lumens	Color	CRI	Rated Life (h)	Price Each
A19 40W REPLACEMENT						
LED6DA19827	6	480	2,700K	80	15,000	7.42
A19 60W REPLACEMENT						
LED10DA19827	10	800	2,700K	80	15,000	8.74
A21 75W REPLACEMENT						
LED12DA21827	12	1,100	2,700K	80	15,000	10.23
A21 100W REPLACEMENT						
LED15DA21827	15	1,600	2,700K	80	15,000	14.07

Catalog Numbers Listed are 2,700K (27). Replace 27 with 30 for 3,000K, 40 for 4,000K and 50 for 5,000K.

LED REFLECTOR LAMPS



Vendor Code: GEL

Catalog Number	Watts	Lumens	Color	CRI	Rated Life (h)	Price Each
R20						
LED7DR20827	7	470	2,700	80	25,000	7.67
BR30						
LED10DR303827W	10	700	2,700	80	25,000	11.41
BR40						
LED13DBR40827	13	1,070	2,700	80	25,000	11.87

Catalog Numbers Listed are 2,700K (27). Replace 27 with 30 for 3,000K, 40 for 4,000K and 50 for 5,000K.



Genuine GE Lamps

Lighting & Lighting Controls



LED Lamps (Bright Stik™ · HID Replacements · CFL Plug-In Replacements · Decorative)

LED BRIGHT STIK™ BULBS



Vendor Code: **GEL**


Catalog Number	Watts	Lumens	Color	LPW	Typically Replaces	Price Each
LED9LS3827*	9	800	2,700K	89	60W	5.46
LED12LS2827**	12	1,100	2,700K	91	75W	11.03
LED15LS2827**	15	1,600	2,700K	107	100W	12.30

*Pack of Three

**Pack of Two

Other Color Temperatures are Available. Replace the Two Black Numbers with **27** for 2,700K, **28** for 2,850K, or **50** for 5,000K.

LED HID REPLACEMENT LAMPS



Vendor Code: **GEL**

Catalog Number	Watts	Lumens	Color	LPW	Typically Replaces	Price Each
BALLAST BYPASS 120-277V						
LED50ED23.5750	50	7,500	5,000K	150	100W	119.08
LED80ED23.5750	80	12,000	5,000K	150	175W	214.10
LED115ED28750	115	18,000	5,000K	156	250W	239.93
LED150ED28750	150	23,500	5,000K	140	400W	323.94
BALLAST BYPASS 277-480V						
LED270BT56750	270	40,000	5,000K	148	1,000W	592.72
LED450BT56750	450	65,000	5,000K	144	1,000W	623.94
BALLAST COMPATIBLE						
LED602M175750*	60	8,800	5,000K	147	175W	162.44
LED802M250750*	80	11,800	5,000K	148	250W	170.98
LED1302M400750*	130	18,500	5,000K	142	400W	209.99

Catalog Numbers Listed are 5,000K. Replace **50** with **40** for 4,000K.

Open or Enclosed Rated.

Fit ANSI Profile of Lamps Being Replaced.



Genuine GE Lamps

LED 4-PIN CFL REPLACEMENTS



Horizontal



Vertical

GE's LED plug-in lamps allow you to replace inefficient CFL 4 pin G24q/GX24 without tools or costly upgrades. Simply plug the replacement lamp into the existing ballast.

- Uses 50% less energy than CFL
- With LED CFL Replacements you can save over \$100 in energy costs vs. CFL over the rated life of the lamp (based on \$0.12 per kWh)
- 50,000 Hour Rated Life
- CFL could need replacement up to four times before you would have to replace a single LED Plug-In

Vendor Code: **GEL**

Catalog Number	Watts	Lumens	Color	LPW	Typically Replaces	Price Each
HORIZONTAL WITH ROTATABLE BASE						
LED9G24QH840*	9	1,200	4,000K	133	26W	23.56
LED19GX24QH840	18.5	1,950	4,000K	105	42W	33.87
VERTICAL						
LED9G24QV840*	9	1,200	4,000K	133	26W	17.03
LED19GX24QV840	18.5	1,950	4,000K	105	42W	23.31

Catalog Numbers Listed are 4,000K (**40**). Replace **40** with **27** for 2,700K, **30** for 3,000K, and **35** for 3,500K.

*G24q/GX24q Base

LED DECORATIVE LAMPS GLOBES



GE LEDs offer outstanding energy efficiency, long-lasting performance and just-right brightness, all in one package. They're dimmable and illuminate your home with soft, warm light.

- 15,000 Hour Rated Life
- Available with a CRI of 80

Vendor Code: **GEL**

Catalog Number	Watts	Lumens	Color	LPW	Typically Replaces	Price Each
LED5DG25W3827	5	350	2,700K	70	40	8.60
LED7DG25W3827	7	500	2,700K	71	60	10.22

Catalog Numbers Listed are 2,700K (**27**). Replace **27** with **30** for 3,000K, and **35** for 3,500K.

LED Lamps (Compact PAR20 · Dimmable Candle · Directional · Vintage/Filament Style)

LED COMPACT PAR20 LAMPS



For hard-to-reach downlight application fixtures, GE's dimmable 7-watt LED PAR20 lamp is the ideal solution.

- For example, using only 7 watts of energy, save over \$236 in energy costs over the life of the lamp versus a standard 35-watt halogen lamp based on \$0.11 per kWh.
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent or halogen light sources.

Vendor Code: **GEL**

Catalog Number	Watts	Lumens	Color	CRI	Beam Angle	Price Each
NARROW FLOOD						
LED7DP203B83020	50	520	3,000K	80	20°	17.36
FLOOD						
LED7DP203W83035	50	520	3,000K	80	35°	11.89

B=Black Casing
W=White Casing

Catalog Numbers Listed are 3,000K (30). Replace 30 with 27 for 2,700K. 25,000 Hour Rated Life

LED DIMMABLE CANDLE LAMPS



For any decorative lighting application, GE's LED dimmable candle lamps are the perfect solution and offer a multitude of wattage options.

- For example, using only 2.2 watts of energy, save over \$21 in energy costs over the rated life of a lamp versus a standard 15-watt incandescent lamp based on \$0.11 per kWh.
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources.

Vendor Code: **GEL**

Catalog Number	Base	Watts	Lumens	Color	CRI	Rated Life (h)	Price Each
40W INCANDESCENT EQUIVALENT							
LED4DCACC3827	Cand	4	300	2,700K	80	15,000	7.81
LED4DCAMC3827	Med	4	300	2,700K	80	15,000	7.81
60W INCANDESCENT EQUIVALENT							
LED7DCACC3827	Cand	7	500	2,700K	80	15,000	10.22
LED7DCAMC3827	Med	7	500	2,700K	80	15,000	10.22

Catalog Numbers Listed are 2,700K (27). Replace 27 with 50 for 5,000K.



Genuine GE Lamps

LED DIRECTIONAL LAMPS

MR16



LED7DMR1683015

For high-output in decorative lighting applications, GE's dimmable 7-watt LED MR16 lamp is the perfect solution.

- For example, using only 7 watts of energy, save over \$118 in energy costs over the rated life of a lamp versus a standard 50-watt halogen lamp based on \$0.11 per kWh.
- Energy efficiency and long life mean fewer lamp replacements versus halogen MR16/MRX16 light sources.
- Available in 15°, 25°, and 35° beam patterns

Vendor Code: **GEL**

Catalog Number	Watts	Lumens	Color	CRI	Beam Angle	Price Each
35W INCANDESCENT EQUIVALENT						
LED7DMR16S83015	7	460	3,000K	80	15°	15.54
50W INCANDESCENT EQUIVALENT						
LED7XDMRX1683025	7	520	3,000K	80	25°	17.97
LED7XDMRX1683035	7	520	3,000K	80	35°	17.97

25,000 Hour Rated Life

Catalog Numbers Listed are 3,000K (30). Replace 30 with 27 for 2,700K.

LED VINTAGE/FILAMENT STYLE



GE LED Vintage Style lamps combine the retro look of antique incandescent lamps with the benefits of LED. A warm, candlelight glow is provided by the LED filament, and the golden-tinted glass gives the lamp a vintage look. The long life and low energy of LED create savings on energy usage and maintenance costs versus incandescent.

- Common applications include pendants, sconces, chandeliers and other decorative fixtures.
- Perfect for creating an inviting atmosphere in restaurants and hotels, as well as adding vintage accents in retail and office locations.

Vendor Code: **GEL**

Catalog Number	Watts	Lumens	Color	Wattage Equivalent	Rated Life (h)	Price Each
LED3DST19V	3	200	2,500K	25W	15,000	9.97
LED3DCAMV120	3.5	300	2,500K	40W	15,000	9.97

Lighting & Lighting Controls



A-LINE LAMPS




Vendor Code: **GEL**

Catalog Number	Watts	Volts	Base	Color	Price Each
72AWH2PK120*	72	120	Medium	Soft White	13.44

Halogen Lamp

REFLECTOR LAMPS




Vendor Code: **GEL**

Catalog Number	Watts	Volts	Base	Shape	Price Each
45R20130VPR0130	45	130	Medium	R20	2.59
65BR30PR0130	65	130	Medium	BR30	2.90
65BR40FLPR0130	65	130	Medium	BR40	6.78

Popular Lamps Indicated in Bold

PAR LAMPS



Vendor Code: **GEL**

Catalog Number	Watts	Volts	Base	Type	Price Each
38PAR20HFL25	38	120	Medium	PAR20	9.58
38PAR30HFL25	38	120	Medium	PAR30	8.60
60PARH1500FL25TP	60	120	Medium	PAR38	12.10

Popular Lamps Indicated in Bold

NOTE: 130V lamps last 3 times as long as 120V lamps at the socket voltage.



Genuine GE Lamps

EXIT SIGN TUBULAR LAMPS



Vendor Code: **GEL**

Catalog Number	Watts	Volts	Base	Color	Price Each
25T6.5CLPR0	25	130	Intermediate	Clear	2.67

QUARTZ LAMPS



Vendor Code: **GEL**

Catalog Number	Watts	Volts	Length	Price Each
Q500T3CLPR0130	500	130	4-11/16"	3.71
Q1500T3CLPR0240	1,500	240	10-1/16"	9.76

Popular Lamps Indicated in Bold

APPLIANCE LAMPS



Vendor Code: **GEL**

Catalog Number	Watts	Volts	Base	Color	Price Each
40A15CLPR0130	40	130	Medium	Clear	0.96

Popular Lamps Indicated in Bold

HALOGEN PRECISE LAMPS




Vendor Code: **GEL**

Catalog Number	Watts	Volts	Type	Price Each
Q50MR16FL	50	12	Flood	3.67

Linear Fluorescent Lamps (T8 Tubes · T5 Tubes · U Shaped · T12 Tubes)

T8 TUBES




Vendor Code: **GEL**

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
RAPID START							
F17T8SP41EC0	17	24"	1,260	4,100K	78	24,000	8.21
F25T8SP41EC0	25	36"	1,970	4,100K	78	24,000	8.84
F32T8SPX41EC02	32	48"	2,925	4,100K	80	30,000	7.71

Rated Life at 12 Hour Cycles

Popular Lamps Indicated in Bold

T5 TUBES



Vendor Code: **GEL**


Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
HIGH OUTPUT							
F54WT5850EC0**	54	45.2"	4,600	5,000K	85	36,000	11.19

*Starter Required

**5/8" Diameter

Popular Lamps Indicated in Bold

U SHAPED FLUORESCENT LAMPS



Vendor Code: **GEL**


Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
T8 - 6" SPACING							
F32T8SPX41U62	32	22.5"	2,630	4,100K	82	20,000	18.62

Popular Lamps Indicated in Bold



Genuine GE Lamps

T12 TUBES




Vendor Code: **GEL**

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
RAPID START							
F34CWCWMEC0	34	48"	1,500	4,100K	87	15,000	3.63
F40DXEC0	40	48"	1,740	6,500K	90	20,000	7.66

*Starter Required

Popular Lamps Indicated in Bold

INSTANT START



Vendor Code: **GEL**

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
F96T12CWCWM	60	96"	2,900	4,100K	90	12,000	18.41

Popular Lamps Indicated in Bold

T12 HIGH OUTPUT



Vendor Code: **GEL**

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
F48T12CWHO	60	48"	3,520	4,100K	60	12,000	23.66
F72T12CWHO	85	72"	5,520	4,100K	60	12,000	23.83
F96T12CWHOCT*	110	96"	7,740	4,100K	60	12,000	27.28
F96T12HL41H0WM	95	96"	7,920	4,100K	77	12,000	41.62


Popular Lamps Indicated in Bold

*For Cold Temperature Use

Lighting & Lighting Controls



PULSE START METAL HALIDE LAMPS



Vendor Code: **GEL**

Catalog Number	Watts	Base	Bulb Descr.	Light Output Initial/Mean	Rated Life (h)	Price Each
MVR320VBUH0PA	320	Mog.	Clear	31,000/18,000	20,000	63.53
MVR400UPA	400	Mog.	Clear	38,000/22,000	18,000	59.41

Light Output and Rated Life Based On Base Up Installation
Popular Lamps Indicated in Bold

PROBE START METAL HALIDE LAMPS




- Probe start lamps used with pulse start ballasts will damage the lamp and ballast.

Vendor Code: **GEL**

Catalog Number	Watts	Base	Bulb Descr.	Light Output Initial/Mean	Rated Life (h)	Price Each
MVR175UMED	175	Med.	Clear	13,600/8,800*	10,000	42.59
MVR175U	175	Mog.	Clear	13,600/8,800*	10,000	40.90
MVR250U	250	Mog.	Clear	20,800/13,500*	10,000	44.23
MVR400U	400	Mog.	Clear	36,000/23,500*	20,000	30.17
MVR1000U	1,000	Mog.	Clear	110,000/88,000*	15,000	52.11
MVR1500USP0RTS	1,500	Mog.	Clear	170,000/153,000*	3,000	111.85

*Light Output and Rated Life Based on Base Up Installation
Popular Lamps Indicated in Bold

HIGH PRESSURE SODIUM LAMPS



Vendor Code: **GEL**

Catalog Number	Watts	Base	Bulb Descr.	Light Output Initial/Mean	Rated Life (h)	Price Each
LU1505HECO	150	Mog.	Clear	16,000/14,400	24,000+	31.63
LU250HECO	250	Mog.	Clear	28,000/27,000	24,000+	32.51
LU400HECO	400	Mog.	Clear	51,000/45,000	24,000+	47.39


Popular Lamps Indicated in Bold



Genuine GE Lamps

TRIPLE BIAX - 4 PIN

FOR DIMMING AND ELECTRONIC BALLAST



GX24Q-3




GX24Q-4

Vendor Code: **GEL**

Catalog Number	Watts	Length	Base	Lumens	Color	Rated Life (h)	Price Each
F32TBX841AECO	32	5.5"	G24Q-3	1,850	4,100K	12,000	20.84
F42TBX841AECO	42	6.4"	G24Q-4	2,690	4,100K	12,000	21.50

Popular Lamps Indicated in Bold

DOUBLE BIAX - 2 PIN WITH STARTER IN LAMP BASE FOR MAGNETIC BALLAST



G24D-3

Vendor Code: **GEL**

Catalog Number	Watts	Length	Base	Lumens	Color	Rated Life (h)	Price Each
F26DBX835ECO	26	6.67"	G24D-3	1,460	3,500K	10,000	19.83

DOUBLE BIAX 4 PIN FOR DIMMING AND ELECTRONIC BALLAST




G24Q-1

Vendor Code: **GEL**

Catalog Number	Watts	Length	Base	Lumens	Color	Rated Life (h)	Price Each
F13DBX841EC04P	13	4.9"	G24Q-1	755	4,100K	17,000/20,000	18.42

LED A-LINE LAMPS




Vendor Code: SYL

Catalog Number	Watts	Type	Color	Lumens	LPW	Rated Life (h)	Price Each
LED8.5A19FR5010Y	8.5	A19	5,000K	800	94	11,000	2.33
LED14A19FR5010YV	14	A19	5,000K	1,500	107	11,000	3.91

Non-Dimmable
Catalog Numbers Listed are 5,000K (50). Replace 50 with 27 for 2,700K, or 35 for 3,500K.

DIMMABLE LED A-LINE LAMPS



Vendor Code: SYL

Catalog Number	Watts	Type	Color	Lumens	LPW	Replaces	Price Each
LED9A19DIM0830UR	9	A19	3,000K	800	89	60W Incan.	2.84
LED16A21DIM0850	16	A21	5,000K	1,600	100	100W Incan.	6.97

Other Color Temperatures are Available. Replace the Two Black Numbers with 27 for 2,700K, 28 for 2,850K, or 50 for 5,000K.

LED T8 TUBES



Vendor Code: SYL

Catalog Number	Watts	Size	Color	Lumens	LPW	Rated Life (h)	Price Each
BALLAST COMPATIBLE							
LED17T8L48FGIS85	17	48"	5,000K	2,220	129	36,000	8.95
LED17T8L48FGIS84	18	48"	4,000K	2,220	129	36,000	8.95
120-277V (SINGLE OR DOUBLE ENDED)							
LED17T8L48850BF	17	48"	5,000K	2,220	129	50,000	13.61
LED17T8L48841BF	17	48"	4,100K	2,220	129	50,000	13.61

Frosted Glass
Other Color Temperatures are Available. Replace the Two Black Numbers with 30 for 3,000K, 35 for 3,500K, 41 for 4,100K or 50 for 5,000K.

SUBSTITUTE® LED T5HO LAMPS
REPLACEMENT FOR FLUORESCENT T5HO LAMPS




Vendor Code: SYL

Catalog Number	Watts	Size	Color	Lumens	LPW	Rated Life (h)	Price Each
LED25T5H0L48FG84	25	48"	4,000K	3,500	140	50,000	18.99

Frosted Glass
Other Color Temperatures are Available. Replace 5 with 3 for 3,000K, 35 for 3,500K, or 4 for 4,000K.

LED PAR LAMPS




Vendor Code: SYL

Catalog Number	Watts	Lumens	Color	CRI	Beam Spread	Rated Life (h)	Price Each
PAR 20							
LED6PAR20830FL45	6	425	3,000K	82	45°	11,000	3.56
PAR 30							
LED9PAR30LN830FL	9	650	3,000K	82	45°	11,000	5.93
PAR 38							
LED13PAR38830FL4	13	900	3,000K	82	45°	11,000	7.51

Medium Base
Non-Dimmable
PAR 38 also Available in 5,000K. Replace 30 with 50 for 5,000K.

DIMMABLE LED PAR LAMPS




Vendor Code: SYL

Catalog Number	Watts	Lumens	Color	CRI	Beam Spread	Replaces	Price Each
PAR 20							
LED7PAR20DIM830	7	525	3,000K	82	40°	50w Hal.	11.69
PAR 30							
LED12.5PAR30LN30	12.5	1,000	3,000K	91	40°	75w Hal.	15.90
PAR 38							
LED16PAR38DIM850	16	1,300	5,000K	82	40°	125w Hal.	13.64

Medium Base
Other Color Temperatures are Available. Replace the Two Black Numbers with 27 for 2,700K, 30 for 3,000K, or 50 for 5,000K.



DIMMABLE LED REFLECTOR LAMPS CONTRACTOR SERIES



Rated up to 11,000 hours at 70% lumen maintenance, Contractor Series LED reflector lamps offer years of service and reduce energy and maintenance costs. Contractor Series LED reflector lamps are environmentally preferred products. They are RoHS compliant and contain no mercury, lead or other hazardous materials. They emit no UV or IR radiation.


Vendor Code: **SYL**

Catalog Number	Watts	Lumens	Color	CRI	Rated Life (h)	Price Each
R20						
LED5R20DIM82710Y	5	325	2,700K	80	11,000	3.30
BR30						
LED9BR30DIM82710	9	650	2,700K	80	11,000	3.75
BR40						
LED13BR40DIM8271	13	900	2,700K	80	11,000	9.24

Medium Base

Catalog Numbers Listed are 2,700K (27). Replace 27 with 35 for 3,500K or 50 for 5,000K.

DIMMABLE LED MR16 LAMPS




Long lasting, energy efficient, ULTRA LED MR16 lamps are now true halogen equivalent lamps when comparing lumen output and center beam candlepower. MR16 lamps are available in 6, 8 and 9W versions in 25° and 35° beam angles and are high-quality replacements for halogen 20W-50W MR16 lamps. These LED MR16 lamps are available in GU5.3 base configurations and dimmable down to 10%. Lamps boast a 25,000 hours life (L70) providing 12.5 times longer life than halogen MR16 lamps thereby reducing maintenance costs. Lamps have a 3,000K color temperature similar to halogen and 80+ CRI. These products are free of UV and IR radiation, minimizing discoloration and fading of materials.

Vendor Code: **SYL**

Catalog Number	Watts	Lumens	Color	Beam Angle	Rated Life (h)	Price Each
LED6MR16DIM830F	6	450	3,000K	35°	25,000	5.89
LED6MR16DIM830NF	6	450	3,000K	25°	25,000	6.50



DIMMABLE LED FILAMENT LAMPS



B10 (Bent Tip)

G25

ST19

Rated up to 15,000 hours at 70% lumen maintenance, SYLVANIA ULTRA LED filament lamps offer years of service and reduce energy and maintenance costs. SYLVANIA ULTRA LED filament lamps are environmentally preferred products. They are RoHS compliant and contain no mercury, lead or other hazardous materials. They emit no UV or IR radiation. A CRI of 80 ensures good color definition and with warm white 2,700K color temperature, these lamps can be used in many applications in both homes and businesses.

Vendor Code: **SYL**


Catalog Number	Watts	Lumens	Color	CRI	Rated Life (h)	Price Each
LED5A15DIMCL927C	5	450	2,700K	90	15,000	5.18
LED5A19DIM0927CE	5	450	2,700K	90	15,000	5.40
LED4B10CBENTDIM9	4	320	2,700K	90	15,000	6.30
LED4.5G25CLDIM92	4.5	350	2,700K	90	15,000	7.78
LED5ST19DIM827CE	5	450	2,700K	90	15,000	7.18

*Medium Base Clear Finish

**Candelabra

Clear Finish

LED VINTAGE LAMPS



A19

ST19

Rated up to 15,000 hours at 70% lumen maintenance, SYLVANIA LED Vintage lamps offer years of service and reduce energy and maintenance costs. They are RoHS compliant and contain no mercury, lead or other hazardous materials.

Vendor Code: **SYL**


Catalog Number	Watts	Lumens	Color	CRI	Rated Life (h)	Price Each
LED6.5A19DIM822V	6.5	650	2,175k	80	15,000	7.87
LED6.5ST19DIM822	6.5	650	2,200K	80	15,000	4.75
LED4B10CBENTDIM8	4	360	2,175k	80	15,000	3.66

Amber Finish

Lighting & Lighting Controls

LED Lamps (High Lumen · U Shaped · T5 · Pin Base)

ULTRA LED™ HIGH LUMEN LAMPS



LEDHIDR5000850



LED80HIDR8000840

The SYLVANIA ULTRA LED high lumen lamp is a self-ballasted medium base HID replacement lamp. The lamp is easy to install and is ideal for indoor high/low bay lighting and outdoor decorative post top fixtures in walkway lighting applications. This lamp provides excellent color rendering (82 CRI) in comparison with traditional high pressure sodium and metal halide lamps, and a selection of color temperatures (2,700K, 3,000K, 4,000K and 5,000K). The optical design efficiently directs light output in a 360° (horizontal) beam angle (or omnidirectional) with Type V distribution.


Vendor Code: **SYL**

Catalog Number	Watts	Color	Lumens	LPW	Rated Life (h)	Price Each
LED HID REPLACEMENTS, E26 BASE						
LEDHIDR5000850*	55	5,000K	5,000	100	50,000	170.98
LED80HIDR8000840**	80	4,000K	8,000	100	50,000	233.98
LED HID REPLACEMENT ACCESSORY						
LEDADAPTORMOGULB	Mogul Base Adaptor for E26 Base					6.16

*Catalog Number Listed above is 5,000K (50). Replace 50 with 30 for 3,000K and 40 for 4,000K.

**Catalog Number Listed above is 4,000K (40). Replace 40 with 30 for 3,000K.

U SHAPED LED LAMPS
SUBSTITUBE® CURVALUME® IPS LED T8



SYLVANIA SubstiTUBE CURVALUME IPS LED T8 lamps are an energy saving alternative, designed to replace traditional fluorescent T8 lamps. These shatter-resistant LED T8 lamps contain no mercury, provide instant light and a uniform light distribution.

Engineered to operate on existing instant start and select programmed rapid start electronic T8 ballasts, these lamps minimize labor and recycling costs. Because the SubstiTUBE CURVALUME IPS LED T8 is not affected by switching cycles, the use of occupancy or vacancy sensors can be installed with the existing instant start ballasts for optimal energy savings.


Install a new QHE Instant start ballast with the SubstiTUBE CURVALUME IPS LED T8 lamp for optimal performance and to take advantage of the QUICK 72SUB+ System warranty.

Vendor Code: **SYL**

Catalog Number	Watts	Color	Lumens	LPW	Rated Life (h)	Price Each
6" LEG SPACE						
LED15T8UFP835SUB	15	3,500K	2,100	147	50,000	23.65

Catalog Number Listed Above is 3,500K (35). Replace 35 with 30 for 3,000K, 41 for 4,100K and 50 for 5,000K.

T5 LED LAMPS
SUBSTITUBE® DULUX® L LED




Energy efficient 50,000 hour LED T5 lamps providing instant light and a uniform light distribution with an optimized glass design. These lamps contain no mercury, provide instant light and a uniform light distribution. They are engineered to operate on existing instant start electronic DL40 ballasts.

Vendor Code: **SYL**


Catalog Number	Watts	Color Temp.	Lumens (Mean)	LPW	Rated Life (h)	Price Each
LED17T5DLFG841S	17	4,100K	2,200	130	50,000	25.20

Catalog Number Listed above is 4,100K (41). Replace 41 with 30 for 3,000K and 35 for 3,500K.
G211 Four Pin Base

PIN BASE LAMPS
SUBSTITUBE® DULUX® LED



GX24Q



GX23

SubstiTUBE DULUX LED Pin Base lamps are direct replacements for compact fluorescent lamps. They can be directly installed without the need to bypass the existing CFL ballast. The lamps are available in GX23 and G24Q/GX24Q bases and in magnetic or electronic ballast configurations.

The LED pin base lamps have all the features of your typical LEDs, such as low heat emission and high energy efficiency, and a long rated life of 50,000 hours.

Vendor Code: **SYL**

Catalog Number	Watts	Color	Lumens	LPW	Rated Life (h)	Price Each
VERTICAL						
LED9PBGX24QV841*	9	4,100K	900	100	50,000	13.17
HORIZONTAL						
LED9PBGX24QH841*	9	4,100K	900	100	50,000	20.46
LED9PBGX23H841**	9	4,100K	1,100	122	50,000	18.69

*GX24 Base

**GX23 Base


Catalog Number Listed above is 4,100K (41). Replace 41 with 35 for 3,500K for the part numbers: LED9PBGX24QV841 and LED9PBGX24QH841.
Replace 41 with 27 for 2,700K for the part number: LED9PBGX23H841.



Lighting & Lighting Controls

C

"A" LAMPS



Vendor Code: **SYL**

Catalog Number	Watts	Base	Color	Price Each
300MCL130V	300	Med	Clear	8.13
HALOGEN				
43AHALSSW4120V	43	Med	Soft White	3.19
72AHALSSW4120V	72	Med	Soft White	3.19

REFLECTOR LAMPS



Vendor Code: **SYL**

Catalog Number	Watts	Volts	Base	Shape	Price Each
45R20CVP130V	50	130	Med	R20	3.82
65BR30FLCVP130V	65	130	Med	BR30	3.56
65BRFL130V	65	130	Med	BR40	4.82
250BR401*	250	120	Med	BR40	10.02

*Infrared Heat Lamp

PAR LAMPS



Vendor Code: **SYL**

Catalog Number	Watts	Volts	Shape	Price Each
HALOGEN FLOODS WITH MEDIUM BASE				
39PAR20HALFL3013	39	130	PAR20	12.71
50PAR30HALSNFL25	50	120	PAR30	10.91
70PAR38HALSNFL25	70	120	PAR38	7.99

DECORATIVE LAMPS WITH A BENT TIP



Vendor Code: **SYL**

Catalog Number	Watts	Volts	Base	Color	Price Each
25B10CBL120V	25	120	Cand	Clear	1.39


HALOGEN LAMPS



Vendor Code: **SYL**

Catalog Number	Volts	Description	Beam Spread	Price Each
50MR16FL35CEXN	12	Reflector	35°	10.49

T8 RAPID START MEDIUM BI PIN G13



Vendor Code: **SYL**

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
F017741ECO	17	24"	1,170	4,100K	75	30,000	3.61
F025741ECO	25	36"	1,755	4,100K	75	30,000	3.99
F032V41ECO	32	48"	2,450	4,100K	90	22,500	4.02
F032865XPECO	32	48"	2,708	6,500K	85	40,000	5.70

Rated Life at 3 Hour Cycles

T5 HIGH OUTPUT RAPID START MINIATURE BI PIN G5



Vendor Code: **SYL**


Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
FP54841HOECO	54	45.8"	4,650	4,100K	82	20,000	5.91

RAPID START MEDIUM BI PIN G13

Vendor Code: **SYL**

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
F34CWXS	34	48"	1,656	4,100K	87	20,000	3.33


INSTANT START SINGLE PIN FA8



Vendor Code: **SYL**

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
F96T12CWX	75	96"	3,872	4,100K	87	12,000	14.50
F096841ECO	59	96"	5,428	4,100K	82	15,000	14.70

T12 HIGH OUTPUT RECESSED DOUBLE CONTACT R17D




Vendor Code: **SYL**

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
F48T12CWH0	60	48"	3,281	4,200K	60	12,000	10.64
F72T12CWH0	85	72"	5,063	4,200K	60	12,000	12.43
F96T12CWHOCOLD*	110	96"	6,966	4,200K	60	12,000	13.37

*For Cold Temperature Use

PULSE START METAL HALIDE



Vendor Code: SYL

Catalog Number	Watts	Base	Light Output Initial/Mean	Rated Life (h)	Price Each
CLEAR BULB					
MS320PSSBUHORED28	320	Mog.	32,000/21,000*	20,000	43.07

*Light Output and Rated Life Based on Vertical Installation

PULSE START METAL HALIDE FOR OPEN RATED FIXTURES




Vendor Code: SYL

Catalog Number	Watts	Base	Bulb Desc.	Light Output Initial/Mean	Rated Life (h)	Price Each
MP100UMED	100	Med.	Clear	7,600/4,900	15,000	32.90

*Light Output and Rated Life Based on Base Up Installation
Popular Lamps Indicated in Bold

PROBE START METAL HALIDE



Vendor Code: SYL

Catalog Number	Watts	Base	Bulb Desc.	Light Output Initial/Mean	Rated Life (h)	Price Each
M175UMED	175	Med.	Clear	*14,000/9,750*	10,000	24.55
M250UED28	250	Mog.	Clear	*21,500/17,500*	10,000	28.50
M400UED37	400	Mog.	Clear	*36,000/28,800*	20,000	47.07
M400UED28	400	Mog.	Clear	*36,000/23,500*	20,000	38.92
M1000U	1,000	Mog.	Clear	*110,000/88,000*	12,000	51.27
M1000UBT37	1,000	Mog.	Clear	110,000/93,500	15,000	37.20

*Light Output and Rated Life Based on Base Up Installation
Popular Lamps Indicated in Bold

HIGH PRESSURE SODIUM




Vendor Code: SYL

Catalog Number	Watts	Base	Bulb Descr.	Light Output Initial/Mean	Rated Life (h)	Price Each
LU250ECO	250	Mog.	Clear	28,000/27,000	24,000+	33.27
LU400ECO	400	Mog.	Clear	51,000/45,000	24,000+	37.91

Popular Lamps Indicated in Bold

DOUBLE BIAx 2 PIN

WITH STARTER IN LAMP BASE FOR MAGNETIC BALLAST




G24D-3

Vendor Code: SYL

Catalog Number	Watts	Length	Base	Lumens	Color	Rated Life (h)	Price Each
CF26DD841ECO	26	6.8"	G24D-3	1,548	4,100K	10,000	6.63

U SHAPED FLUORESCENT LAMPS AND CIRCLINE



Vendor Code: SYL

Catalog Number	Watts	Length	Lumens	Color	CRI	Rated Life (h)	Price Each
T8 - 6" SPACING							
FB0327416ECO	32	22.5"	2,475	4,100K	75	20,000	17.56
T12 - 6" SPACING							
FB40CWx6	40	22.6"	1,806	4,100K	87	18,000	17.50

DOUBLE BIAx 4 PIN

FOR DIMMING AND ELECTRONIC BALLAST



G24Q-2



G24Q-3

Vendor Code: SYL

Catalog Number	Watts	Length	Base	Lumens	Color	Rated Life (h)	Price Each
CF18DDE835ECO	18	5.8"	G24Q-2	989	3,500K	12,000	6.39
CF26DDE835ECO	26	6.5"	G24Q-3	1,470	3,500K	12,000	6.39

Popular Lamps Indicated in Bold

TRIPLE BIAx 4 PIN

FOR DIMMING AND ELECTRONIC BALLAST



GX24Q-3




GX24Q-4

Vendor Code: SYL

Catalog Number	Watts	Length	Base	Lumens	Color	Rated Life (h)	Price Each
CF32DTEIN835ECO	32	5.6"	GX24Q-3	2,002	3,500K	16,000	7.67
CF42DTEIN841ECO	42	6.5"	GX24Q-4	2,670	4,100K	12,000	6.82

Popular Lamps Indicated in Bold

T5 COMPACT FLUORESCENT LAMPS



Vendor Code: SYL

Catalog Number	Watts	Length	Base	Lumens	Color	Rated Life (h)	Price Each
FT40DL841RSECO	40	22.4"	2G11	2,709	4,100K	15,000	9.34

Lighting & Lighting Controls



LED Lamps (Replacement Tubes · Sign Tubes · Tube Strip Fixtures)

LED REPLACEMENT TUBES DIRECT WIRE 120-277V



DirectDrive LED tubes eliminate the need for an external driver or ballast. For new construction installations, simply connect the 120-277V line voltage directly to the sockets. For retrofit installations, bypass the existing ballast by cutting the wires and connecting the 120-277V line voltage directly to the sockets. No ballast or driver is required.

- May be connected on one or each end.

Vendor Code: **KST**

Catalog Number	Watts	Color	Length	Lumens	Rated Life (h)	Price Each
SHATTERPROOF COATED GLASS - SINGLE OR DOUBLE-ENDED WIRING						
L7T824GC840DX2	7	4,000K	24"	950	50,000	10.90
L15T848GC840DX2G	15	4,000K	48"	1,900	50,000	10.09
PLASTIC - SINGLE ENDED WIRING						
LED36T896P850D**	36	5,000K	96"	4,000	50,000	50.08

*ETL Sanitation Listed NSF/ANSI Standard 2 - Food Equipment Catalog Numbers Listed are 4,000K (40). Replace 40 with 30 for 3,000K, 35 for 3,500K and 50 for 5,000K.

**Catalog Number Listed is 5,000K (50). Replace 50 with 40 for 4,000K.

BALLAST COMPATIBLE


- Compatible with Most Instant and Program Start Electronic T8 Ballasts, Check Ballast Compatibility List
- Direct Replacement for the Following Fluorescent Lamps: F32T8/32W, F32T8/30W, F32T8/28W, F32T8/25W

Vendor Code: **KST**

Catalog Number	Watts	Color	Length	Lumens	Rated Life (h)	Price Each
SHATTERPROOF COATED GLASS						
LED15T848GC840S	15	4,000K	48"	2,200	50,000	12.32

ETL Sanitation Listed NSF/ANSI Standard 2 - Food Equipment Catalog Numbers Listed are 4,000K (40). Replace 40 with 30 for 3,000K, 35 for 3,500K and 50 for 5,000K.

NON-SHUNTED TOMBSTONE HARNESSES



- Replacement for shunted sockets when using single ended direct wire tubes.

Vendor Code: **KST**


Catalog Number	Description	Price Each
KTS0CKETT8UT2W*	2-Lamp Wiring Harness for LED Tubes	7.17
KTS0CKETT8UT4W**	4-Lamp Wiring Harness for LED Tubes	9.97

*Includes (2) Pre-Wired Tall, Non-Shunted Sockets with Power Quick Disconnect

**Includes (4) Pre-Wired Tall, Non-Shunted Sockets with Power Quick Disconnect



SIGN HERO LED SIGN TUBES




A perfect solution for retrofits or new sign installations, as well as single or double sided sign needs. With revolutionary DirectDrive technology there's no need for an external driver or ballast, saving precious labor time and costs.

Vendor Code: **KST**


Catalog Number	Watts	Color	Length	Lumens	Rated Life	Price Each
360° DOUBLE SIDED TUBES						
LED21T848P2S865D	21	6,500K	48"	2,600	50,000	63.14
LED26T860P2S865D	26	6,500K	60"	3,250	50,000	82.29
LED31T872P2S865D	31	6,500K	72"	4,000	50,000	98.29
LED42T896P2S865D	42	6,500K	96"	5,300	50,000	128.14
LED52T8120P2S865	52	6,500K	120"	6,400	50,000	183.05
180° SINGLE SIDED TUBES						
LED11T848P1S865D	11	6,500K	48"	1,340	50,000	45.25
LED13T860P1S865D	13	6,500K	60"	1,625	50,000	63.98
LED16T872P1S865D	16	6,500K	72"	2,000	50,000	75.34
LED21T896P1S865D	21	6,500K	96"	2,650	50,000	98.29
LED26T8120P1S865	26	6,500K	120"	3,200	50,000	146.45

Catalog numbers listed are 6,500K (65). Replace 65 with 40 for 4,000K. Also Available 18", 24", 30", 36", 42", 64", 84", 109", 117".

LED T5 HO TUBES



L25.5T5H048GC8




L25T5H048GC850D

Vendor Code: **KST**

Catalog Number	Watts	Color	Length	Lumens	Rated Life (h)	Price Each
BALLAST COMPATIBLE						
LED25.5T5H048GC8	25.5	5,000K	48"	3,200	50,000	17.02
120-277V						
L25T5H048GC850DX	25	5,000K	48"	3,400	50,000	18.05

ETL Sanitation Listed NSF/ANSI Standard 2 - Food Equipment Available in 3,500K, 4,000K, and 5,000K

LED TUBE STRIP FIXTURES




Vendor Code: **KST**

Catalog Number	Description	Price Each
KTDDSL2EDT842L	4' 2-Lamp Configuration	29.08
KTDDSL2EDT884L	8' 4-Lamp Configuration	50.01

For use with 120-277V LED Tubes (22W Max per Lamp) Lamps not Included

LED HID Replacement Lamps · LED CFL Plug-In Replacement Lamps

LED HID REPLACEMENT LAMPS
DIRECT WIRE 120-277V



L18HIDE26850D

LED100HIDEX39850

Smart Port LED Sensors

• Smart Port LED sensors conveniently install in seconds via a standard 3.5mm AUX port connection. Simply insert the LED light sensor and adjust the settings quickly by hand. Even if you choose not to plug in a sensor, the light will operate as a regular lamp.

Vendor Code: **KST**


Catalog Number	Watts	Color	Typical Replacement	Lumens	Rated Life (h)	Price Each
BASE TYPE: E26 (MEDIUM)						
L18HIDE26850D	18	5,000K	70W	2,610	50,000	39.01
L27HIDE26850DG2	27	5,000K	100W	3,915	50,000	47.59
L36HIDE26850DG3*	36	5,000K	150W	5,400	50,000	55.08
L45HIDE26850DG3*	45	5,000K	175W	6,750	50,000	65.98
BASE TYPE: EX39 (MOGUL)						
L45HIDEX39850DG3*	45	5,000K	175W	6,750	50,000	65.98
L54HIDEX39850DG3*	54	5,000K	200/250W	8,100	50,000	70.28
L80HIDEX39850DG2*	80	5,000K	320W	12,000	50,000	110.69
L100HIDEX39850D2*	100	5,000K	400W	15,000	50,000	147.31

Catalog Number	Description	Price Each
KTSP1R112VAUX	PIR Motion Sensor	36.44
KTSPS112VAUX	Daylight Sensor	40.00
KTSMW112VAUX	Microwave Motion Sensor	40.68

*Accepts SmartPort Sensors.
Catalog Numbers for LED HID Replacement Lamps Listed are 5,000K (50). Replace 50 with 30 for 3,000K, and 40 for 4,000K.

EXPANDABLE LED HID
REPLACEMENT LAMPS

EX39 ROTATABLE BASE DIRECT WIRE 120-277V




Vendor Code: **KST**

Catalog Number	Watts	Color	Typical Replacement	Lumens	Rated Life (h)	Price Each
L27HIDHDX39850D	27	5,000K	100/150W	4,100	50,000	65.08
L45HIDHDX39850D	45	5,000K	175W	6,400	50,000	77.00
L63HIDHDX39850D	63	5,000K	250W	9,200	50,000	134.07
L80HIDHDX39850D	80	5,000K	250/320W	10,000	50,000	149.00
L110HIDHDX39850D	110	5,000K	400W	14,000	50,000	179.85

Catalog Numbers Listed are 5,000K (50). Replace 50 with 30 for 3,000K, and 40 for 4,000K.

LED PLL REPLACEMENT
DIRECT WIRE 120-277V




Vendor Code: **KST**

Catalog Number	Watts	Color	Length	Lumens	Base	Price Each
LED17PLL22G835D	17	3,500K	22"	2,200	2G11	14.21

Catalog Number Listed is 3,500K (35). Replace 35 with 40 for 4,000K or 50 for 5,000K.

VERTICAL LED HIGH BAY
REPLACEMENT LAMPS
DIRECT WIRE 120-277V




Vendor Code: **KST**

Catalog Number	Watts	Color	Typical Replacement	Lumens	Rated Life (h)	Price Each
L80HIDVEX39850D	80	5,000K	250W	9,600	50,000	153.70
L115HIDVEX39850D	115	5,000K	400W	15,700	50,000	186.65

Catalog Numbers Listed are 5,000K (50). Replace 50 with 30 for 3,000K and 40 for 4,000K.

LED CFL PLUG-IN REPLACEMENTS



LED94PV840S

LED62PH840D

Vendor Code: **KST**

Catalog Number	Watts	Color	Base	Lumens	Orientation	Price Each
BALLAST COMPATIBLE 4-PIN						
LED94PV840S	9	4,000K	G24q	1,000	Vertical	13.24
LED94PH840S	9	4,000K	G24q	1,000	Horizontal	13.24
DIRECT WIRE 120-277V 2-PIN						
LED62PH840D	6	4,000K	GX23	700	Horizontal	13.28
LED82PV840D	8	4,000K	G24d	1,000	Vertical	11.96
LED82PH840D	8	4,000K	G24d	1,000	Horizontal	11.96
LED82PEV840D	8	4,000K	G24d	1,000	Extended Vertical	10.70

Catalog Numbers Listed are 4,000K (40). Replace 40 with 27 for 2,700K, 30 for 3,000K, 35 for 3,500K and 50 for 5,000K.



Lighting & Lighting Controls

C

LED A-LINE LAMPS




Vendor Code: **KST**

Catalog Number	Watts	Color	Lumens	CRI	Price Each
DIMMABLE					
LED6A190930	6	3,000k	450	90	3.48
LED9A190930	9	3,000k	800	90	4.17
LED11A190830	11	3,000k	1,100	80	4.30
NON-DIMMABLE					
LED6A190830ND	6	3,000k	480	80	1.92
LED9A190830ND	9	3,000k	800	80	1.85
LUMEN ADJUSTABLE					
LED16A2108303W	6/8/16	3,000k	450/800/1,600	80	11.34

Catalog Numbers Listed are 3,000k (30). Replace 30 with 27 for 2,700k or 50 for 5,000k.

LED REFLECTOR LAMPS



Vendor Code: **KST**

Catalog Number	Watts	Color	Lumens	CRI	Price Each
R20					
LED7.5R20830	7	3,000k	525	80	3.21
BR30					
LED8BR30830G2	8	3,000k	650	80	3.36
BR40					
LED15BR40830	15	3,000k	1,300	80	7.58

Catalog Numbers Listed are 3,000k (30). Replace 30 with 27 for 2,700k or 50 for 5,000k.

LED PAR LAMPS




Vendor Code: **KST**

Catalog Number	Watts	Color	Lumens	CRI	Price Each
PAR20					
LED6PAR20F930	6	3,000k	500	90	8.07
PAR30					
LED9.5PAR30F930	9.5	3,000k	800	90	11.00
PAR38					
LED13PAR38F830*	13	3,000k	1,200	80	11.03
LED13PAR38NF830**	13	3,000k	1,250	80	11.03

Catalog Numbers Listed are 3,000k (30). Replace 30 with 27 for 2,700k, 40 for 4,000k or 50 for 5,000k.

*40° Beam Angle
**25° Beam Angle

LED MR16 LAMPS




Vendor Code: **KST**

Catalog Number	Watts	Color	Lumens	Beam Angle	Price Each
LED6MR16S830	6	3,000k	450	35°	4.64
LED7.5MR16NS930	7.5	3,000k	570	25°	9.53
LED7.5MR16S930	7.5	3,000k	570	35°	8.31

Catalog Numbers Listed are 3,000k (30). Replace 30 with 27 for 2,700k, 40 for 4,000k or 50 for 5,000k.

LED DECORATIVE LAMPS




Vendor Code: **KST**

Catalog Number	Watts	Color	Lumens	Base	Price Each
GLOBES					
LED45FG16E12930C	4.5	3,000k	350	Candlabra	3.72
LED55FG25E26930C	5.5	3,000k	500	Medium	4.65
STRAIGHT TIP B11					
LED4FB11E26927C	4	2,700k	350	Medium	3.44
BENT TIP CA11					
L5.5FCA11E12927C	5.5	2,700k	500	Candlabra	3.92
EDISON					
L4.5FT19E26822A	4.5	2,200k	350	Medium	5.16

Lighting & Lighting Controls



BLAZE™ 12V LED TAPE LIGHT




BLAZE Tape Light is a versatile, indirect, linear light that provides high-output, architectural-grade lighting at 80+ CRI. BLAZE is available in a wide range of color temperatures, from warm whites starting at 2,400K, to very cool white 6,300K, as well as red, green, and blue. BLAZE's high lumen output makes it ideal for task and display lighting, as well as an efficient ambient light when paired with an LED dimmer.

Vendor Code: **DIO**

Catalog Number	Watts per foot	Kelvin	Length	Lumens per foot	Price Each
DI12VBL308016	2.88	3,000K	16.4' Spool	286	263.33
DI12VBL278016	2.88	2,700K	16.4' Spool	293	243.08
DI12VBL3080100	2.88	3,000K	100' Spool	286	1255.83
DI12VBL2780100	2.88	2,700K	100' Spool	293	1159.23

Replace the Two Black Numbers with **24** for 2,400K, **27** for 2,700K, **30** for 3,000K, **33** for 3,300K, **35** for 3,500K, **38** for 3,800K, **42** for 4,200K, **44** for 4,400K, **50** for 5,000K, and **63** for 6,300K.

LED TAPE DRIVERS




OMNIDRIVE® Electronic Dimmable Drivers are our best-selling dimmable power supplies. They offer superior dimming performance for the widest range of dimming switches. The built-in electronic filter eliminates flicker and provides the smoothest dimming from 100% down to 10%. They offer superior dimming performance when paired with: TRIAC dimmer controls, magnetic low voltage (MLV), electronic low voltage (ELV) and incandescent/halogen dimmer switches, as well as 3/4/5-way and on/off switching.

Vendor Code: **DIO**

Catalog Number	Watts	Voltage	Dimensions	Price Each
ENVIRONMENT RATING: INDOOR				
DITD12V20W	20	12V DC	5.5 x 1.8 x 1.1 in.	117.77
DITD12V30W	30	12V DC	7 x 2.3 x 1.4 in.	136.10
DITD12V45W	45	12V DC	7 x 2.3 x 1.4 in.	149.39
ENVIRONMENT RATING: OUTDOOR/INDOOR				
DITD12V60W	60	12V DC	7.9 x 2.7 x 1.8 in.	174.13
DITD12V80W	80	12V DC	7.9 x 2.7 x 1.8 in.	197.05
DITD12V120W	120	12V DC	7.9 x 2.7 x 1.8 in.	241.50


CHROMAPATH® BUILDER CHANNELS FOR LED TAPE

Vendor Code: **DIO**

Catalog Number	Form Factor	Length	Finish	Included Accessories	Price Each
DICPCHASL48	Slim	48"	Aluminum	No	21.54
DICPCHASQ48	Square	48"	Aluminum	Yes*	40.33
DICPCHA4548	45°	48"	Aluminum	Yes*	50.41


*Includes Four Mounting Clips with Screws and Two End-to-End Interconnects.

CHANNEL COVERS

Vendor Code: **DIO**

Catalog Number	Form Factor	Length	Price Each
DICPCHCFR48	Frosted Cover	48"	11.00
DICPCHCPD48	Premium Diffusion	48"	17.54

CHANNEL END CAPS

Vendor Code: **DIO**


Catalog Number	Description	Price Each
DICPECSL	Gray Slim End Caps	1.78
DICPECSQ	Gray Square Endcaps	8.88
DICPECA5	Gray 45° End Caps	14.97

A Set of End Caps Includes Closed and Notched Open Cap That Can Accommodate Wire up to 18 AWG.

Catalog Numbers Listed Above are Gray.

Add **W** to the End of the Part Number for White or **B** to the End of the Part Number for Black.

CLICKTIGHT® PRO TAPE LIGHT CONNECTORS

Vendor Code: **DIO**


Catalog Number	Type	Dimensions	Price Each
DICKTPTW10*	Tape to Wire Connector	0.51 x 1.1 in.	48.47
DICKTPTT5**	Tape to Tape Connector	0.51 x 1.1 in.	26.67

*Includes 10 Connectors, 25 Spade Connectors and 10 Wire Fasteners w/ 10 Nails

**Includes 5 Connectors, 10 Tape Light Fasteners and 20 Screws



FLUORESCENT BALLASTS



ELECTRONIC BALLAST

Vendor Code: **ADV**

Catalog Number	Number of Lamps and Type	Price Each
120-277V		
ICN2P32N35I	1 or 2: F17T8, F25T8, F32T8, F40T8	23.34
ICN3P32N35I	2 or 3: F17T8, F25T8, F32T8, F40T8	27.18
ICN4P32N35I	3 or 4: F17T8, F25T8, F32T8	31.89
ICN2S40N35I	2: F34T12, F34T12U	38.72
ICN2P60N35I	1 or 2: F72T12, F96T12	47.54
ICN2S110SC35I	2: F48T12HD, F60T12HD	67.26

Popular Ballasts Indicated in Bold.

ELECTRONIC HIGH BAY BALLAST RATED AT 90C FOR HIGH TEMP APPLICATIONS

Vendor Code: **ADV**

Catalog Number	Number of Lamps and Type	Price Each
120-277V		
ICN2S5490CT35M	2: F54T5HO	73.28
ICN4S5490CTLSG35	4: F54T5HO	101.01

Blank Start
For Frequent Switching Applications Such as Occupancy Sensors, Programmed Start Ballasts Are Recommended and Require Non-Shorted Lamp Sockets.

ELECTRONIC BALLAST KIT FOR 4-PIN COMPACT FLUORESCENT LAMPS T4, 2D, T5 AND TT5

Vendor Code: **ADV**

Catalog Number	Number of Lamps and Type	Price Each
120-277V		
ICF2S26H1LDK	1 or 2: 26W CFL, 1: 28W CFL, 32W CFL, 42W CFL	46.04
ICF2S42M2LDK	2: 26W CFL, 28W CFL, 40W CFL, 42W CFL	55.63


SIGN

120V / 800MA, HO RAPID START

Vendor Code: **ADV**

Catalog Number	Number of Lamps	Min. - Max. Lamp Length	Price Each
ISB021612EI	1 - 2	2 - 16"	75.11
ISB104014EI	1 - 2	10 - 40"	171.48
ISB043214EI	1 - 4	4 - 32"	138.33
ISB084846EI	4 - 6	8 - 48"	179.88

HIGH INTENSITY DISCHARGE REPLACEMENT BALLASTS



HIGH PRESSURE SODIUM BALLAST

Vendor Code: **ADV**

Catalog Number	Lamp Watts	Lamp Type	Price Each
MULTI-TAP: 120/208/240/277V			
71A8172001D	150	S-55	220.52
5-TAP: 120/208/240/277/480V			
71A8453001D	400	S-51	346.19

Includes Core & Coil, Capacitor and Ignitor Where Required.

Popular Ballasts Indicated in Bold.

METAL HALIDE BALLAST

Vendor Code: **ADV**

Catalog Number	Lamp Watts	Lamp Type	Price Each
MULTI-TAP: 120/208/240/277V			
71A5390001D	100	M90 / M140	206.67
71A5570001D	175	M57 / H39	176.65
5-TAP: 120/208/240/277/480V			
71A5750001D	250	M58 / H37	225.78
71A6051001D	400	M59 / H33	180.23
71A6552001	1,000	M47 / H36	270.11
SINGLE TAP: 480V			
71A6742001	1,500	M48	344.65
MULTI-TAP: 120/208/240/277V			
71A6772001	1,500	M48	346.72

Includes Core & Coil and Capacitor.
Popular Ballasts Indicated in Bold.

PULSE START METAL HALIDE BALLAST

Vendor Code: **ADV**


Catalog Number	Lamp Watts	Lamp Type	Price Each
71A5792001D	250	M138 / M153	272.05
71A6092001D	400	M135 / M155	240.81

120/208/240/277V
Must Use Pulse Start Lamps.

ADVANCE

by @ignify

PROGRAMMABLE LED DRIVERS



Vendor Code: **ADV**

Catalog Number	Output Current	Output Voltage	Price Each
LAY-IN/LINEAR DRIVERS			
XI020C056V054BST	100-560	22-5-54	30.57
XI054C150V054BST	100-1500	22-5-54	47.44
XI075C200V054BST	100-2,000	27-54	37.17
OUTDOOR AND INDUSTRIAL DRIVERS			
XI055C180V054BSJ	100-1,800	18-54	64.01
XI095C275V054BSF	100-2,750	20-54	87.93
XI180C125V200BSF	100-1,250	70-210	87.17
COMMERCIAL DOWNLIGHTING DRIVERS			
XI036C100V054DSM	100-1,000	27-54	45.76

*Bolted Numbers Indicates Maximum Output Wattage

DESKTOP READER FOR PROGRAMMABLE DRIVERS



By using the desktop programming tool, trained associates are capable of quickly programming LED drivers equipped with SimpleSet technology. Ask your local sales representative about in store programming capabilities in your area.

Vendor Code: **ADV**

Catalog Number	Description	Price Each
LCN9620	LED Driver Programming Tool	754.69



Try QuickSelect Now!
Desktop Reader for Programmable Drivers

LED HID REPLACEMENTS




These LED corn lamps feature five extendable panels, capable of adjusting to three different light distribution options (360° beam angle, 270° beam angle, and a 180° beam angle)! These lamps are UL listed for damp locations and approved for use in totally enclosed fixtures.

Vendor Code: **SAT**

Catalog Number	Watts	Color	HID Equivalent	Lumens	Life	Price Each
S29751	40	5,000K	175W	5,200	50,000	77.08
S29752	60	5,000K	250W	7,800	50,000	92.67

These Lamps are Not for Use with Dimmers. Surge Protector Sold Separately.

SHOE BOX LAMP SERIES




These LED lamps a convenient and energy-efficient solution for replacing traditional high-pressure sodium and metal halide sources in enclosed shoe box parking lot area lighting fixtures.

Vendor Code: **SAT**

Catalog Number	Watts	Color	HID Equivalent	Lumens	Life	Price Each
S8932	80	5,000K	250W	10,000	50,000	162.59
S8938	110	5,000K	400W	14,000	50,000	178.78

LED FILAMENT LAMPS



S9876



S9923



S9255



S9872

If you are looking for the antique style and traditional incandescent look and feel with all the energy efficient benefits LED technology can provide, this is the bulb for you. The Satco LED Filament Lamps are the perfect vintage light bulb with an historically accurate and beautifully reproduced design.

Vendor Code: **SAT**

Catalog Number	Watts	Lumens	Color	Bulb	Base	Price Each
S29879	8	800	2,700K	A19	Medium	7.74
S29923	4	350	2,700K	CA11	Candelabra	5.12
S8613	3.5	350	2,700K	C11	Candelabra	5.69
S9569	4.5	450	2,700K	C11	Medium	6.57
S9564	6.5	810	2,700K	G25	Medium	7.33
S9872	2.5	200	2,700K	T6	Candelabra	4.95

LED PAR LAMPS



Vendor Code: **SAT**

Catalog Number	Lamp Type	Watts	Lumens	Color	Beam Spread	Price Each
S9405	PAR20	7	525	2,700K	40°	4.22
S9436	PAR30	13	1,000	3,000K	60°	7.38
S9454	PAR38	15	1,200	5,000K	60°	10.23

LED REFLECTOR LAMPS




Vendor Code: **SAT**

Catalog Number	Lamp Type	Watts	Lumens	Color	CRI	Rated Life	Price Each
S9631	BR20	6.5	525	3,000K	80	25,000	5.02
S9621	BR30	9.5	750	3,000K	80	25,000	5.19
S9635	BR40	11.5	940	3,000K	80	25,000	8.03

LED MINIATURE LAMPS



S9542



S9544


These lamps are silicon LED replacements for Halogen G4, G6.35, G9, GU5.3, MR11 and MR16 lamps. The light of these lamps is thrust upward. They are dimmable and have a 25,000 hour life. There is a silicon based sealant on the outer shell, so these lamps can be used in wet or damp applications like outdoor lighting!

Vendor Code: **SAT**

Catalog Number	Watts	Lumens	Color	Volts	Base	Price Each
S9542	1.6	200	3,000K	12	G4	9.21
S9544	3	300	3,000K	12	G6.35	11.50



120V DIMMERS




Ariadni Skylark Contour Diva Maestro

- C.L. dimmers are forward phase dimmers specifically designed for controlling dimmable LEDs, incandescent, and halogen bulbs.
- Alleviate dimmer interaction for smooth, flicker-free dimming
- No neutral required.
- All are 600W for incandescent or halogen lamps.

Vendor Code: **LUT**

Catalog Number	LED/ CFL	Type	Price Each
ARIADNI			
AYCL153PWH	150	Single Pole/3 Way	28.77
AYCL253PWH	250	Single Pole/3 Way	50.18
SKYLARK CONTOUR			
CTCL153PWH	150	Single Pole/3 Way	31.20
CTCL150HWH	150	Single Pole Only	30.26
DIVA			
DVCL153PWH	150	Single Pole/3 Way	34.20
DVCL253PWH	250	Single Pole/3 Way	81.69
MAESTRO			
MACL153MWH	150	Multi-Location	40.37
MARWH	Companion Dimmer for Multi-Location Application.		27.53

REVERSE PHASE DIMMERS



Diva Skylark Contour Nova T

- Reverse phase dimmers control dimmable LEDs and CFLs, as well as incandescent, halogen, and ELV loads.
- All are 500W for incandescent, halogen lamps, or ELV lamps.

Vendor Code: **LUT**

Catalog Number	LED/ CFL	Type	Price Each
DIVA			
DVRP253PWH	250	Single Pole/3-Way	111.76
SKYLARK CONTOUR			
CTRP253PWH	250	Single Pole/3-Way	71.95
NOVA T			
NTRP250WH	150	Single Pole	126.09

MAESTRO C.L. PRO DIMMER



MAPROWH

- Phase selectable – works in both forward or reverse phase dimming.
- Neutral optional.
- Load ratings: 250W of LED/CFL, 500W of Incandescent/Halogen/ELV, 400VA/300W of MLV

MKDWH


- Color Change Kits allow for changing the color of the actuating switch assembly of an existing MAPRO dimmer.

Vendor Code: **LUT**

Catalog Number	Description	Price Each
	120V, Phase Selectable Neutral Optional Dimmer	70.96
COLOR CHANGE KITS		
MKDWH	1 Piece Color Change Kit	8.21
MKDSWH	5 Piece Color Change Kit	24.61

Catalog Numbers Listed Above are White (WH). Replace WH with LA for Light Almond, or BL for Black.

0-10V DIMMERS




MSZ101WH DVSTVWH NTSTVDVWH

Lutron Maestro 0–10 V Dimmer Sensors are lighting controls with passive infrared sensors that automatically control the lights in an area. These sensors detect heat from occupants moving within an area to determine when the space is occupied. The Maestro 0–10 V Dimmer Sensor combines a Maestro 0–10 V Dimmer with an occupancy or vacancy Sensor.

Vendor Code: **LUT**

Catalog Number	Type	Price Each
120-277 OPERATING VOLTAGE		
MSZ101WH	Single Pole/Multi-Location	110.39
DVSTVWH	Single Pole/3 Way	92.57
NTSTVDVWH	Single Pole	131.74

FAN CONTROLS




Skylark Ariadni Diva

Vendor Code: **LUT**

Catalog Number	Amp	Type	Price Each
SKYLARK (SLIDE TO ON/OFF)			
SFSQFHW	1.5	3 Speed	25.77
SFS5EWH	5	Variable	43.14
ARIADNI (TOGGLE SWITCH)*			
AYFSQFHW	1.5	3 Speed	29.56
DIVA (DECORATOR SWITCH)*			
DVFSQFHW	1.5	3 Speed	40.78
SKYLARK CONTOUR FAN CONTROL			
CTFSQFHW	1.5	3 Speed	26.98

*For Single Ceiling Fan.

FAN & LIGHT CONTROLS




Maestro Diva

- UL Listed to control: LED, CFL, Incandescent, Halogen loads.
- No canopy module required
- No neutral wire required

Vendor Code: **LUT**

Catalog Number	Light Rating	Price Each
MAESTRO		
MACLLFQWH	250W Inc./Halogen or 75W LED/CFL	72.08
DIVA		
DVFSQLFHW	1A LED/CFL (switch only)	39.65

DUAL SLIDE



Skylark Ariadni

- All are 300W for incandescent lamps.


Vendor Code: **LUT**

Catalog Number	Amp	Type	Price Each
SKYLARK			
SZLFSQWH	1.5	3 Speed	39.30
SZLFWH	2.5	Variable	36.03
ARIADNI			
AY2LFSQWH	1.5	3 Speed	39.28

1.5A for 1 Fan Only
2.5 Amp for Multiple Fans



SENSORS OCCUPANCY/VACANCY



- Programmable Occupancy (Automatic ON/Automatic OFF) or Vacancy (Manual ON/Automatic OFF).
- Tamper-resistant lenses.
- Ambient light detection (set to learnable or fixed).
- Adjustable timeout settings.
- No Dip switches or dials.

Vendor Code: **LUT**

Catalog Number	Description	Type	Price Each
SINGLE CIRCUIT PIR			
MS0PS2WH	120V, 2A	Single Pole	25.87
MS0PS5MWH	120V, 5A Lighting, 3A (120V) Fan	3-Way/Multi-Location	45.38
MS0PS6M2UDVWH	120/277V 6A Lighting, 3A Fan Neutral Required	3-Way/Multi-Location	42.96
MS0PS6M2D2VWH	120/277V 6A Lighting, 3A Fan No Neutral	3-Way/Multi-Location	47.26
DUAL CIRCUIT PIR			
MS0PS6DDVWH	120/277V, 6A Lighting, 4.4A (120V) Fan Per Circuit	Single Pole	85.98
C.L. DIMMER SENSOR			
MSCL0P153MWH	120V, 600W Inc, 150W CFL/LED	3-Way/Multi-Location	49.62
0-10V DIMMER SENSOR			
MSZ101WH	120/277V, 8A Lighting, Neutral Optional	3-Way/Multi-Location	110.39
SINGLE CIRCUIT, DUAL TECH			
MSA102WH	120/277V, 6A Lighting, 4.4A (120V) Per Circuit, No Neutral	Single Pole	96.62
MSB102WH	120/277V, 6A Lighting, 4.4A (120V) Per Circuit, Neutral Required	3-Way/Multi-Location	96.62
DUAL CIRCUIT, DUAL TECH			
MSA202WH	120/277V, 6A Lighting, 4.4A (120V) Per Circuit, No Neutral	Single Pole	120.59
MSB202WH	120/277V, 6A Lighting, 4.4A (120V) Per Circuit, Neutral Required	3-Way/Multi-Location	120.59

Replace WH with IV for Ivory, AL for Almond, LA for Light Almond or BL for Black.

VIVE HUBS



Vive Hub



Power Supply



Flush-Mount Adapter


- Communicates with controls on a floor using Lutron wireless Clear Connect technology (range radius of 71 ft).
- Distributed system architecture.
- Wireless sensors and controls must be located within 60 ft. line of sight, or 30 ft., through walls, of the associated device.
- Supports timeclock events based on both sunrise and sunset or fixed time-of-day.
- Integrated multi-color LED provides feedback on what mode the hub is in.
- Contact Closure Inputs for integration with devices by others including devices for Title 24 Automatic Demand Response.

Vendor Code: **LUT**

Catalog Number	Description	Price Each
HJS0FM	Starter Hub, Flush-Mount Adapter and Power Supply	Contact
HJS1FM	Vive Hub, Flush-Mount Adapter and Power Supply	Elliott
HJS1SM	Vive Hub, Surface-Mount Adapter and Power Supply	Electric
HJS2FM	Premium Vive Hub, Flush-Mount Adapter and Power Supply	Supply
HJS2SM	Premium Vive Hub, Surface-Mount Adapter and Power Supply	Sales Rep

See the Chart for Summary of Code Requirements for Lighting Control on Page L23.

RADIO POWR SAVR™ WIRELESS SENSORS



Occupancy/Vacancy Sensor




Daylight Sensor

Vendor Code: **LUT**

Catalog Number	Description	Price Each
OCCUPANCY/VACANCY SENSORS		
LRF20CR2BPWH	Ceiling Mount, 360° Field-of-View	118.65
LRF20WLBPWH	Wall Mount, 180° Field-of-View	118.65
LRF20KLBPWH	Corner Mount, 90° Field-of-View	118.65
LRF20HLBPWH	Halfway	118.65
DAYLIGHT SENSOR		
LRF2DCRBWH	Ceiling Mounted	169.50

RF RECEPTACLES

Vendor Code: **LUT**

Catalog Number	Description	Price Each
WIRELESS		
CAR2S15STRWH	15A Split (Half Switching; Single Pole/Downstream), 120V	231.75
CAR2S15DTRWH	15A Duplex (Dual Switching; Single Pole/Downstream), 120V	161.07
CAR2S20STRWH	20A Split (Half Switching; Single Pole/Downstream), 120V	260.00
CAR2S20DTRWH	20A Split (Half Switching; Single Pole/Downstream), 120V	260.00




MAESTRO® WIRELESS PRODUCTS



Wallbox Dimmer



Wallbox Switch



Plug In Lamp Dimmer



Plug In Dimming Module

Vendor Code: **LUT**

Catalog Number	Description	Price Each
WALLBOX DIMMERS, SINGLE POLE/MULTI-LOCATION		
MRF260MWH	120V, 600W Incandescent/Halogen	74.46
MRF26MLVWH	120V, 600W Incandescent/Halogen, Magnetic Low Voltage	96.43
WALLBOX SWITCHES		
MRF26ANSWH	120V, 6 A Light or 3A Fan, Incandescent, Halogen, MLV, ELV, Non-Dim Fluorescent Ballasts, and General Purpose Fans	88.43
MRF28SDVWH	120V / 8A Light or 3A Fan or 1/10 HP Motor	125.00
PLUG IN LAMP DIMMER		
MRF23LDWH	300 W, Inc./Halogen for Table or Floor Lamps	145.83
PLUG IN DIMMING MODULE		
MRF23PD1WH	120V, 300W Incandescent/Halogen Plug-In Dimming/Switching Module, One Receptacle	96.43

Replace **WH** with **IV** for Ivory, **AL** for Almond, **LA** for Light Almond or **BL** for Black.


POWPAK® CONTROLS




Vendor Code: **LUT**

Catalog Number	Description	Price Each
POWPAK RELAY MODULE		
RMJS5RDVB	5A Relay	152.75
RMJS5RCC01DVB	5A Relay with One Contact Closure Output	126.92
RMJS16RDVB	16A Relay	175.25
RMJS16RCC01DVB	16A Relay with One Contact Closure Output	197.75
UL 924 RATED EMERGENCY WIRELESS CONTROLS		
RMJS16RDVBEM	Emergency Rated 16A Relay	243.00
RMJS8TNDVBEM	Emergency Rated 8A, 0-10V Dimmer	271.50
FCJSEC0EM	Emergency Rated Ecosystem Control Module	117.86
FCJS010EM	Emergency Rated 0-10V Control Module	117.86
POWPAK DIMMING MODULE		
RMJS8TDVB	8A 0-10V Controller-Connector	203.50
RMJS8TNDVB	8A 0-10V Controller-Flying Leads	203.50
RMJSEC03SZ	Single Zone Ecosystem/DALI Controller	203.50
POWPAK CONTACT CLOSURE OUTPUT MODULE		
RMJSCC0124B	One Contact Closure Output	106.07

SERENA® REMOTE CONTROLLED SHADES



Roller Style




Honeycomb Style

Serena automated shades are smart shades at an affordable price. Serena automated shades let you schedule your window shades to automatically raise at a set time every morning. You can close as well as open your shades with the press of a button.

- Shades install and operate without wires. You can mount them inside or outside the window frame.
- Shades feature industry-leading battery performance, and you can replace the batteries without taking down the shade.
- The cordless design provides a safer solution for homes with children or pets.
- Available in roller or insulating honeycomb styles, with a variety of headrail options.
- Choose from a wide selection of fabric colors and textures, as well as three opacities.
- Use the Smart Bridge and free Lutron App for convenient control from anywhere. You can also integrate shade control with other smart home solutions, including Amazon Alexa, Apple® HomeKit™, Google® Assistant, and more!

Starting at **\$350.00** for a 3' x 5' window, automated shades are more affordable than ever. Contact your local Elliott Electric Supply for more information

VIVE WIRELESS




Vive wireless is a revolutionary, modular wireless lighting control system for new and existing commercial buildings.



RA2 SELECT PRODUCTS



C•L Dimmer



Pico



Switch

When you choose RA2 Select, you're selecting a smart home system comprised of keypads, light controls, fan controls, temperature controls, appliance controls, and shades. RA2 Select was developed so you can choose the specific components you want in order to create the system that will best suit your lifestyle.

Vendor Code: **LUT**

Catalog Number	Description	Price Each
C•L DIMMER		
MSB102WH	120 V/ 600 W/ 150 W LED	96.62
PICO WIRELESS CONTROL		
PJ23BRLWHL01R	434 MHz, 4-button	28.27
SWITCH WITH NEUTRAL WIRE		
RRD8ANSWH*	120 V/ 8 A	188.00

*Replace **WH** with **BL** for Black, **IV** for Ivory, or **LA** for Light Almond.


ADDITIONAL SMART HOME TECHNOLOGY

	Apple® HomeKit™ The Smart Bridge contains Apple HomeKit technology, so you can use Siri® to control your lights and shades.
	Nest Protect smoke + CO alarm When smoke or CO is detected your lights will turn on and your shades will open automatically to help you find your way.
	IFTTT (If This Then That) Create IFTTT recipes, such as lowering your shades if it's sunny, or turning off lights if the Nest thermostat is set to "Away" mode
	Logitech Harmony Dim lights, lower shades, and start a movie with one button press on Logitech Harmony hub-based remote controls or from the Harmony app.
	XFINITY Home Control your lights from anywhere using the XFINITY Home app.
	Amazon Alexa Create just the right light using Alexa voice control. Ask Alexa to turn lights on, off, or dim them to your favorite level.
	Sonos Control your Sonos Home Sound System from a Pico remote control for audio or from scenes in the Lutron App.
	Google Assistant Get the lights with just your voice. Smart lighting control is now available through any Google Assistant-enabled device.




CASÉTA™ WIRELESS PRODUCTS

Adjusting lights and shades from a smart phone has never been easier, more reliable, or affordable. The Smart Bridge Pro works with Caséta™ Wireless dimmers and is compatible with Serena®, Triathlon®, and select styles of Sivoia® QS Wireless shades. Control lights and shades from anywhere so lights aren't left on or shades aren't left open while you're away. Schedule lights and shades to automatically adjust via the timeclock at set times of day. Integrate light and shade control with select security systems and AV remote controls



Dimmer



Kits with Dimmer, Pico Remote and Wallplate




Smart Bridge Kit



Pico Remote



Single Tabletop Pedestal



Double Tabletop Pedestal

Caséta Wireless provides peace of mind, comfort and convenience at the touch of a button. So whether you want your lights on, off, or somewhere in between, you can count on Caséta Wireless to deliver what you need.

Control your lights from anywhere

- Turn lights on from your car, purse, or pocket
- Dim lights for a movie
- Turn off lights from your bedside

Add comfort and enhance peace of mind

- Adjust lights for any activity
- Create just the right ambiance
- Turn lights on before you walk into your house

Install in minutes

- Ideal for existing or new homes
- No new wiring required
- Set up is easy

Vendor Code: **LUT**


Catalog Number	Description	Price Each
KITS		
PPKG1WWH	1 In-Wall Light Dimmer, 1 Pico Remote, 1 Wallplate	80.45
PJ2WALLWHL01	1 Pico Remote, 1 Wallplate Bracket, 1 Wallplate	43.74
PBDGPKG1W	1 Smart Bridge, 1 In-Wall Light Dimmer, 1 Pico Remote, 1 Wallplate	123.92
SMART BRIDGE AND SMART BRIDGE PRO		
LDG2WH	Smart Bridge with HomeKit Technology	105.65
LDGPR02WH	Smart BridgePRO with HomeKit Technology	189.18
PICO REMOTE AND ACCESSORIES		
PJ23BRLWHL01R	Remote Control	28.27
LPED1WH	LPED1WH Single Tabletop Pedestal	16.72
LPED2WH	Double Tabletop Pedestal	29.97
PIC0CARCLIP	Car Visor Clip	14.70
DIMMERS AND SWITCHES		
PD5NEWH	Dimmer ELV+	139.02
PD6ANSWH	In-Wall Neutral Switch	74.58
PDFSQNWH	120V Fan Speed Control	72.90
PD6WCLWH	120V In-Wall Light Dimmer	66.79

Replace **WH** with **IV** for Ivory, **LA** for Light Almond or **BL** for Black.

Lighting & Lighting Controls

Photocontrols

PHOTOCONTROLS FIXED POSITION MOUNT



Vendor Code: **TOR**

Catalog Number	Volts	Watts Tungsten	VA Ballast	VA LED	Price Each
KNOCKOUT MOUNT FIXED POSITION					
2000	120	2,000	1,800	600	31.57
2000Z	208	2,000	1,800	1,385	35.38

PHOTOCONTROLS PLUG-IN LOCKING MOUNT



- Ideal for roadway, area, parking, flood and security lighting.
- Works with all LED, CFL, induction, HPS and HID lighting fixtures.
- Long life components exceeding the 20 year long-life requirement.
- Life tested up to 10,000 on/off operations with 8 year warranty.
- Instant response, 2-5 second delay off and 510J MOV surge protection.
- Meets ANSI C136.10-2010, UL773, & CSA TIL A15.

Vendor Code: **TOR**

Catalog Number	Volts	Watts Tungsten	VA Ballast	VA LED	Price Each
5237UL	103-305	1,000	1,800	1,000	26.59


PHOTOCONTROL ACCESSORIES

Vendor Code: **TOR**

Catalog Number	Description	Price Each
2421	Receptacle, 120-480V, Color Coded #12 Leads, Plastic Housing, Lock Nut with 1/2" NPT), and Mounting Bracket.	45.23
5500	Turn Lock, 480V Max, 1,800W Tungsten, 1,800VA Ballast	14.86

Not UL or CSA Listed.

PHOTOCONTROLS STEM AND SWIVEL MOUNT



- Conformal coated cadmium sulphide photocell resists effects of moisture and airborne contaminants. Photocell responds to the light spectrum near to that of a human eye.
- Delay of up to two minutes to prevent false switching due to light from passing vehicles, lightning, etc.
- All Lexan® enclosures are impact and vandal resistant.
- Translucent Lexan Dome prolongs cell life by further screening out ultraviolet rays. Dome and base are ultrasonically welded for maximum strength.

Vendor Code: **TOR**

Catalog Number	Volts	Watts Tungsten	VA Ballast	VA LED	Price Each
2001	120	2,000	1,800	600	26.43
2002	208-277	3470-4620	2080-2770	1,385	38.88

PHOTOCONTROLS LED RATED



The ZTL Series Photocontrol is designed with enhanced ZERO-CROSS Switching Technology allowing it to withstand the high inrush currents commonly found in LED Luminaires.


- Ideal for roadway, area, parking, flood and security type lighting fixtures.
- Enhanced 510 Joule MOV surge device providing superior surge protection against unpredictable line voltage spikes.
- Circuit Board protection enhanced with conformal coating to protect against extreme weather elements and moisture.

Vendor Code: **TOR**

Catalog Number	Description	Price Each
ZTL124	105-305V, 1000W Tungsten, 1800VA Ballast, 8A LED	39.92

TORK

PHOTOCONTROLS STEM MOUNT




- Ideal for commercial and municipal lighting applications.
- Works with all 120 through 277VAC LED, CFL, induction, HPS and HID lighting fixtures.
- Extremely corrosion-resistant for coastal, ocean spray applications.
- Mounts in 1/2" conduit hole commonly found in gang and power distribution enclosures.
- Gasketed for weather protection.
- Meets ANSI/UL773A.

Vendor Code: **TOR**

Catalog Number	Volts	Watts Tungsten	VA Ballast	VA LED	Price Each
DIE CAST ZINC HOUSING AND BASE					
2129A	120/208-277V	2,000	1,800	600	59.29
DIE CAST ALUMINUM HOUSING AND BASE					
2119A	120/208-277V	2,000	1,800	600	22.91

PHOTOCONTROLS FLUSH MOUNT




- Conformal coated cadmium sulphide photocell resists effects of moisture and airborne contaminants. Photocell responds to the light spectrum near to that of a human eye.
- Delay of up to two minutes to prevent false switching due to light from passing vehicles, lightning, etc.
- Meets ANSI/UL773A.
- Control housing is weather-resistant molded Lexan® with ultrasonically welded seams.
- Flush mounting through .6875" hole in post lantern or lighting fixture, 3/8" NPT, stem 3/4" long. Gasket and nut supplied.

Vendor Code: **TOR**

Catalog Number	Volts	Watts Tungsten	VA Ballast	VA LED	Price Each
3000	120	2,000	1,800	600	22.08
3002	208-277	3470-4620	2080-2770	1,385	34.38

Lighting & Lighting Controls

DIGITAL TIME CLOCKS



- No reset after power failure
- Multipurpose 7 day, available in 1 and 2 channels
- Permanent schedule retention
- Super capacitor backup
- Multi-voltage input 120-277V AC
- Automatic daylight savings and leap year compensation
- Non-metallic, NEMA 3R enclosure
- Standard or Astronomic Programs (7 Day)
- 40 amp contacts

Vendor Code: TOR


Catalog Number	Switch Type	Amps	Channels	Price Each
24 HOUR / NEMA 3R, NON-METALLIC ENCLOSURE				
E101B	SPST	40	1	191.34
E103B	DPST	40	1	253.60
7 DAY / NEMA 3R, NON-METALLIC ENCLOSURE				
EWZ101	SPST	40	1	377.36
EWZ201C*	SPST	30	2	349.85

*Has an Option for 1 Channel DPST Operation

TIMERS
SPRING WOUND



A515MW




C515M

- Twist knob for time ON setting. Time ON lengths from 15 minutes to 12 hour vary by model.
- No adjustments. Just wire and go!
- No neutral required. Great for retrofit!
- 125/250/277 VAC

Vendor Code: TOR

Catalog Number	Switch Type	Length of Time	Price Each
WHITE FACE PLATE INCLUDED			
A515MW	SPDT	15 Minute Max	60.26
A530MW	SPDT	30 Minute Max	61.82
A560MW	SPDT	60 Minute Max	64.01
METAL-BRUSHED ALUMINUM COLOR			
C515M	SPDT	15 Minute Max	72.30
C530M	SPDT	30 Minute Max	73.78
C560M	SPDT	60 Minute Max	53.61

ELECTROMECHANICAL
TIME CLOCKS
24 HOUR



1101NC

- NEMA 3R/NEMA 1 housing
- Clear Lexan cover
- Auto on/off same time 7 days a week

Vendor Code: TOR

Catalog Number	Switch Type	Voltage	Price Each
NEMA 3R, NON-METALLIC ENCLOSURE / 40A			
1101BPC	SPST	120	105.85
1103BPC	DPST	120	58.82
1104BPC	DPST	208-277	71.97
SCREW-ON ON/OFF TRIPPERS			
P47	-	-	9.89

DIGITAL TIME SWITCH
ASTRO WALL TIMER




- Scheduling: 10 ON & OFF pairs of set points for individual programs on each day of the week. 11 day groups speed programming.
- Astronomic/Daylight Savings/Leap Year/Random Mode
- Both models can be used as a 3-way switch.
- Supercapacitor provides power outage backup

Vendor Code: TOR

Catalog Number	Input Supply (VAC)	Amps	Action	Price Each
7 DAY ASTRONOMICAL				
SS703Z	120/277	15	SPST	79.30

White Color


ELECTROMECHANICAL
TIME CLOCKS
24 HOUR WITH PULLOUT TABS



Vendor Code: TOR

Catalog Number	Switch Type	Voltage	Price Each
NEMA 1, METAL ENCLOSURE / 20A			
8001	SPDT	120V	359.46
8001U	SPDT	480V	290.05

7 DAY WITH SKIP-A-DAY



Vendor Code: TOR


Catalog Number	Switch Type	Voltage	Price Each
NEMA 1 METAL ENCLOSURE / 40A			
W400B	4PST	120	397.35

TORK

Lighting & Lighting Controls

C


PREMIUM FAN UNITS



QTXE080



QTXE150



QTX110HL

 Vendor Code: **BRO**

Catalog Number	Description	Price Each
QTXE080	80 CFM, 0.3 Sones, Energy Star	149.98
QTXE150	150 CFM, 1.4 Sones, Energy Star	271.65
QTX110HL*	110 CFM, 1.2 Sones w/ Heater, Light, and Nightlight	343.44

*Lamps for Light and Night Light Not Included with Fan

INTERMEDIATE FAN UNITS



AE50




AE80L

 Vendor Code: **BRO**

Catalog Number	Description	Price Each
AE50	50 CFM, 0.5 Sones, Energy Star	91.83
AE80B	80 CFM, 1.5 Sones, Energy Star	89.27
AE80	80 CFM, 0.8 Sones, Energy Star	142.73
AE80L	80 CFM, 0.8 Sones, Energy Star, LED Light	231.56
AE110	110 CFM, 1.0 Sones, Energy Star	135.40
AE110L	110 CFM, 1.0 Sones, Energy Star, LED Light	153.19

ECONOMY FAN UNITS



Fan/Light




Ceiling/Wall Mount Fan

 Vendor Code: **BRO**

Catalog Number	Description	Price Each
FAN/LIGHT		
678*	50 CFM, 2.5 Sones, 4" Duct, 100w Incan. Max	49.46
A70L*	70 CFM, 2.0 Sones, 4" Duct, 100w Incan. Max	94.61
CEILING MOUNT FAN ONLY		
A110	110CFM, 3.0 Sones, 4" Duct	100.41
CEILING/WALL MOUNT FAN		
688	50 CFM, 4.0 Sones, 3" Duct	27.45
HEATER/FAN		
658	70 CFM, 4.0 Sones, 4" Duct, 1300w Heater	173.87
HEATER/FAN/LIGHT		
655	170 CFM, 4.0 Sones, 4" Duct, 1300w Heater	130.42

*Lamps Not Included

RECESSED FAN/LIGHT WITH HIDDEN VENTILATION


 Vendor Code: **BRO**

Catalog Number	Description	Price Each
744*	70 CFM, 1.5 Sones, 75w Max	174.99

Accepts R30, BR30, PAR30, or PAR30LN

*Lamps Not Included

CHIMES AND CHIME KITS


 Vendor Code: **NUT**

Catalog Number	Description	Price Each
LA174WH*	Recessed Westminster Electronic Chime	135.95
BK110NBWH	Non-Lighted Button Kit: One 2-Note, White Door Chime Assembly	24.57
BK115LWH	Lighted Button Kit: One 2-Note, White Door Chime	32.08
BK125LWH	Lighted Button Kit: One 2-Note, White Door Chime, 2 Pushbuttons	33.63
C905	16V 10VA Transformer for Door Chime	32.53
C907	16V 13VA Transformer for Multiple Door Chimes	40.93

*Pushbutton Not Included

COMBINATION SWITCHES



66V or 66W



82W

 Vendor Code: **BRO**

Catalog Number	Description	Price Each
66V	120v, 20 Amp Multi-Function Wall Switch; Ivory	27.70
66W	120v, 20 Amp Multi-Function Wall Switch; White	27.70
82W	120v, Humidity Sensing Wall Control; White	65.40

UPGRADE KITS


 Vendor Code: **NUT**

Catalog Number	Description	Price Each
LED GRILLE UPGRADE		
FG500NS	LED Grille Upgrade Kit for Ventilation Fans	41.93
BATHROOM FAN UPGRADE KIT		
690	60 CFM Motor Upgrade w/Grille	49.72

SMOKE/CO ALARMS



SC9120B/SC9120LBL
9120B/9120LBL



SC0500B/SA511B



SA350B



FG250B

SC9120B

Hardwired ionization and CO combination alarm meets new construction requirements including an advanced electrochemical CO and ionization smoke sensing technologies and a ten year CO Sensor/End of Life signal.

SC9120LBL

Wire-in, 120V AC 60Hz single and/or multiple station smoke and CO alarm specifically designed for residential and institutional applications. This alarm features a 10 year battery backup. The battery drawer is shipped pre-locked so battery will not be discarded prematurely.

SC0500B

BRK Wireless Interconnect Alarms provide a cost effective solution when it comes to renovation and retrofit projects where interconnectability is a requirement. Easily interconnect between floors and new to existing construction wirelessly.

9120LBL

Features a dual ionization smoke sensing chamber, an 85Db horn and a "silence" feature. This alarm has a 10 year battery backup. The battery drawer is shipped pre-locked so battery will not be discarded prematurely. Under normal conditions you should not have to replace the battery for the life of the alarm.

SA350B

Provides full 10-years of protection. Sealed Tamper proof design eliminates removal of batteries for other uses and ensures operation over the life of the alarm.

FG250B

Basic battery operated smoke alarm perfect for use in existing multi-family applications.

SA511B

BRK Wireless Interconnect Alarms provide a cost effective solution when it comes to renovation and retrofit projects where interconnectability is a requirement. Easily interconnect between floors and new to existing construction wirelessly.

Vendor Code: **BRK**

Catalog Number	Description	Price Each
SC9120B*	120V Combo Smoke and CO w/ Battery Backup	50.61
SC9120LBL*	120V Combo Smoke and CO w/ 10 Year Extended Life	57.08
SC0500B**	Wireless Interconnect Combo Smoke and CO w/Voice	71.67
SMOKE ALARMS		
9120B*	120V AC with Battery Backup	15.58
9120LBL*	120V AC/DC Ionization Smoke Alarm with a 10 Year Lithium Battery Back-up.	27.19
SA350B	10 Year Sealed Tamper Proof Battery Powered	22.26
FG250B	9V Battery Smoke Alarm	10.24
SA511B**	Wireless Interconnect Smoke w/Voice	52.94

*Hardwired

**Requires Two AA Batteries

HEATERS



174




198

Vendor Code: **BR0**

Catalog Number	Description	Price Each
174	1,500W Wall Heater, 8-9/16" x 12-9/16" x 4"	235.77
198	4,000W Wall Heater, 17-3/4" X 21-5/8" X 3-3/4"	520.54


**CEILING HEATER
LOW PROFILE**



Vendor Code: **BR0**

Catalog Number	Volts	Watts	Amps	Price Each
157	120	1,250	10.7	181.00

INFRARED LAMP HEATERS



161




162

Vendor Code: **BR0**

Catalog Number	Description	Price Each
161	250W Bulb Heater without Vent	45.26
162	70 CFM Exhaust Single Bulb Heater Fan	86.29

Does Not Include Lamps

FLEXIBLE VINYL DUCTING



Vendor Code: **DTC**

Catalog Number	Description	Price Each
BH350W	3" x 50' Flex Vinyl Duct Hose	17.59
BH450W	4" x 50' Flex Vinyl Duct Hose	18.79

Lighting & Lighting Controls

C