

# Weatherproof Electrical Products



**TEDDICO** BWF  
ELECTRICAL PRODUCTS




## Corporate Statement

As Manufacturers of Outdoor Weatherproof Electrical Products, it is BWF/M. Stephens' goal to provide our Customers with quality products at competitive prices - backed by the highest level of commitment and service available in this industry.

We provide a broad range of electrical fittings and weatherproof products to the market, and are committed to total Customer satisfaction by meeting or exceeding expectations for quality, on-time delivery, and friendly, knowledgeable Customer service.

The vision of M. Stephens is to achieve this by being more responsive, more flexible, faster, easier and more profitable to do business with than our competitors. Every element of our on-going business strategies will be aimed at accomplishing this vision.



# Weatherproof Electrical Products



---

Outlet Boxes

Pages 2-7



---

Covers

Pages 8-21



---

Lampholders and Accessories

Pages 22-25



---

Garden Lighting

Pages 26-27



---

Vaportight

Pages 28-33



---

Conduit Bodies

Pages 34-41



---

Service Entrance Heads,  
Replacement Parts & Accessories

Pages 42-44

For over 50 years, BWF/M. Stephens has been a leader in the die casting industry. With the full line of outdoor weatherproof products, BWF/M. Stephens is committed to offering the high quality and customer service expected from the BWF/M. Stephens name.

## One Gang Weatherproof Outlet Boxes - Die Cast Metal

### BWF Product Benefits & Features

- Rugged, seamless, die-cast construction that prevents moisture entry
- Reinforced connector outlets provide a secure mechanical installation
- State of the art powder coat finish for maximum durability
- Closure plugs, ground screw and mounting lugs included
- Complete installation instructions included with each product

### Applications

- For use in branch circuit wiring in wet, damp or dry locations
- May be used as a weatherproof junction box, or as a housing for receptacles, switches and GFCI's



**B-5V**



**DB-5V**



**B5-2V**



### One Gang Outlet Box with 3 Threaded Outlets

4 9/16" x 2 13/16" x 2", closure plugs, ground screw and mounting lugs included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
B-5V	18021-6	18.3"	3-1/2"	Grey	20	11.6
B-5AV	18520-4	18.3"	3-1/2"	Bronze	20	11.6
B-5WV	18720-8	18.3"	3-1/2"	White	20	11.6
B-75V	18031-5	18.3"	3-3/4"	Grey	20	11.4
B-75AV	52886-5	18.3"	3-3/4"	Bronze	20	11.4
B-75WV	52885-8	18.3"	3-3/4"	White	20	11.4
B-100V	27100-6	18.3"	3-1"	Grey	20	11.2
<b>Blister Carded</b>						
1503-1	01503-7	18.3"	3-1/2"	Grey	6	3.9
1503AB-1	18523-5	18.3"	3-1/2"	Bronze	6	3.9
1503W-1	50000-7	18.3"	3-1/2"	White	6	3.9
1753-1	01753-6	18.3"	3-3/4"	Grey	6	3.9
1753AB-1	18533-4	18.3"	3-3/4"	Bronze	6	3.9
1753W-1	50005-2	18.3"	3-3/4"	White	6	3.9

### Deep, One Gang Outlet Box with 3 Threaded Outlets

4 9/16" x 2 13/16" x 2 5/8", closure plugs, ground screw and mounting lugs included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
DB-5V	38006-7	25.5	3-1/2"	Grey	12	10
DB-75V	27105-1	25.5	3-3/4"	Grey	12	10
DB-100V	27108-2	25.5	3-1"	Grey	12	10

### One Gang Outlet Box with 4 Threaded Outlets

4 9/16" x 2 13/16" x 2", closure plugs, ground screw and mounting lugs included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
B5-2V	18041-4	18.3"	4-1/2"	Grey	20	12.1
B5-2AV	27111-2	18.3"	4-1/2"	Bronze	20	12.1
B5-2WV	18044-5	18.3"	4-1/2"	White	20	12.1
B75-2V	18051-3	18.3"	4-3/4"	Grey	20	12.1
B75-2AV	27113-6	18.3"	4-3/4"	Bronze	20	12.1
B75-2WV	27114-3	18.3"	4-3/4"	White	20	12.1
<b>Blister Carded</b>						
1504-1	01504-4	18.3"	4-1/2"	Grey	6	4.0
1504AB-1	18543-3	18.3"	4-1/2"	Bronze	6	4.0
1504W-1	50010-6	18.3"	4-1/2"	White	6	4.0
1754-1	01754-3	18.3"	4-3/4"	Grey	6	4.0
1754AB-1	18553-2	18.3"	4-3/4"	Bronze	6	4.0
1754W-1	50015-1	18.3"	4-3/4"	Bronze	6	4.0

## One Gang Outlet Box with 5 Threaded Outlets

4 9/16" x 2 13/16" x 2", closure plugs, ground screw and mounting lugs included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
B5-22V	18061-2	18.3"	5-1/2"	Grey	20	12
B5-22AV	27115-0	18.3"	5-1/2"	Bronze	20	12
B5-22WV	27116-7	18.3"	5-1/2"	White	20	12
B75-22V	18071-1	18.3"	5-3/4"	Grey	20	11.4
B75-22AV	27117-4	18.3"	5-3/4"	Bronze	20	11.4
B75-22WV	27118-1	18.3"	5-3/4"	White	20	11.4
B5-22XV	18081-0	18.3"	5-1/2" X	Grey	20	12
B75-22XV	27121-1	18.3"	5-3/4" X	Grey	20	12
B100-22XV	27124-2	18.3"	5-1" X	Grey	20	12



**B5-22V**

## Deep, One Gang Outlet Box with 5 Threaded Outlets

4 9/16" x 2 13/16" x 2 5/8", closure plugs, ground screw and mounting lugs included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
DB5-22XV	27127-3	25.0	5-1/2" X	Grey	12	10
DB75-22XV	27130-3	25.0	5-3/4" X	Grey	12	10
DB-100-22XV	27133-4	25.5	5-1" X	Grey	12	10



**DB5-22XV**

## Two Gang Weatherproof Outlet Boxes – Die Cast Metal

### BWF Product Benefits & Features

- Rugged, seamless, die-cast construction that prevents moisture entry
- Reinforced connector outlets provide a secure mechanical installation
- State of the art powder coat finish for maximum durability
- Closure plugs, ground screw and mounting lugs included
- Complete installation instructions included with each product

### Applications

- For use in branch circuit wiring in wet, damp or dry locations
- May be used as a weatherproof junction box, or as a housing for receptacles, switches and GFCI's

## Two Gang Outlet Box with 3 Threaded Outlets

4 9/16" x 4 5/8" x 2", closure plugs, ground screw and mounting lugs included

BWF#	Unit UPC TYPE0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TGB-5V	19000-0	31.0"	3-1/2"	Grey	12	13
TGB-75V	19016-1	31.0"	3-3/4"	Grey	12	13
TGB-100V	27147-1	31.0"	3-1"	Grey	12	13
TGB-100AV	27148-8	31.0"	3-1"	Bronze	12	13
TGB-100WV	27149-5	31.0"	3-1"	White	12	13
<b>Blister Carded</b>						
2503-1	02503-6	31.0"	3-1/2"	Grey	6	8
2503AB-1	19508-1	31.0"	3-1/2"	Bronze	6	8
2503W-1	50020-5	31.0"	3-1/2"	White	6	8




**TGB-5V**



## Two Gang Weatherproof Outlet Boxes – Die Cast Metal

### Two Gang Outlet Box with 4 Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2", closure plugs, ground screw and mounting lugs included



**TGB-54V**

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TGB-54V	19026-0	31.0"	4-1/2"	Grey	12	13
TGB75-4V	27152-5	31.0"	4-3/4"	Grey	12	13
<b>Blister Carded</b>						
2504-1	02504-3	31.0"	4-1/2"	Grey	6	7
2504AB-1	19527-2	31.0"	4-1/2"	Bronze	6	7
2504W-1	50025-0	31.0"	4-1/2"	White	6	7

### Two Gang Outlet Box with 5 Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2", closure plugs, ground screw and mounting lugs included



**TGB-55V**

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TGB-55V	19047-5	31.0"	5-1/2"	Grey	12	13
TGB75-5V	19056-7	31.0"	5-3/4"	Grey	12	13
TGB-55XV	27165-5	31.0"	5-1/2" X	Grey	12	13
TGB75-5XV	27168-6	31.0"	5-3/4" X	Grey	12	13
TGB100-5XV	27171-6	31.0"	5-1" X	Grey	12	13

### Deep, Two Gang Outlet Box with 5 Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2-5 / 8", closure plugs, ground screw and mounting lugs included



**DTB-5V**

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
DTB-5V	38028-9	36.0	5-1/2"	Grey	6	7
DTB-75V	27183-9	36.0	5-3/4"	Grey	6	7
DTB-100V	27186-0	36.0	5-1"	Grey	6	7

### Two Gang Outlet Box with 6 "X" Type Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2", closure plugs, ground screw and mounting lugs included



**TGB-56XV  
"X" Type**

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TGB-56XV	27174-7	31.0"	6-1/2" X	Grey	12	13
TGB75-6XV	27177-8	31.0"	6-3/4" X	Grey	12	13

### Two Gang Outlet Box with 7 Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2", closure plugs, ground screw and mounting lugs included



**DTB75-7XV**

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TGB-57V	27159-4	31.0	7-1/2"	Grey	12	13
TGB-77V	27162-4	31.0	7-3/4"	Grey	12	13

### Two Gang Outlet Box with 7 "X" Type Threaded Outlets

STD: 4-9 / 16" x 4-5 / 8" x 2",

DEEP: 4-9 / 16" x 4-5 / 8" x 2-5 / 8", closure plugs, ground screw & mounting lugs included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TGB-57XV	27178-5	31.0	7-1/2" X	Grey	12	13
TGB-77XV	27179-2	31.0	7-3/4" X	Grey	12	13
DTB75-7XV	27192-1	36.0	7-3/4" X, Deep	Grey	6	7
DTB100-7XV	27195-2	36.0	7-1" X, Deep	Grey	6	7

## Round Weatherproof Outlet Boxes – Die Cast Metal

### BWF Product Benefits & Features

- Rugged, seamless, die-cast construction that prevents moisture entry
- Reinforced connector outlets provide a secure mechanical installation
- State of the art powder coat finish for maximum durability
- Closure plugs, ground screw and mounting lugs included
- Complete installation instructions included with each product

### Applications

- For use in branch circuit wiring in wet, damp or dry locations
- May be used as a weatherproof junction box, or as a housing for receptacles, switches and GFCI's

### Round Outlet Box with 5 Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2", closure plugs, ground screw and mounting lugs included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
RB-5V	20066-2	16.5	5-1/2"	Grey	16	12
RB-5AV	20565-0	16.5	5-1/2"	Bronze	16	12
RB-5WV	20765-4	16.5	5-1/2"	White	16	12
RB-7V	27200-3	16.5	5-3/4"	Grey	16	12
<b>Blister Carded</b>						
3505-1	03505-9	16.5	5-1/2"	Grey	6	5
3505AB-1	20568-1	16.5	5-1/2"	Bronze	6	5
3505W-1	50030-4	16.5	5-1/2"	White	6	5



**RB-5V**



**RB-5CGV**

### Round Outlet Box with 5 Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2", cover, screws, closure plugs, ground screw, gasket & mounting lugs included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
RB-5CGV	27208-9	16.5	5-1/2"	Grey	16	12
RB-7CGV	27211-9	16.5	5-3/4"	Grey	16	12

## Extensions & Extension Adapters – Die Cast Metal

### One Gang Box Extension

4-9 / 16" x 2-13 / 16" x 1", gasket & mounting screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
EXR-1V	35007-7	10	1"	Grey	24	7
EXR-1WV	27137-2	10	1"	White	24	7
<b>Blister Carded</b>						
10XR-1	01013-1	65	1"	Grey	6	2
10XRAB-1	35503-4	65	1"	Bronze	6	2
10XRW-1	50165-3	65	1"	White	6	2



**EXR-1V**

### One Gang Box Extension Adapter – Flanged

5-1 / 4" x 3-1 / 2" x 1-1 / 2", closure plugs, mounting screws & gasket included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
EXF5-2V	35011-4	13.3	4-1/2"	Grey	12	7
EXF75-2V	27140-2	13.3	4-3/4"	Grey	12	8
EXF75-2WV	21742-6	13.3	4-3/4"	White	12	8
<b>Blister Carded</b>						
10XF-1	01011-7	76	4-1/2"	Grey	6	4
10XFAB-1	35513-3	76	4-1/2"	Bronze	6	4
10XFW-1	50170-7	76	4-1/2"	White	6	4



**EXF5-2V**



**EXR-2V**



**EX-5V**



**PB-50**

## Extensions & Extension Adapters –Die Cast Metal

### Two Gang Outlet Box Extension

4-9 / 16" x 4-5 / 8" x 1", gasket & mounting screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
EXR-2V	35008-4	16.3	1"	Grey	12	4
EXR-2AV	27198-3	16.3	1"	Bronze	12	4

### Round Outlet Box Extension with 4 Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2", closure plugs, mounting screws & gasket included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
EX-5V	35030-5	18.3	4-1/2"	Grey	18	10
EX-7V	27205-8	18.3	4-3/4"	Grey	18	10

## Swimming Pool Junction Boxes – Metal/Plastic

### Swimming Pool Junction Boxes with 3 Threaded Outlets

4-9 / 16" x 4-5 / 8" x 2", gasket included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Outlets	Color	Case Qty.	Case Weight
<b>Boxed</b>						
PB-50	26005-5	22	3-1/2"	Brass	10	15
PB-75	34010-8	22	3-3/4"	Brass	10	15
PB-100	34015-3	22	2-3/4"/1-1"	Brass	10	15


For use with installation of underwater pool lights.

For connecting to 120V or low voltage below normal water level of the pool.

Complies with the latest NEC, UL and CSA standards. Solid brass wiring platform with grounding post and 3 ground terminals - use with metallic or PVC conduit.


**NOTE:** To achieve watertight installation, reference is made to the 1999 National Electrical Code (NEC) Article 680-20(b)(2) which states "The end of the flexible-cord jacket and the flexible-cord conductor terminations within a fixture shall be covered with, or encapsulated in, a suitable potting compound to prevent the entry of water into the fixture through the cord or its conductors. In addition, the grounding connection within a fixture shall be similarly treated to protect such connection from the deteriorating effect of pool water in the event of water entry into the fixture." Article 680-21 Exception (a), which states "An approved potting compound is used to fill the box to prevent the entrance of moisture."

### Outside Dimensions



NPF Conduit Hub			
BWF#	A	B	C
PB-50	1/2"	1/2"	1/2"
PB-75	3/4"	3/4"	3/4"
PB-100	3/4"	1"	3/4"

### Outside Dimensions



Grounding Post for flexible cord ground wire

Grounding Post for attaching grounding conductor from feed wire

Use Hub "C" for entry of feed wiring


Use Hub "B" for entry of flexible cord from pool light

Compression Grounding Post for bonding wire (if required)


## One Gang Box & Extension Drawings

### Single Gang Boxes – Standard & Deep Dimensions and Cubic Inches

BWF#	Hub Size	A	B	C	D	E	F	G	H	J	Cubic Inches
B-5V	1/2"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	18.3"
B-75V	3/4"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	18.3"
B-100V	1"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	18.3"
DB-5V	1/2"	4-9/16"	2-13/16"	25/8"	3/4"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	23.8"
DB-75V	3/4"	4-9/16"	2-13/16"	25/8"	3/4"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	23.8"
DB-100V	1"	4-9/16"	2-13/16"	25/8"	3/4"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	23.8"
B5-2V	1/2"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	1-1/2"	18.3"
B75-2V	3/4"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	1-1/2"	18.3"
B5-22V	1/2"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	1-1/2"	18.3"
B75-22V	3/4"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	1-1/2"	18.3"
B5-22XV	1/2"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	18.3"
B75-22XV	3/4"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	18.3"
B100-22XV	1"	4-9/16"	2-13/16"	2"	5/8"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	18.3"
DB5-22XV	1/2"	4-9/16"	2-13/16"	2-5/8"	3/4"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	23.8"
DB75-22XV	3/4"	4-9/16"	2-13/16"	2-5/8"	3/4"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	23.8"
DB-100-22XV	1"	4-9/16"	2-13/16"	2-5/8"	3/4"	3-3/16"	3-1/2"	3-1/4"	1-7/8"	–	23.8"




Extensions and Extension Adapters are used to provide additional capacity needed for NEC box fill requirements. Adapters allow installer to add "take-offs" to new boxes and/or devices.




## Two Gang Box & Extension Drawings

### Two Gang Boxes – Standard & Deep Dimensions and Cubic Inches


BWF#	Hub Size	A	B	C	D	E	F	G	H	J	K	L	Cubic Inches
TGB-5V	1/2"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	–	–	3-1/4"	30.5"
TGB-75V	3/4"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	–	–	3-1/4"	30.5"
TGB-100V	1"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	–	–	3-1/4"	30.5"
TGB-54V	1/2"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	30.5"
TGB75-4V	3/4"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	30.5"
TGB-55V	1/2"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	30.5"
TGB75-5V	3/4"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	30.5"
TGB-55XV	1/2"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	–	–	3-1/4"	30.5"
TGB75-5XV	3/4"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	–	–	3-1/4"	30.5"
TGB100-5XV	1"	4-9/16"	4-5/8"	2"	5/8"	5"	3-7/8"	3-11/16"	3-3/4"	–	–	3-1/4"	30.5"
DTB-5V	1/2"	4-9/16"	4-5/8"	2-5/8"	3/4"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	40.3"
DTB-75V	3/4"	4-9/16"	4-5/8"	2-5/8"	3/4"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	40.3"
DTB-100V	1"	4-9/16"	4-5/8"	2-5/8"	3/4"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	40.3"
TGB-56XV	1/2"	4-9/16"	4-5/8"	2"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	30.5"	
TGB75-6XV	3/4"	4-9/16"	4-5/8"	2"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	30.5"	
TGB-57V	1/2"	4-9/16"	4-5/8"	2"	5"	3-7/8"	3-11/16"	3-3/4"	–	1-1/2"	3-1/4"	40.3"	
TGB-77V	3/4"	4-9/16"	4-5/8"	2"	5"	3-7/8"	3-11/16"	3-3/4"	–	1-1/2"	3-1/4"	40.3"	
DTB-57XV	1/2"	4-9/16"	4-5/8"	2-5/8"	3/4"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	40.3"
DTB75-7XV	3/4"	4-9/16"	4-5/8"	2-5/8"	3/4"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	40.3"
DTB100-7XV	1"	4-9/16"	4-5/8"	2-5/8"	3/4"	5"	3-7/8"	3-11/16"	3-3/4"	1-1/2"	–	3-1/4"	40.3"




Extensions and Extension Adapters are used to provide additional capacity needed for NEC box fill requirements. Adapters allow installer to add "take-offs" to new boxes and/or devices.



## Round Box & Extension Drawings



Extensions and Extension Adapters are used to provide additional capacity needed for NEC box fill requirements. Adapters allow installer to add "take-offs" to new boxes and/or devices.



## One Gang Weatherproof Blank Covers – Stamped Steel

### BWF Product Benefits & Features

- Rugged, seamless construction that prevents moisture entry
- State of the art powder coat finish for maximum durability
- Includes installation hardware, gasket and instructions

### Steel One Gang Blank Cover

4 9/16" x 2 13/16", stamped steel cover, gasket & screws included



BC-1V

BWF#	Unit UPC 0-87115	Outlets	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
BC-1V	29005-2		Blank	Grey	42	4
BC-1AV	29505-7		Blank	Bronze	42	4
BC-1WV	29705-1		Blank	White	42	4
<b>Blister Carded</b>						
711-1	00711-7		Blank	Grey	12	2
711AB-1	29509-5		Blank	Bronze	12	2
711W-1	50105-9		Blank	White	12	2




BC-1XV

### Steel One Gang Blank Cover, "X" Type

4 9/16" x 2 13/16", stamped steel cover, gasket & screws included

BWF#	Unit UPC 0-87115	Outlets	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
BC-1XV	27231-7		Blank X	Grey	42	5





## Weatherproof “While-In-Use” Receptacle Covers

### BWF Product Benefits & Features

- Choose from high-impact polycarbonate construction or heavy duty die cast covers for more severe applications, such as schools and commercial buildings
- Both meet NEC Article 410-57(b). The code requires receptacles be protected in outdoor or other wet locations with the cord set plugged in, unless the receptacle is attended.
- All covers are shipped with gasket, mounting screws, base and cover assembly, two inserts and complete “easy-to-install” instructions.
- Covers may be mounted to a box or device.
- When security is important, there are covers available with a lockable hasp.
- Flexibility in the field: covers combined with one of the 26 rotating, snap-in, inserts will meet any installation requirement.

### COMPLIANCES

- UL Listed - CSA Certified
- NEMA 3R rated



### APPLICATIONS

- Where weatherproof protection is required while an outlet is in use, such as; bug zappers, holiday lighting, low voltage lighting, soda machines, portable spas, engine block heater, irrigation pond pumps, etc.

MEETS 2002 NEC 406.8(B) (1) Receptacles installed outdoors in a wet location must have an enclosure that is weatherproof when you insert the attachment plug.



### HIGH IMPACT CLEAR POLYCARBONATE “WHILE-IN-USE” COVERS

gasket, mounting screws, base & cover assembly, 2 inserts included

PACKAGE TYPE	BWF No.	Unit UPC 0-87115	Description	Color	Case QTY	Case WT
SHOW PAK	WT1000C*	00102-3	1 gang Vertical ONLY	2 1/4"	Clear	6 3
	WT1000GC*	34011-5	1 gang Vertical ONLY	2 1/4"	Grey	6 3
	WT1000HC	34012-2	1 gang Horizontal ONLY	2 1/4"	Clear	6 4.25
	WT1000HGC*	34013-9	1 gang Horizontal ONLY	2 1/4"	Grey	6 8
	WT1010C*	34014-6	1 gang Vertical ONLY	3 1/8"	Clear	6 8
	WT1010GC*	34020-7	1 gang Vertical ONLY	3 1/8"	Gray	6 3
	WT1010HC*	34021-4	1 gang horizontal ONLY	3 1/8"	Clear	6 3
	WT1100C	00100-9	1 gang vertical/horizontal	2 1/4"	Clear	5 4.25
	WT1110C	34022-1	1 gang vertical/horizontal	3 1/8"	Clear	6 8
	WT1150C	34023-8	1 gang vertical/horizontal	4 3/4"	Clear	6 8
	WT1100WC	31175-7	1 gang vertical/horizontal	3 1/8"	White	5 8
	WT1110WC	34024-5	1 gang vertical/horizontal	3 1/8"	White	5 8
	WT1020C	34016-0	2 gang/horizontal only	2 1/4"	Clear	5 8
	WT1220C	00200-6	2 gang	2 1/4"	Clear	5 8
	WT1230C	34027-6	2 gang	3 1/8"	Clear	6 8
WT1250C	34028-3	2 gang	4 3/4"	Clear	6 8	

\*With lockable hasp



### HEAVY DUTY DIE CAST METAL “WHILE-IN-USE” COVERS

gasket, mounting screws, base & cover assembly, 2 inserts included

PACKAGE TYPE	BWF No.	Unit UPC 0-87115	Description	Color	Case QTY	Case WT
SHOW PAK	WT1010HMC*	34018-4	1 gang horizontal	3 1/8"	Grey	4 5
	WT1010MC*	34017-7	1 gang vertical	3 1/8"	Grey	4 5
	WT1030MC*	34019-1	2 gang	3 1/8"	Grey	2 3.5

\*With lockable hasp



## One Gang Weatherproof Raised Covers – Die Cast Metal



**RC-1V**

### One Gang Rectangular Lampholder Cover – One 1/2" Hole

4 9/16" x 2 13/16" x 1 1/16", gasket & screws included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
RC-1V	28036-7	1-1/2"	Grey	20	6
RC-1AV	52880-3	1-1/2"	Bronze	20	6
RC-1WV	52879-7	1-1/2"	White	20	6
<b>Blister Carded</b>					
811-1	00811-4	1-1/2"	Grey	12	5
811AB-1	28542-3	1-1/2"	Bronze	12	5
811W-1	50095-3	1-1/2"	White	12	5






**RC-3V**

### One Gang Rectangular Lampholder Cover – Three 1/2" Holes

4 9/16" x 2 13/16" x 1 1/16", gasket, screws and closure plugs included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
RC-3V	28056-5	3-1/2"	Grey	20	6
RC-3AV	28555-3	3-1/2"	Bronze	20	6
RC-3WV	28755-7	3-1/2"	White	20	6
<b>Blister Carded</b>					
813-1	00813-8	3-1/2"	Grey	12	4
813AB-1	28566-9	3-1/2"	Bronze	12	4
813W-1	50100-4	3-1/2"	White	12	4



**FG-1DCV**

### One Gang Cover for Horizontal GFCI Devices

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FG-1DCV	25006-3	Horiz GFCI	Grey	24	12
FG-1DCAV	25505-1	Horiz GFCI	Bronze	24	12
FG-1DCWV	25705-5	Horiz GFCI	White	24	2
<b>Blister Carded</b>					
511H-1	05114-1	Horiz GFCI	Grey	6	3
511HAB-1	25508-2	Horiz GFCI	Bronze	6	3
511HW-1	50065-6	Horiz GFCI	White	6	3

## One Gang Weatherproof Covers – Die Cast Metal

### Horizontal GFCI Kit Includes:

Rectangular 3-hole box, self closing GFCI cover, GFCI receptacle, hardware & instructions

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Clamshell Kit</b>					
GFBK-C-1	41201-0	Horiz GFCI Kit	Grey	10	18
GFBKAB-C-1	41202-7	Horiz GFCI Kit	Bronze	10	18
GFBKW-C-1	41203-4	Horiz GFCI Kit	White	10	18
GFBKB-C-1	41204-1	Horiz GFCI Kit	Black	10	18
<b>Display Box Kit</b>					
GFBK	41200-3	Horiz GFCI Kit	Grey	10	17
GFBKAB	41205-8	Horiz GFCI Kit	Bronze	10	17
GFBKW	50220-9	Horiz GFCI Kit	White	10	17
GFBKB	50221-6	Horiz GFCI Kit	Black	10	17



**GFBK-C**


### One Gang Cover for Vertical GFCI Devices

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FGV-1DCV	25012-4	Vertical GFCI	Grey	24	12
FGV-1DCAV	25510-5	Vertical GFCI	Bronze	24	12
FGV-1DCWV	25710-9	Vertical GFCI	White	24	12
<b>Blister Carded</b>					
511V-1	05115-8	Vertical GFCI	Grey	6	3
511VAB-1	25513-6	Vertical GFCI	Bronze	6	3
511VW-1	50070-0	Vertical GFCI	White	6	3



**FGV-1DCV**



GFCI: Ground Fault Circuit Interrupter or “Shock Protection” outlet stops the flow of electricity at the outlet. Required by the National Electrical Code (NEC) for wet or damp locations, inside or out.

### One Gang Vertical Cover for Duplex Receptacles, Switches or Combination Devices

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FCL-62V	22095-0 (Locking)	Vertical	Grey	24	8
FC-61AV	52884-1	Vertical	Bronze	24	8
FC-61WV	52883-4	Vertical	White	24	8
<b>Blister Carded</b>					
4161-1	22096-7	Vertical	Grey	24	8



**FCL-62V**

## One Gang Weatherproof Covers – Die Cast Metal



**FC-71V**



**FCL-71V**

### One Gang Vertical Cover for a Single Receptacle or Switch

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FC-71V	23007-2	Vertical	Grey	24	8
FC-71AV	27240-9	Vertical	Bronze	24	8
FC-71WV	27241-6	Vertical	White	24	8
FCL-71V (Locking)	27255-3	Vertical	Grey	24	8
SO-71V	27246-1	Vert Stay Open	Grey	24	8
<b>Blister Carded</b>					
4171 -1	04171-5	Vertical	Grey	6	2
4171AB -1	23508-4	Vertical	Bronze	6	2
4171W 5-1	0040-3	Vertical	White	6	2




**FC-71HV**

### One Gang Horizontal Cover for a Single Receptacle or Switch

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FC-71HV	27242-3	Horizontal	Grey	24	8
FC-71HAV	27243-0	Horizontal	Bronze	24	8
FC-71HWV	27244-7	Horizontal	White	24	8



## One Gang Weatherproof Covers – Die Cast Metal

### One Gang Horizontal Cover for a Duplex Receptacle or Switch

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FC-81V	23015-7	Horizontal	Grey	24	10
FC-81AV	23510-7	Horizontal	Bronze	24	10
FC-81WV	23710-1	Horizontal	White	24	10
SO-81V	27249-2	Horiz Stay Open	Grey	24	9
SO-81AV	27250-8	Horiz Stay Open	Bronze	24	9
SO-81WV	27251-5	Horiz Stay Open	White	24	9
<b>Blister Carded</b>					
4181-1	04181-4	Horizontal	Grey	12	5
4181AB-1	23521-3	Horizontal	Bronze	12	5
4181W-1	50045-8	Horizontal	White	12	5



**FC-81V**

### One Gang Horizontal Cover for a Duplex Receptacle

Self closing cover, receptacle, gasket & screws included

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FC-81RV	23019-5	w/Receptacle	Grey	18	12
FC-81RAV	27245-4	w/Receptacle	Bronze	18	12
FC-81RWV	23018-8	w/Receptacle	White	18	12
<b>Blister Carded</b>					
4181R-1	41813-5	w/Receptacle	Grey	6	4
4181RAB-1	23526-8	w/Receptacle	Bronze	6	4
4181RW-1	50050-2	w/Receptacle	White	6	4



**FC-81RV**

### Double Outlet Kit Includes:

Rectangular 3 hole box, self closing duplex cover, duplex receptacle, hardware & instructions

BWF#	Unit UPC 0-87115	Description Cover	Color	Case Qty.	Case Weight
<b>Clamshell Kit</b>					
B81RK-C-1	08137-7	Duplex Kit	Grey	10	14
B81RKAB-C-1	08138-4	Duplex Kit	Bronze	10	14
B81RKW-C-1	08139-1	Duplex Kit	White	10	14
B81RKB-C-1	08140-7	Duplex Kit	Black	10	14
<b>Display Box Kit</b>					
B81RK	08130-8	Duplex Kit	Grey	10	14
B81RKAB	08136-0	Duplex Kit	Bronze	10	14
B81RKW	50210-0	Duplex Kit	White	10	14
B81RKB	08135-3	Duplex Kit	Black	10	14



**B81RK-C**

## One Gang Weatherproof Covers – Die Cast Metal




**PO-50V**

### One Gang Power Outlet Cover for Single Receptacle; 20A, 30A, 50A

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Amps	Opening	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
PO-50V	26006-2	20A-50A	2.125"		Grey	24	15
PO-17V	27269-0	30A	1.750"		Grey	24	15
PO-16V	27272-0	20A & 30A	1.625"		Grey	24	15
PO-14V	27275-1	STD	1.438"		Grey	24	15



**TS-1V**

## One Gang Weatherproof Toggle Switch Covers – Die Cast Metal

### One Gang Toggle Switch Cover for One 10A or 20A Switch

Gasket & screws included

BWF#	Unit UPC 0-87115	Switch	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TS-1V	27281-2	N/A		Grey	20	5

## One Gang Lockable Multi - Use Weatherproof Covers – Die Cast Metal

### One Gang Vertical Cover,

Die cast cover, inserts, gasket & screws included

BWF#	Unit UPC 0-87115	Color	Case Qty.	Case Weight
<b>Show Pak</b>				
FCLV-MUSE-V	22097-4	Grey	24	7.00
FCLV-MUSE-AV	22098-1	Bronze	24	7.00
FCLV-MUSE-WV	22099-8	White	24	7.00
<b>Blister Carded</b>				
FCLV-MUSE-1	22106-3	Grey	6	2.00
FCLV-MUSE-A1	22107-0	Bronze	6	2.00
FCLV-MUSE-W1	22108-7	White	6	2.00



### 3 Configurations



Duplex



GFCI



Adapter  
for 1 3/8  
Round  
(included)

## One Gang Lockable Multi - Use Weatherproof Covers – Die Cast Metal

### One Gang Horizontal Cover,

Die cast cover, inserts, gasket & screws included

BWF#	Unit UPC 0-87115	Color	Case Qty.	Case Weight
<b>Show Pak</b>				
FCL-MUSE-V	22100-1	Grey	24	7.00
FCL-MUSE-AV	22101-8	Bronze	24	7.00
FCL-MUSE-WV	22102-5	White	24	7.00
<b>Blister Carded</b>				
FCL-MUSE-1	22109-4	Grey	6	2.00
FCL-MUSE-A1	22110-0	Bronze	6	2.00
FCL-MUSE-W1	22111-7	White	6	2.00



### 3 Configurations



Duplex



GFCI



Adapter  
for 1 3/8  
Round  
(included)



**TS-11V**




- All BWF switch covers are made of rugged, die cast metal construction.
- For use when weatherproof protection is required for an "on-off" type switch.

## One Gang Weatherproof Toggle Switch Covers - Die Cast Metal

### One Gang Toggle Switch Cover with Switch

Gasket & screws included

BWF#	Unit UPC 0-87115	Switch	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>					
TS-11V	27012-2	15A/single pole	Grey	18	10
TS-11AV	27284-3	15A/single pole	Bronze	18	10
TS-11WV	27011-5	15A/single pole	White	18	10
TS-13V	27016-0	15A/3 way	Grey	18	10
TS-15V	27287-4	20A/single pole	Grey 18		10
TS-15AV	27288-1	20A/single pole	Bronze	18	10
TS-15WV	27289-8	20A/single pole	White	18	10
<b>Blister Carded</b>					
611-1	00611-0	15A/single pole	Grey	6	2
611AB-1	27512-7	15A/single pole	Bronze	6	2
611W-1	50075-5	15A/single pole	White	6	2
613-1	00613-4	15A/3 way	Grey	6	3
613AB-1	50081-6	15A/3 way	Bronze	6	3
613W-1	50080-9	15A/3 way	White	6	3



Dimensional cover drawing for:  
TS-1V, TS-11V, TS-13V, TS-15V, 611, 613



**BC-2V**

## Two Gang Weatherproof Covers - Stamped Steel

### Two Gang Blank Cover

Stamped steel cover, gasket & screws included

BWF#	Unit UPC 0-87115	Cover	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>					
BC-2V	29010-6	Blank	Grey	24	3
BC-2AV	27290-4	Blank	Bronze	24	3
BC-2WV	27291-1	Blank	White	24	3
<b>Blister Carded</b>					
722-1	00722-3	Blank	Grey	12	2
722AB-1	29516-3	Blank	Bronze	12	2
722W-1	50110-3	Blank	White	12	2



**FGV-291V**

### Two Gang Cover for 1 GFCI Receptacle & 1 Single Switch or Receptacle

Die cast self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Cover	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>						
FGV-291V	27292-8		Two Gang	Grey	18	9

## Two Gang Weatherproof Covers – Die Cast Metal


### Two Gang Cover for 1 GFCI Receptacle & 1 Duplex Receptacle, Switch or Combination Device

Die cast self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Cover	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
FGV-261V	27295-9		Two Gang	Grey	18	9
FGV-261AV	27296-6		Two Gang	Bronze	18	9
FGV-261WV	27297-3		Two Gang	White	18	9



**FGV-261V**



### Two Gang Cover for 2 GFCI Receptacles

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Cover	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
FGV-2DCV	25031-5		Two Gang	Grey	18	9



**FGV-2DCV**

### Two Gang Cover for 1 GFCI Receptacle & 1 10A/20A Switch

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Cover	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
FGV-TS1V	25040-7		Two Gang	Grey	18	9




**FGV-TS1V**

### Two Gang Cover for 2 Duplex Receptacles, Switches or Combination Devices

Self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Cover	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
FC-261V	24011-8		Two Gang	Grey	18	10
FC-261AV	27303-1		Two Gang	Bronze	18	10
<b>Blister Carded</b>						
4261-1	04261-3		Two Gang	Grey	6	4
4261AB-1	24512-0		Two Gang	Bronze	6	4
4261W-1	50060-1		Two Gang	White	6	4



**FC-261V**

## Two Gang Weatherproof Covers – Die Cast Metal

### Universal Duplex Cover, Fits 1 Gang, 2 Gang & Round Boxes

Gasket & screws included



**FC-271V**

BWF#	Unit UPC 0-87115	Cover	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FC-271V	27305-5	Universal	Grey	18	10

### Two Gang Cover for 2 Single Receptacles and/or Switches

gasket & screws included



**FC-281V**

Left & Right Lids Lock

BWF#	Unit UPC 0-87115	Cover	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FC-281V	24000-2	Two Gang	Grey	18	10
<b>Blister Carded</b>					
4281 -1	04281-1	Two Gang	Grey	6	4
4281AB-1	24502-1	Two Gang	Bronze	6	4
4281W-1	50055-7	Two Gang	White	6	4




### Two Gang Cover for 1 Single Receptacle or Switch & 1 Duplex Receptacle, Switch or Combination Device

Gasket & screws included



**FC-291V**

BWF#	Unit UPC 0-87115	Cover	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>					
FC-291V	24716-2	Two Gang	Grey	18	11



## Two Gang Weatherproof Covers – Die Cast Metal

### Two Gang Power Outlet Cover for Single Receptacle; 20A, 30A, 50A, 60A

Die cast self closing cover, gasket & screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Opening	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TPO-50V	26740-5	20A-50A	2.125"	Grey	24	9
TPOL-50V (Locking)	27321-5	20A-50A	2.125"	Grey	24	9
TPO-60V	27324-6	30A-60A	2.64"	Grey	24	9
TPOL-60V (Locking)	27327-7	30A-60A	2.64"	Grey	24	9
TPO-17V	27330-7	30A	1.75"	Grey	24	9




**TPO-50V**


### Two Gang Toggle Switch Cover for 2 15A-20A Switches

Stamped aluminum cover, gasket & screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Opening	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TS-2V	27040-5	N/A	N/A	Grey	24	11




**TS-2V**



#### Power Outlet Covers:

- TPO-50V = 2.125"D
- TPOL-50V = 2.125"D
- TPO-60V = 2.64"D
- TPOL-60V = 2.64"D
- TPO-17V = 1.75"D




**TS-2V**

### Two Gang Toggle Switch Cover with 2 Switches

Stamped aluminum cover, gasket & screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Switch	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TS-21V	27040-5	N/A	(2)15A Single Pole	Grey	18	16
TS-25V	27345-1	N/A	(2)20A Single Pole	Grey	18	16



**TS-21V**

### Two Gang Toggle Switch & Receptacle Cover for 1 Switch & 1 Single Receptacle

Die cast cover, gasket & screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Description Switch	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TS-171AV	27349-9	N/A	N/A	Bronze	24	16
TS-171WV	27350-5	N/A	N/A	White	24	16



**TS-171AV**


### Two Gang Toggle Switch & Receptacle Cover for 1 Switch & 1 Duplex Receptacle

Die cast cover, gasket & screws included


BWF#	Unit UPC 0-87115	Unit Cubic	Description Switch	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
TS-161V	27351-2	N/A	N/A	Grey	24	16
TS-161AV	27352-9	N/A	N/A	Bronze	24	16




**TS-161V**



**TS-21V, TS-25V**



**TS-171V**



**TS-161V**

## Two Gang Weatherproof Covers – Die Cast Metal

### Two Gang Cover,

Die cast cover, gasket & screws included



BWF#	Unit UPC 0-87115	Unit Cubic	Color	Case Qty.	Case Weight
<b>Show Pak</b>					
2FCLV-MUSE-V	22097-4	N/A	Grey	18	8.00
2FCLV-MUSE-AV	22098-1	N/A	Bronze	18	8.00
2FCLV-MUSE-WV	22099-8	N/A	White	18	8.00
<b>Blister Carded</b>					
2FCLV-MUSE-1	22106-3	N/A	Grey	6	3.00
2FCLV-MUSE-A1	28512-6	N/A	Bronze	6	3.00
2FCLV-MUSE-W1	50085-4	N/A	White	6	3.00



### 6 Configurations



**GFCI**



**Duplex**



**1 3/8  
Round**



**GFCI &  
Duplex**



**Duplex &  
Round**



**Duplex &  
1 3/8 Round**

## Round Weatherproof Covers – Die Cast Metal

### Ceiling Outlet Cover, 5" O.D., Flat with Beveled Edge

Stamped aluminum cover with mounting screws

BWF#	Unit UPC 0-87115	Unit Cubic	Cover	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
CC-3WV	27356-7	N/A	for 3" box		White	50	8
CC-4WV	27359-8	N/A	for 4" box		White	50	8



**CC-3WV**

### Round Blank Cover, 4" O.D.

Stamped aluminum covers, gasket & screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Cover	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
RBCV	20100-3	N/A	Blank		Grey	50	10
RBCAV	52882-7	N/A	Blank		Bronze	50	10
RBCWV	52881-0	N/A	Blank		White	50	10



**RBCV**

### Round Lampholder Cover, One 1/2" Hole, 4-1/2" Diameter

Die cast cover, gasket & screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Cover	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
CR-1V	28006-0	N/A	1-1/2"		Grey	24	10
CR-1AV	52877-3	N/A	1-1/2"		Bronze	24	10
CR-1WV	52876-6	N/A	1-1/2"		White	24	10
<b>Blister Carded</b>							
931-1	00931-9	78	1-1/2"		Grey	6	2
931AB-1	28512-6	78	1-1/2"		Bronze	6	2
931W-1	50085-4	78	1-1/2"		White	6	2



**CR-1V**

### Round Lampholder Cover, Three 1/2" Holes, 4-1/2" Diameter

Closure plugs, gasket & screws included

BWF#	Unit UPC 0-87115	Unit Cubic	Cover	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
CR-3V	28026-8		3-1/2"		Grey	24	10
CR-3AV	28525-6		3-1/2"		Bronze	24	10
CR-3WV	28725-0		3-1/2"		White	24	10
<b>Blister Carded</b>							
933-1	00933-3		3-1/2"		Grey	6	3
933AB-1	28532-4		3-1/2"		Bronze	6	3
933W-1	50090-8		3-1/2"		White	6	3
<b>Show Pak</b>							
CRD-3V-(Domed)	28066-4		3-1/2"		Grey	24	10



**CR-3V**


### Automatic Door Operated Light Switch

Switch in "ON" when door is open

BWF#	Unit UPC 0-87115	Unit Cubic	Switch	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
DS-1V	09005-8		Automatic		Metal	24	2.5



**DS-1V**



**CC-3WV, CC-4WV**



## Lampholders – Die Cast Metal

### BWF Product Benefits & Features

- Rugged, seamless, die-cast construction that prevents moisture entry
- State of the art powder coat finish for maximum durability
- Locking swivel knuckle allows positive lamp positioning and pin-point directional aiming
- Lampholders supplied with porcelain sockets, internal gaskets, extra long wire leads, hardware and installation instructions

### Applications

- For exterior or interior lighting
- For safety and security, light walkways, driveways and doorways

### Die Cast Lampholder

Porcelain socket with leads& internal gasket included



**H-1V**




**HG-100V**



**H-90**




**H-92**



**H1V**

All BWF Incandescent Lampholders use one 150 Watt maximum standard base floodlight bulb. Bulbs not included.



**H-90, HH55 H-92, HH75**

BWF#	Unit UPC 0-87115	Color	Case Qty.	Case Weight
<b>Bulk</b>				
HU-1	30015-7	Unfinished	50	25
<b>Show Pak</b>				
H-1V	30006-5	Grey	27	14
H-1AV	30505-3	Bronze	27	14
H-1WV	30705-7	White	27	14
<b>Blister Carded</b>				
1001-1	01001-8	Grey	6	4
1001AB-1	30156-7	Bronze	6	4
1001W -1	50115-8	White	6	4

### Die Cast Lampholder with External Gasket

Porcelain socket with leads& internal gasket included

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
HG-100V	27370-3	H1 w/gasket		Grey	27	15
HG-100AV	27371-0	H1 w/gasket		Bronze	27	15
HG-100WV	27372-7	H1 w/gasket		White	27	15

### Die Cast Lampholder with Attached 5-1/2" Hood

Porcelain socket with leads& internal gasket included

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>						
H-90	31005-7	5-1/2" Hood		Grey	6	6
H-90AB	31505-2	5-1/2" Hood		Bronze	6	6
H-90W	31705-6	5-1/2" Hood		White	6	6
<b>Display Packaging</b>						
HH55	04455-6	5-1/2" Hood		Grey	6	7
HH55AB	31507-6	5-1/2" Hood		Bronze	6	7
HH55W	50120-2	5-1/2" Hood		White	6	7
HH55B	31506-9	5-1/2" Hood		Black	6	7

### Die Cast Lampholder with Attached 5-1/8" Contemporary Hood

Porcelain socket & internal gasket included

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>						
H-92	31022-4	Contemporary		Grey	6	7
H-92AB	31522-9	Contemporary		Bronze	6	7
H-92W	50131-8	Contemporary		White	6	7
<b>Display Packaging</b>						
HH75	04475-4	Contemporary		Grey	6	7
HH75AB	31523-6	Contemporary		Bronze	6	7
HH75W	50130-1	Contemporary		White	6	7

## Lampholders – Die Cast Metal

### Slip Fitter Pole Top Adapters

For use with troughs or boxes

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>						
A-20	39020-2	1/2" NPT		Metal	10	4



**A-20**

### Two Lamp Swivel Light with Deep Ceiling Plate

Deep ceiling plate, 2 adjustable lampholders, porcelain sockets with leads & internal gaskets


BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>						
SVLD-2	31136-8	Deep Box		Grey	8	14
SVLD-2AB	31537-3	Deep Box		Bronze	8	14
SVLD-2W	31737-7	Deep Box		White	8	14



### Round One Lamp Floodlight Includes:

1 lampholder, porcelain socket with leads, round cover, gaskets & screws

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
LHC-1V	31025-5	RD 1 Lamp		Grey	8	7.5
LHC-1AV	31525-0	RD 1 Lamp		Bronze	8	7.5
LHC-1WV	31725-4	RD 1 Lamp		White	8	7.5
<b>Blister Carded</b>						
93101-1	66599-7	RD 1 Lamp		Grey	6	6
93101AB-1	31526-7	RD 1 Lamp		Bronze	6	6
93101W-1	50135-6	RD 1 Lamp		White	6	6
93101B-1	31527-4	RD 1 Lamp		Black	6	6



**SVLD-2**

### Round Two Lamp Floodlight Includes:

2 lampholders, porcelain sockets with leads, 3 hole round cover, gaskets & screws

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
LHC-2V	31035-4	RD 2 Lamp		Grey	8	10.5
LHC-2AV	31535-9	RD 2 Lamp		Bronze	8	10.5
LHC-2WV	31735-3	RD 2 Lamp		White	8	10.5
<b>Blister Carded</b>						
93102-1	66600-0	RD 2 Lamp		Grey	6	9
93102AB-1	31531-1	RD 2 Lamp		Bronze	6	9
93102W-1	50140-0	RD 2 Lamp		White	6	9
93102B-1	31530-4	RD 2 Lamp		Black	6	9



**LHC-1V**

### Round Two Lamp Floodlight Kit Includes:

2 lampholders, porcelain sockets with leads, 3 hole round cover, 5 hole round box, gaskets & screws

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Clamshell Kit</b>						
2HRBK-C-1	02437-4	RD 2 Lamp Kit		Grey	10	21
2HRBKAB-C-1	02438-1	RD 2 Lamp Kit		Bronze	10	21
2HRBKW-C-1	02439-8	RD 2 Lamp Kit		White	10	21
2HRBKB-C-1	02440-4	RD 2 Lamp Kit		Black	10	21
<b>Display Packaging</b>						
2HRBK	02430-5	RD 2 Lamp Kit		Grey	10	23
2HRBKAB	02436-7	RD 2 Lamp Kit		Bronze	10	23
2HRBKW	50190-5	RD 2 Lamp Kit		White	10	23
2HRBKB	02435-0	RD 2 Lamp Kit		Black	10	23



**LHC-2V**



**2HRBK**

## Lampholders – Die Cast Metal

### Rectangular One Lamp Floodlight Includes:

1 lampholder, porcelain socket with leads, 1 hole rectangular cover, gaskets & screws



**LHR-1V**

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
LHR-1V	31055-2	RT 1 Lamp	Grey		8	6.5
LHR-1AV	31555-7	RT 1 Lamp	Bronze		8	6.5
LHR-1WV	31755-1	RT 1 Lamp	White		8	6.5

### Rectangular Two Lamp Floodlight Includes:

2 lampholders, porcelain sockets with leads, 3 hole rectangular cover, plug, gaskets & screws



**LHR-2V**

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
LHR-2V	31065-1	RD 2 Lamp	Grey		8	10
LHR-2AV	31565-6	RD 2 Lamp	Bronze		8	10
LHR-2WV	31765-0	RD 2 Lamp	White		8	10

### Rectangular Two Lamp Floodlight Kit Includes:

2 lampholders, porcelain sockets with leads, 3 hole rectangular cover, 3 hole rectangular box, gaskets & screws



**2HBK-C-1**

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Clamshell Kit</b>						
2HBK-C-1	02401-5	RT 2 Lamp Kit	Grey		10	20
2HBKAB-C-1	02402-2	RT 2 Lamp Kit	Bronze		10	20
2HBKW-C-1	02403-9	RT 2 Lamp Kit	White		10	20
2HBKB-C-1	02404-6	RT 2 Lamp Kit	Black		10	20
<b>Display Box Kit</b>						
2HBK	02400-8	RT 2 Lamp Kit	Grey		10	20
2HBKAB	02406-0	RT 2 Lamp Kit	Bronze		10	20
2HBKW	50185-1	RT 2 Lamp Kit	White		10	20
2HBKB	02405-3	RT 2 Lamp Kit	Black		10	20

### Rectangular Three Lamp Floodlight Kit Includes:

3 lampholders, porcelain sockets with leads, 3 hole rectangular cover, 3 hole rectangular box, gaskets & screws



**LHR-3V**

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>						
LHR-3AV	27393-2	RT 3 Lamp	Bronze		8	13
LHR-3WV	27394-9	RT 3 Lamp	White		8	13

### Contemporary Two Lamp Floodlight Kit Includes:

2 lampholders, porcelain sockets with leads, 3 hole rectangular cover, 3 hole rectangular box, gaskets & screws



**2H75K**

BWF#	Unit UPC 0-87115	Type	Description	Color	Case Qty.	Case Weight
<b>Display Box Kit</b>						
2H75KW	50215-5	RT 2 Lamp Kit	White		6	19
2H75KB	24755-1	RT 2 Lamp Kit	Black		6	19

Every BWF Kit is a complete weatherproof installation. All hardware and components are included, making additional purchases unnecessary. Each kit includes illustrated, easy-to-install instructions.



## Security Lighting – Die Cast Metal

BWF has a complete line of Security Lighting and Photoelectric components and replacement parts. Automatic night switches will effectively light and protect an area from dusk until dawn. They are used for sunset activated control of night lighting and may be used for many applications, such as: porch lights, garden lights, post lanterns, barn lights, loading dock areas, industrial sites and outdoor signage. A built in time delay prevents operation triggered by auto headlamps or other temporary light flashes.

### Rectangular Two Lamp Security Light Includes:

2 lampholders w/porcelain sockets, 3 hole rectangular cover with photoelectric eye, gaskets & screws

BWF#	Unit UPC 0-87115	Description Outlets	Color	Case Qty.	Case Weight
<b>Clamshell Kit</b>					
SL-2C-1	50147-9	RT 2 Lamp Kit	Grey	10	19
SL-2BC-1	50151-6	RT 2 Lamp Kit	Black	10	19
<b>Display Box Kit</b>					
SL-2	00782-7	RT 2 Lamp Kit	Grey	10	21
SL-2B	50146-2	RT 2 Lamp Kit	Black	10	21



**SL-2**

### Chrome Plated Clamp-on Guard – for Bulb Protection

#### Clamp-on Guard – Chrome Plated

Fits H-1 lampholders for floodlight bulb protection

BWF#	Unit UPC 0-87115	Type	Description Color	Case Qty.	Case Weight
<b>Clamshell Kit</b>					
GD-100V	31169-6	Clamp	Chrome	5	2.5



**GD-100V**



Lights will automatically come on at dusk



Avoid accidents and intrusions by brightly illuminating walkways and driveways.



Deter crime by brightly lighting areas that might otherwise attract a potential burglar.

## Garden Lighting – Die Cast Metal



**P-3**

Incandescent: 75W or 13W CFL max, Bulb not included




**P-4**

Incandescent: 75W or 13W CFL max, Bulb not included



### Isolux Curve

Wattage	Multiplier	Wattage	Multiplier
150	1.0	50	.27
75	.68	40	.26
60	.44	25	.13



### Photometrics:

Based on lamp center 24" above ground. Based on 100 Watt A-19 inside frosted 1750 lumen lamp. For other wattage see table above.



### BWF Product Benefits & Features

- Rugged, seamless, die-cast construction that does not allow moisture entry
- State of the art powder coat finish for maximum durability
- Includes screw-in clear glass globe, 5" for 3-Tier, 7" for 4-Tier lights

### Applications

- For accent lighting along walkways, driveways, • Lighting around pools, patios and garden areas terraces and porches
- Accent shrubbery and landscaping

### Three Tier Louver Light with 5" Glass Globe



1/2" NPT base, 110/120V 75 Watt Max

BWF#	Unit UPC 0-87115	Pipe Size	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>							
P-3	33005-5	1/2	3 Tier		Green	6	18
P-3AB	33510-4	1/2	3 Tier		Bronze	6	18
P-3W	33705-4	1/2	3 Tier		White	6	18
P-3B	33010-9	1/2	3 Tier		Black	6	18
LL3	00883-1	1/2	3 Tier		Green	6	18

### Four Tier Louver Light with 7" Glass Globe

1/2" NPT base, 110/120V 100 Watt Max

BWF#	Unit UPC 0-87115	Pipe Size	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>							
P-4	33015-4	1/2	4 Tier		Green	6	22
P-4AB	33515-9	1/2	4 Tier		Bronze	6	22
P-4W	33706-1	1/2	4 Tier		White	6	22
P-4B	33020-8	1/2	4 Tier		Black	6	22
LL4	00884-8	1/2	4 Tier		Green	6	23



## Garden Lighting – Die Cast Metal

### Portable Spikelite

1 - H-1 lampholder with external gasket, 5" ground spike, 7 ft 18/3 cord w/molded plug

BWF#	Unit UPC 0-87115	Type	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>					
SP-1V	27399-4	H-1 w/Spike/Cord	Grey	6	7
SP-1GV	31193-1	H-1 w/Spike/Cord	Green	6	7
<b>Bulk Pallet</b>					
SP-1G-24	31194-8	H-1 w/Spike/Cord	Green	24	90
SP-1GN-48	31509-0	H-1 w/Spike/Cord	Green	48	90



SP-1V

### Replacement Parts and Accessories for Garden Lighting

BWF#	Unit UPC 0-87115	Type	Description Color	Case Qty.	Case Weight
<b>Boxed</b>					
G-5	33085-7	5" Globe	Clear Glass	40	32
G-7	33090-1	6" Globe	Clear Glass	32	33
<b>Show Pak</b>					
MGSV	21030-2	7" Ground spike	Grey	18	6



G-5



G-7



MGSV

## Vaportight Fixtures – Incandescent or Self Ballasted CFL

G= Wire Guard  
CG= Cast Guard



**VPKG-11**



**VPKG-11-CG**



**VPXG-70MH-CG**



**VPKG-42-CG**



**VXWG-70MH-CG**

### Pendant Fixtures

1/2" & 3/4" NPT base, 110/120V, fully enclosed & gasketed

BWF#	Unit UPC 0-87115	Hub Size	Description Wattage	Color	Case Qty.	Case Weight
<b>Boxed</b>						
VPKG-11L	14020-3	1/2"	75	Lexan® Clear	6	10
VPKG-11L/S	14028-9	1/2"	75	Lexan® Clear w/weep hole	6	10
VPKG-21L	14025-8	3/4"	75	Lexan® Clear	6	10
VPKG-21L/S	14027-2	3/4"	75	Lexan® Clear w/weep hole	6	10
VPKG-11	14030-2	1/2"	100	Glass Clear	6	13
VPKG-21	14035-7	3/4"	100	Glass Clear	6	13
VPKG-12L	14220-7	1/2"	100	Lexan® Clear	1	2.1
VPKG-22L	14225-2	3/4"	100	Lexan® Clear	1	2.1
VPKG-12	14230-6	1/2"	200	Glass Clear	1	3.6
VPKG-22	14235-1	3/4"	200	Glass Clear	1	3.6

### Pendant Fixtures with Guard

1/2" & 3/4" NPT base, 110/120V, fully enclosed & gasketed

BWF#	Unit UPC 0-87115	Hub Size	Description Wattage	Color	Case Qty.	Case Weight
<b>Boxed</b>						
VPKG-11-G	14040-1	1/2"	100	Glass Clear	6	16
VPKG-11-CG	14039-5	1/2"	100	Glass Clear	6	20
VPKG-21-G	14045-6	3/4"	100	Glass Clear	6	16
VPKG-21-CG	14044-9	3/4"	100	Glass Clear	6	20
VPKG-12-G	14240-5	1/2"	200	Glass Clear	1	4.1
VPKG-22-G	14245-0	3/4"	200	Glass Clear	1	4.1

### HID Vaportight Fixtures – Metal Halide, HPS and Compact Fluorescent

#### Box Mounted Fixture for Wall or Ceiling

1/2" reducing bushing and 3/4" NPT base, fully enclosed & gasketed

BWF#	Unit UPC 0-87115	Volts	Description Wattage	Lumens	Case Qty.	Case Weight
<b>Boxed</b>						
VPXG-70MH-CG	15100-9	Quad	70	6,000	1	23
VPXG-150HPS-CG	15101-6	120	150	16,000	1	20
VPXG-100HPS-CG	15102-3	120	100	9,500	1	20
VPXG-42CF-CG	15103-0	120/277	42	3,200	1	20

### Pendant Fixtures with Guard

1/2" reducing bushing and 3/4" NPT base, fully enclosed & gasketed

BWF#	Unit UPC 0-87115	Volts	Description Wattage	Lumens	Case Qty.	Case Weight
<b>Boxed</b>						
VPKG-70MH-CG	15110-8	Quad	70	6,000	1	23
VPKG-150HPS-CG	15111-5	120	150	16,000	1	20
VPKG-100HPS-CG	15112-2	120	100	9,500	1	20
VPKG-42CF-CG	15113-9	120/277	42	3,200	1	20

### Wall Mount Fixture with Right Angle Bracket

1/2" reducing bushing and 3/4" NPT base, fully enclosed & gasketed

BWF#	Unit UPC 0-87115	Volts	Description Wattage	Lumens	Case Qty.	Case Weight
<b>Boxed</b>						
VXWG-70MH-CG	15120-7	Quad	70	6,000	1	23
VXWG-150HPS-CG	15121-4	120	150	16,000	1	20
VXWG-100HPS-CG	15122-1	120	100	9,500	1	20
VXWG-42CF-CG	15123-8	120/277	42	3,200	1	20

## Vaportight Fixtures – Incandescent or Self Ballasted CFL

### Surface Mount Fixtures for Round or Octagonal Boxes

Fits all 3-1/2" and 4" round boxes, 1/2" & 3/4" NPT base, 110/120V, fully enclosed & gasketed

BWF#	Unit UPC 0-87115	Box Size	Wattage	Description Color	Case Qty.	Case Weight
<b>Boxed</b>						
VPAG-01L	14050-0	3-1/2 & 4"	75	Lexan® Clear	6	7
VPAG-01	14055-5	3-1/2 & 4"	100	Glass Clear	6	10
VPAG-02L	14250-4	3-1/2 & 4"	100	Lexan® Clear	1	1.5
VPAG-02	14255-9	3-1/2 & 4"	200	Glass Clear	1	3.0

G= Wire Guard  
CG= Cast Guard



**VPAG-01**

### Surface Mount Fixtures with Guard for Round or Octagonal Boxes

Fits all 3-1/2" and 4" round boxes, 1/2" & 3/4" NPT base, 110/120V, fully enclosed & gasketed

BWF#	Unit UPC 0-87115	Box Size	Wattage	Description Color	Case Qty.	Case Weight
<b>Boxed</b>						
VPAG-01-G	14060-9	3-1/2 & 4"	100	Glass Clear	6	18
VPAG-01-CG	14059-3	3-1/2 & 4"	100	Glass Clear	6	20
VPAG-02-G	14260-3	3-1/2 & 4"	200	Glass Clear	1	3.5



**VPAG-01-CG**

**INCANDESCENT:** 75W, 100W, 200W, see individual products, bulb not included.

**IMPORTANT:**

- Vaportight fixtures are not for use in hazardous locations.
- Fixtures supplied with glass globes are furnished with "Clear" glass. See page 31 for colored glass globes.
- Standard Lexan® fixtures have "Clear" Lexan globes. To order any of those fixtures with Red, White, Amber, Blue or Green globes, add the suffix "R", "W", "A", "B" or "G" to the catalog number. See page 31 for Lexan® globes.

LEXAN® is a registered trademark of General Electric Co.

### Box Mounted Fixture for Wall or Ceiling

Four holes 1/2" & 3/4" NPT base, 110/120V, fully enclosed & gasketed, 3 plugs

BWF#	Unit UPC 0-87115	Hub Size	Wattage	Description Color	Case Qty.	Case Weight
<b>Boxed</b>						
VPXG-11L	14065-4	1/2"	75	Lexan® Clear	6	10
VPXG-21L	14070-8	3/4"	75	Lexan® Clear	6	10
VPXG-11	14075-3	1/2"	100	Glass Clear	6	13
VPXG-21	14080-7	3/4"	100	Glass Clear	6	13
VPXG-12L	14265-8	1/2"	100	Lexan® Clear	1	1.9
VPXG-22L	14270-2	3/4"	100	Lexan® Clear	1	2.1
VPXG-12	14275-7	1/2"	200	Glass Clear	1	3.6
VPXG-22	14280-1	3/4"	200	Glass Clear	1	3.6



**VPXG-11**

## Vaportight Fixtures – Incandescent or Self Ballasted CFL

### Box Mounted Fixture for Wall or Ceiling with Cast or Wire Guard

Four holes 1/2" & 3/4" NPT base, 110/120V, fully enclosed & gasketed, 3 plugs

G= Wire Guard  
CG= Cast Guard



**VPXG-11-CG**

BWF#	Unit UPC 0-87115	Hub Size	Wattage	Description Color	Case Qty.	Case Weight
<b>Boxed</b>						
VPXG-11-G	14085-2	1/2"	100	Glass Clear	6	16
VPXG-11-CG	14086-9	1/2"	100	Glass Clear	6	20
VPXG-21-G	14090-6	3/4"	100	Glass Clear	6	16
VPXG-21-CG	14092-0	3/4"	100	Glass Clear	6	20
VPXG-12-G	14285-6	1/2"	200	Glass Clear	1	4.2
VPXG-22-G	14286-3	3/4"	200	Glass Clear	1	4.2

### Wall Mount Fixture with Right Angle Bracket

For use with 4" box, 110/120V, fully enclosed & gasketed



**VWG-01**

BWF#	Unit UPC 0-87115	Box Size	Wattage	Description Color	Case Qty.	Case Weight
<b>Boxed</b>						
VWG-01L	14011-1	4"	75	Lexan® Clear	1	2.0
VWG-01	14021-0	4"	100	Glass Clear	1	2.8
VWG-02L	14287-0	4"	100	Lexan® Clear	1	2.4
VWG-02	14288-7	4"	200	Glass Clear	1	3.7

### Wall Mount Fixture with Right Angle Bracket with Guard

For use with 4" box, 110/120V, fully enclosed & gasketed



**VWG-01-G**

BWF#	Unit UPC 0-87115	Box Size	Wattage	Description Color	Case Qty.	Case Weight
<b>Boxed</b>						
VWG-01-G	14031-9	4"	100	Glass Clear	1	3.2
VWG-01-CG	14032-6	4"	100	Glass Clear	1	4.1
VWG-02-G	14289-4	4"	200	Glass Clear	1	4.2

**INCANDESCENT:** 75W, 100W, 200W, see individual products, bulb not included.

**IMPORTANT:**

- Vaportight fixtures are not for use in hazardous locations.
- Fixtures supplied with glass globes are furnished with "Clear" glass. See page 31 for colored glass globes.
- Standard Lexan® fixtures have "Clear" Lexan globes. To order any of those fixtures with Red, White, Amber, Blue or Green globes, add the suffix "R", "W", "A", "B" or "G" to the catalog number. See page 31 for Lexan® globes.

LEXAN® is a registered trademark of General Electric Co.



**VWG-01-CG**

## Vaportight Fixtures – Incandescent or Self Ballasted CFL

### Wall Mount Fixture with Right Angle Bracket & Box

Factory assembled to 4" weatherproof box, 110/120V, fully enclosed & gasketed, 3 plugs

BWF#	Unit UPC 0-87115	Hub Size	Wattage	Description Color	Case Qty.	Case Weight
<b>Boxed</b>						
VXWG-11L	14041-8	1/2"	75	Lexan® Clear	1	2.7
VXWG-21L	14051-7	3/4"	75	Lexan® Clear	1	3.0
VXWG-11	14061-6	1/2"	100	Glass Clear	1	3.4
VXWG-21	14071-5	3/4"	100	Glass Clear	1	3.4
VXWG-12L	14290-0	1/2"	100	Lexan® Clear	1	3.1
VXWG-22L	14291-7	3/4"	100	Lexan® Clear	1	3.1
VXWG-12	14292-4	1/2"	200	Glass Clear	1	4.5
VXWG-22	14293-1	3/4"	200	Glass Clear	1	4.5

G= Wire Guard  
CG= Cast Guard



**VXWG-11**

### Wall Mount Fixture with Right Angle Bracket & Box with Guard

Factory assembled to 4" weatherproof box, 110/120V, fully enclosed & gasketed, 3 plugs

BWF#	Unit UPC 0-87115	Hub Size	Wattage	Description Color	Case Qty.	Case Weight
<b>Boxed</b>						
VXWG-11-G	14081-4	1/2"	100	Glass Clear	1	3.8
VXWG-11-CG	14082-1	1/2"	100	Glass Clear	1	4.7
VXWG-21-G	14091-3	3/4"	100	Glass Clear	1	3.8
VXWG-21-CG	14089-0	3/4"	100	Glass Clear	1	4.7
VXWG-12-G	14294-8	1/2"	200	Glass Clear	1	5.1
VXWG-22-G	14295-5	3/4"	200	Glass Clear	1	5.1



**VXWG-11-CG**

## Vaportight Fixtures – Incandescent or Self Ballasted CFL

### BWF Product Benefits & Features

- Rugged, seamless, die-cast construction that prevents moisture entry
- State of the art powder coat finish for maximum durability
- All fixtures are industrial grade, factory assembled and fully gasketed
- Engineered to protect the interior from deteriorating effects of ice, corrosive fumes, non-explosive vapors, etc.
- Choose between heat resistant glass globes or Lexan® plastic globes in a choice of colors, see page 31
- 75, 100 and 200 Watt Incandescent fixtures

### Applications

- Vaportight fixtures are not for use in hazardous locations
- For use in severe service areas where extreme conditions prevail
- Applications: subways, construction sites, bridges, tunnels, freezers, waste water & sewage treatment plants



Wire Guard - VPGW



Cast Guard - VPCG



Pendant - VPKG



Ceiling Mount - VPAG



Box Mounted - VPXG



Right Angle Wall  
Mount - VWG



Right Angle Wall  
Mount Assembled  
to Box - VXWG



## Vaportight Fixtures – Incandescent

### Replacement Parts & Accessories



BWF#	Unit UPC 0-87115	Hub Size	Max Wattage	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>							
VPK-11	15020-2	1/2"	100	Pendant cap,	Grey	10	18
VPK-21	15025-7	3/4"	100	porcelain socket	Grey	10	18
VPK-12	15220-6	1/2"	200	gasket and screws	Grey	10	10
VPK-22	15225-1	3/4"	200		Grey	10	10
VPA-01-N	15030-1	N/A	100	Ceiling box cap, socket	Grey	10	12
VPA-02	15230-5	N/A	200	gasket and screws	Grey	10	12
VPX-11	15035-6	1/2"	100	Ceiling mount box	Grey	10	19
VPX-21	15040-0	3/4"	100	with gaskets,	Grey	10	19
VPX-12	15235-0	1/2"	200	porcelain socket	Grey	10	19
VPX-22	15240-4	3/4"	200	and screws	Grey	10	19
VPXL-1	14271-9	5 - 1/2"	N/A	Cross feed box 5 hole	Grey	10	9
VPXL-13	14272-6	5 - 3/4"	N/A	with gaskets	Grey	10	9
VW-01	14096-8	N/A	100	Right angle bracket	Grey	10	21
VW-02	14196-5	N/A	200	gasket, socket, screws	Grey	6	12
VXW-11	14097-5	1/2"	100		Grey	1	3
VXW-21	14297-9	3/4"	100	Right angle bracket	Grey	1	3
VXW-12	14098-2	1/2"	200	attached box, gasket	Grey	1	1.5
VXW-22	14298-6	3/4"	200	socket and screws	Grey	1	1.5
VPCG	15044-8	N/A	100	Heavy duty cast guard	Cast	5	7
VPGW	15045-5	#8 AWS	100	Heavy duty	Wire	5	4
VPGW-02	15046-2	#8 AWS	200	wire guard	Wire	1	1
VPGL-01	15050-9	N/A	100		Glass Clear	1	1.5
VPGL-01G	15054-7	N/A	100	Glass globe for 100 Watt and 200 Watt fixtures	Glass Green	1	1.5
VPGL-01R	15057-8	N/A	100		Glass Red	1	1.5
VPGL-01A	15054-7	N/A	100		Glass Amber	1	1.5
VPGL-01B	15058-3	N/A	100		Glass Blue	1	1.5
VPGLL-01	15059-0	N/A	75		Lexan® Clear	1	1.5
VPGLL-01R	15051-6	N/A	75	Lexan® globe for 100 Watt and 200 Watt fixtures	Lexan® Red	12	3
VPGLL-01W	15065-3	N/A	75		Lexan® White	12	3
VPGLL-01A	15070-7	N/A	75		Lexan® Amber	12	3
VPGLL-01G	15056-1	N/A	75		Lexan® Green	12	3
VPGL-02	15051-6	N/A	200		Lexan® White	1	3
VPGLL-02	15071-4	N/A	150	Lexan® Clear	6	5	
AP-1	15075-2	3 1/2 & 4"	N/A	Adapter plate w/gasket	Metal	20	4
PL-5	21005-0	1/2"	N/A	Closure Plug	Metal	1000	20
PL-75	21010-4	3/4"	N/A	Closure Plug	Metal	1000	21



VPCG

VPGW



VPGL-01 Series (GLASS) VPGLL-01 Series (LEXAN)

\*Colors Available



VPGLL-02



AP-1

PL-5

## Vaportight Fixtures – Incandescent or Self Ballasted CFL

### VPKG Without Guard

Cat No	A	B
VPKG-11L	3-11/16"	8-3/16"
VPKG-21L	3-11/16"	8-3/16"
VPKG-11	3-11/16"	8-3/16"
VPKG-21	3-11/16"	8-3/16"
VPKG-12L	4-3/8"	10-1/2"
VPKG-22L	4-3/8"	10-1/2"
VPKG-12	4-3/8"	10-1/2"
VPKG-22	4-3/8"	10-1/2"

### VPAG Without Guard

Cat No	A	B
VPAG-01L	3-11/16"	6-13/16"
VPAG-01	3-11/16"	6-13/16"
VPAG-02L	4-3/8"	8-1/2"
VPAG-02	4-3/8"	8-1/2"

### VPXG Without Guard

Cat No	A	B
VPXG-11L	3-11/16"	8-5/8"
VPXG-21L	3-11/16"	8-5/8"
VPXG-11	3-11/16"	8-5/8"
VPXG-21	3-11/16"	8-5/8"
VPXG-12L	4-3/8"	10-1/2"
VPXG-22L	4-3/8"	10-1/2"
VPXG-12	4-3/8"	10-1/2"
VPXG-22	4-3/8"	10-1/2"

### VWG Without Guard

Cat No	A	B	E	F
VWG-01L	3-11/16"	7-1/4"	3"	4-1/4"
VWG-01	3-11/16"	7-1/4"	3"	4-1/4"
VWG-02L	4-3/8"	8-3/4"	3"	4-1/2"
VWG-02	4-3/8"	8-3/4"	3"	4-1/2"

### VXWG Without Guard

Cat No	A	B	E	F
VXWG-11L	3-11/16"	7-1/4"	4-1/2"	4-1/4"
VXWG-21L	3-11/16"	7-1/4"	4-1/2"	4-1/4"
VXWG-11	3-11/16"	7-1/4"	4-1/2"	4-1/4"
VXWG-21	3-11/16"	7-1/4"	4-1/2"	4-1/4"
VXWG-12L	4-3/8"	8-3/4"	4-1/2"	4-1/2"
VXWG-22L	4-3/8"	8-3/4"	4-1/2"	4-1/2"
VXWG-12	4-3/8"	8-3/4"	4-1/2"	4-1/2"
VXWG-22	4-3/8"	8-3/4"	4-1/2"	4-1/2"

### VPKG With Guard

Cat No	C	D
VPKG-11-G	4-1/4"	9-5/8"
VPKG-11-CG	4-1/4"	9-5/8"
VPKG-21-G	4-1/4"	9-5/8"
VPKG-21-CG	4-1/4"	9-5/8"
VPKG-12-G	5-1/2"	11"
VPKG-22-G	5-1/2"	11"

### VPAG With Guard

Cat No	C	D
VPAG-01-G	4-1/4"	7-9/16"
VPAG-01-CG	4-1/4"	7-9/16"
VPAG-02-G	5-1/2"	9"

### VPXG With Guard






Cat No	A	B
VPXG-11-G	4-1/4"	9-1/8"
VPXG-11-CG	4-1/4"	9-1/8"
VPXG-21-G	4-1/4"	9-1/8"
VPXG-21-CG	4-1/4"	9-1/8"
VPXG-12-G	5-1/2"	10-3/4"
VPXG-22-G	5-1/2"	10-3/4"

### VWG With Guard

Cat No	C	D	E	F
VWG-01-G	4-1/4"	7-3/4"	3"	4-1/4"
VWG-01-CG	4-1/4"	7-3/4"	3"	4-1/4"
VWG-02-G	5-1/2"	9-1/4"	3"	4-1/2"

### VXWG With Guard

Cat No	C	D	E	F
VXWG-11-G	4-1/4"	7-3/4"	4-1/2"	4-1/4"
VXWG-11-CG	4-1/4"	7-3/4"	4-1/2"	4-1/4"
VXWG-21-G	4-1/4"	7-3/4"	4-1/2"	4-1/4"
VXWG-21-CG	4-1/4"	7-3/4"	4-1/2"	4-1/4"
VXWG-12-G	5-1/2"	9-1/4"	4-1/2"	4-1/2"
VXWG-22-CG	5-1/2"	9-1/4"	4-1/2"	4-1/2"



## Conduit Bodies – Die Cast Metal

### BWF Product Benefits & Features

- Rugged, seamless, die-cast construction that prevents moisture entry
- Flat back design for easy mounting close to walls
- State of the art powder coat finish for maximum durability
- May be used on aluminum or steel conduit
- Add - CG to part number to include cover and gasket

### Applications

- Combo style for use on both rigid and thinwall (EMT) conduit
- Threaded style conduit bodies are for use on rigid conduit.
- Set-screw style are for use on thinwall (EMT) conduit.
- Use BWF conduit outlet bodies for connecting conduit sections, for making bends in conduit runs, as pull outlets, or to provide openings for making splices and taps in conductors.

CG= Cover & Gasket (BULK PAK)  
CGV= Cover & Gasket (VIEW PAK)



500V

### Type SLB – Aluminum Conduit Entrance Ells

Cover, gasket & screws included, for rigid conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
500V	75005-1	1/2"	SLB Threaded	Grey		38	8
501V	75010-5	3/4"	SLB Threaded	Grey		36	8
502V	75015-0	1"	SLB Threaded	Grey		12	6
503V	75020-4	1-1/4"	SLB Threaded	Grey		12	11.5
504V	75025-9	1-1/2"	SLB Threaded	Grey		10	10
505V	75030-3	2"	SLB Threaded	Grey		4	5.5
<b>Boxed</b>							
503-XL	71035-2	1-1/4"	XLSLB Threaded	Grey		5	6
505-XL	71040-6	2"	XLSLB Threaded	Grey		5	14

### Type LR – Combo both Threaded and Set Screw Aluminum Conduit Bodies

For rigid or thinwall (EMT) conduit



D100V

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
D100V	19102-1	1/2"	LR Threaded	Grey		27	7
D101V	19103-8	3/4"	LR Threaded	Grey		15	7.5
D102V	19104-5	1"	LR Threaded	Grey		14	9
D103V	19119-9	1-1/4"	LR Threaded	Grey		4	5.5
D104V	19132-8	1-1/2"	LR Threaded	Grey		4	6
D105V	19133-5	2"	LR Threaded	Grey		2	5.5



10V

### Type LR – Set Screw Aluminum Conduit Bodies

For thinwall (EMT) conduit



BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
10V	28333-7	1/2"	LR Set Screw	Grey		27	7
11V	28334-4	3/4"	LR Set Screw	Grey		15	7.5
12V	28335-1	1"	LR Set Screw	Grey		14	9
13V	28336-8	1-1/4"	LR Set Screw	Grey		4	5.5
14V	28337-5	1-1/2"	LR Set Screw	Grey		4	6
15V	28338-2	2"	LR Set Screw	Grey		2	5.5
<b>Boxed</b>							
16	19138-0	2-1/2"	LR Set Screw	Grey		1	5
17	19139-7	3"	LR Set Screw	Grey		1	6
18	19140-3	3-1/2"	LR Set Screw	Grey		1	10
19	19141-0	4"	LR Set Screw	Grey		1	9

## Conduit Bodies – Die Cast Metal

### Type LR – Threaded Aluminum Conduit Bodies

For rigid conduit

CG= Cover & Gasket (BULK PAK)  
CGV= Cover & Gasket (VIEW PAK)

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>						
100V	28366-5	1/2"	LR Threaded	Grey	27	7
101V	28367-2	3/4"	LR Threaded	Grey	15	7.5
102V	28368-9	1"	LR Threaded	Grey	14	9
103V	28369-6	1-1/4"	LR Threaded	Grey	4	5.5
104V	28370-2	1-1/2"	LR Threaded	Grey	4	6
105V	28371-9	2"	LR Threaded	Grey	2	5.5
<b>Boxed</b>						
106	71240-0	2-1/2"	LR Threaded	Grey	1	5
107	71245-5	3"	LR Threaded	Grey	1	6
108	71250-9	3-1/2"	LR Threaded	Grey	1	10
109	71255-4	4"	LR Threaded	Grey	1	9



100-CGV



100V

### Type LL – Combo both Threaded and Set Screw Aluminum Conduit Bodies

For rigid or thinwall (EMT) conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>						
D200V	19152-6	1/2"	LL Threaded	Grey	27	7
D201V	19153-3	3/4"	LL Threaded	Grey	15	7.5
D202V	19154-0	1"	LL Threaded	Grey	14	9
D203V	19157-1	1-1/4"	LL Threaded	Grey	4	5.5
D204V	19158-8	1-1/2"	LL Threaded	Grey	4	6
D205V	19159-5	2"	LL Threaded	Grey	2	5.5



D200V

### Type LL – Set Screw Aluminum Conduit Bodies

For thinwall (EMT) conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description Color	Case Qty.	Case Weight
<b>Show Pak</b>						
20V	28339-9	1/2"	LL Set Screw	Grey	27	7
21V	28340-5	3/4"	LL Set Screw	Grey	15	7.5
22V	28341-2	1"	LL Set Screw	Grey	14	9
23V	28342-9	1-1/4"	LL Set Screw	Grey	4	5.5
24V	28343-6	1-1/2"	LL Set Screw	Grey	4	6
25V	28439-6	2"	LL Set Screw	Grey	2	5.5
<b>Boxed</b>						
26	19146-5	2-1/2"	LL Set Screw	Grey	1	5
27	19147-2	3"	LL Set Screw	Grey	1	6
28	19148-9	3-1/2"	LL Set Screw	Grey	1	10
29	19149-6	4"	LL Set Screw	Grey	1	9



20V

## Conduit Bodies – Die Cast Metal

CG= Cover & Gasket (BULK PAK)  
CGV= Cover & Gasket (VIEW PAK)

### Type LL – Threaded Aluminum Conduit Bodies

For rigid conduit



200V



D300V



D300V



300V



300V

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
200V	28372-6	1/2"	LL Threaded	Grey		27	7
201V	28373-3	3/4"	LL Threaded	Grey		15	7.5
202V	28374-0	1"	LL Threaded	Grey		14	9
203V	28375-7	1-1/4"	LL Threaded	Grey		4	5.5
204V	28376-4	1-1/2"	LL Threaded	Grey		4	6
205V	28477-1	2"	LL Threaded	Grey		2	5.5
<b>Boxed</b>							
206	71435-0	2-1/2"	LL Threaded	Grey		1	5
207	71440-4	3"	LL Threaded	Grey		1	6
208	71445-9	3-1/2"	LL Threaded	Grey		1	10
209	71450-3	4"	LL Threaded	Grey		1	9

### Type C – Combo both Threaded and Set Screw Aluminum Conduit Bodies

For rigid or thinwall (EMT) conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
D300V	19511-1	1/2"	C Threaded	Grey		24	6.5
D301V	19512-8	3/4"	C Threaded	Grey		18	7.5
D302V	19513-5	1"	C Threaded	Grey		14	9
D303V	19514-2	1-1/4"	C Threaded	Grey		8	12
D304V	19523-4	1-1/2"	C Threaded	Grey		8	11
D305V	19524-1	2"	C Threaded	Grey		2	5

### Type C – Threaded Aluminum Conduit Bodies

For right conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
300V	28378-8	1/2"	C Threaded	Grey		24	6.5
301V	28379-5	3/4"	C Threaded	Grey		18	7.5
302V	28380-1	1"	C Threaded	Grey		14	9
303V	28381-8	1-1/4"	C Threaded	Grey		8	12
304V	28382-5	1-1/2"	C Threaded	Grey		8	11
305V	28383-2	2"	C Threaded	Grey		2	5
<b>Boxed</b>							
306	71535-7	2-1/2"	C Threaded	Grey		1	6.5
307	71540-1	3"	C Threaded	Grey		1	7.5
308	71545-6	3-1/2"	C Threaded	Grey		1	9
309	71550-0	4"	C Threaded	Grey		1	12

## Conduit Bodies – Die Cast Metal

### Type C – Set Screw Aluminum Conduit Bodies

For thinwall (EMT) conduit

CG= Cover & Gasket (BULK PAK)  
CGV= Cover & Gasket (VIEW PAK)

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
30V	28344-3	1/2"	C Set Screw	Grey	Grey	24	6.5
31V	28345-0	3/4"	C Set Screw	Grey	Grey	18	7.5
32V	28346-7	1"	C Set Screw	Grey	Grey	14	9
33V	28347-4	1-1/4"	C Set Screw	Grey	Grey	8	12
34V	28348-1	1-1/2"	C Set Screw	Grey	Grey	8	11
35V	28349-8	2"	C Set Screw	Grey	Grey	2	5
<b>Boxed</b>							
36	19535-7	2-1/2"	C Set Screw	Grey	Grey	1	6.5
37	19536-4	3"	C Set Screw	Grey	Grey	1	7.5
38	19537-1	3-1/2"	C Set Screw	Grey	Grey	1	9
39	19538-8	4"	C Set Screw	Grey	Grey	1	12



30V



D600V



600V



600-CGV

### Type LB – Combo both Threaded and Set Screw Aluminum Conduit Bodies

For rigid or thinwall (EMT) conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
D600V	19531-9	1/2"	LB Threaded	Grey	Grey	30	7
D601V	19532-6	3/4"	LB Threaded	Grey	Grey	18	7.5
D602V	19533-3	1"	LB Threaded	Grey	Grey	16	9
D603V	19534-0	1-1/4"	LB Threaded	Grey	Grey	8	5.5
D604V	19541-8	1-1/2"	LB Threaded	Grey	Grey	8	6
D605V	19542-5	2"	LB Threaded	Grey	Grey	2	5.5

### Type LB – Threaded Aluminum Conduit Bodies

For rigid conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
600V	28384-9	1/2"	LB Threaded	Grey	Grey	24	7
601V	28385-6	3/4"	LB Threaded	Grey	Grey	18	7.5
602V	28386-3	1"	LB Threaded	Grey	Grey	16	9
603V	28387-0	1-1/4"	LB Threaded	Grey	Grey	8	5.5
604V	28388-7	1-1/2"	LB Threaded	Grey	Grey	8	6
605V	28389-4	2"	LB Threaded	Grey	Grey	2	5.5
<b>Boxed</b>							
606	71135-9	2-1/2"	LB Threaded	Grey	Grey	1	5
607	71140-3	3"	LB Threaded	Grey	Grey	1	5
608	71145-8	3-1/2"	LB Threaded	Grey	Grey	1	9.5
609	71150-2	4"	LB Threaded	Grey	Grey	1	8.5

## Conduit Bodies – Die Cast Metal

CG= Cover & Gasket (BULK PAK)  
CGV= Cover & Gasket (VIEW PAK)

### Type LB – Set Screw Aluminum Conduit Bodies

For thinwall (EMT) conduit



60V



D700-CGV



700V



700-CGV

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
60V	28350-4	1/2"	LB Set Screw	Grey		24	7
61V	28351-1	3/4"	LB Set Screw	Grey		18	7.5
62V	28352-8	1"	LB Set Screw	Grey		16	9
63V	28353-5	1-1/4"	LB Set Screw	Grey		8	5.5
64V	28354-2	1-1/2"	LB Set Screw	Grey		8	6
65V	28355-9	2"	LB Set Screw	Grey		2	5.5
<b>Boxed</b>							
66	71735-1	2-1/2"	LB Set Screw	Grey		1	4.5
67	71740-5	3"	LB Set Screw	Grey		1	5
68	71745-0	3-1/2"	LB Set Screw	Grey		1	9.5
69	71750-4	4"	LB Set Screw	Grey		1	8.5

### Type T – Combo both Threaded and Set Screw Aluminum Conduit Bodies

For rigid or thinwall (EMT) conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
D700V	19543-2	1/2"	T Threaded	Grey		16	5
D701V	19544-6	3/4"	T Threaded	Grey		12	5.5
D702V	19546-3	1"	T Threaded	Grey		14	9
D703V	19547-0	1-1/4"	T Threaded	Grey		4	7.5
D704V	19548-7	1-1/2"	T Threaded	Grey		4	6.5
D705V	19549-4	2"	T Threaded	Grey		2	5.5

### Type T – Threaded Aluminum Conduit Bodies

For rigid conduit

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
700V	28390-0	1/2"	T Threaded	Grey		16	5
701V	28391-7	3/4"	T Threaded	Grey		14	5.5
702V	28392-4	1"	T Threaded	Grey		12	9
703V	28393-1	1-1/4"	T Threaded	Grey		4	7.5
704V	28394-8	1-1/2"	T Threaded	Grey		4	6.5
705V	28395-8	2"	T Threaded	Grey		2	5.5
<b>Boxed</b>							
706	71635-4	2-1/2"	T Threaded	Grey		1	5.5
707	71640-8	3"	T Threaded	Grey		1	6.5
708	71645-3	3-1/2"	T Threaded	Grey		1	10
709	71650-7	4"	T Threaded	Grey		1	9

## Conduit Bodies – Die Cast Metal

### Type T – Set Screw Aluminum Conduit Bodies

For thinwall (EMT) conduit

CG= Cover & Gasket (BULK PAK)  
CGV= Cover & Gasket (VIEW PAK)

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
70V	28360-3	1/2"	T Set Screw	Grey		16	5
71V	28361-0	3/4"	T Set Screw	Grey		14	5.5
72V	28362-7	1"	T Set Screw	Grey		12	9
73V	28363-4	1-1/4"	T Set Screw	Grey		4	7.5
74V	28364-1	1-1/2"	T Set Screw	Grey		4	6.5
75V	28365-8	2"	T Set Screw	Grey		2	5.5
<b>Boxed</b>							
76	19558-6	2-1/2"	T Set Screw	Grey		1	5.5
77	19559-3	3"	T Set Screw	Grey		1	6.5
78	19560-9	3-1/2"	T Set Screw	Grey		1	10
79	19561-6	4"	T Set Screw	Grey		1	9



70V

## Conduit Body Covers – Stamped & Die Cast Metal

### Stamped Aluminum Conduit Body Covers

Screws included

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
SC-1V	31161-0	1/2"	Stamped	Grey		100	5.5
SC-2V	31162-7	3/4"	Stamped	Grey		100	7
SC-3V	31163-4	1"	Stamped	Grey		50	8
SC-4V	31164-1	1-1/4" - 1-1/2"	Stamped	Grey		50	8.5
SC-5V	31165-8	2"	Stamped	Grey		25	7
<b>Boxed</b>							
SC-1	73105-0	1/2"	Stamped	Grey		250	14.5
SC-2	73110-4	3/4"	Stamped	Grey		250	18.5
SC-3	73115-9	1"	Stamped	Grey		250	23
SC-4	73120-3	1-1/4" - 1-1/2"	Stamped	Grey		50	8.5
SC-5	73130-2	2"	Stamped	Grey		75	21
<b>Show Pak</b>							
DC-1V	28497-6	1/2"	Die Cast	Grey		100	7
DC-2V	28498-3	3/4"	Die Cast	Grey		50	4.5
DC-3V	28499-0	1"	Die Cast	Grey		50	6
DC-4V	28500-3	1-1/4" - 1-1/2"	Die Cast	Grey		50	8.5
DC-5V	31150-4	2"	Die Cast	Grey		25	10
<b>Boxed</b>							
DC-1	72805-0	1/2"	Die Cast	Grey		250	15
DC-2	72810-4	3/4"	Die Cast	Grey		250	30
DC-3	72815-9	1"	Die Cast	Grey		250	37
DC-4	72820-3	1-1/4" - 1-1/2"	Die Cast	Grey		50	13
DC-5	72825-8	2"	Die Cast	Grey		75	34
DC-6	72835-7	2-1/2" - 3"	Die Cast	Grey		10	8
DC-7	72840-1	3-1/2" - 4"	Die Cast	Grey		5	7



SC-1V



DC-1V

## Conduit Body Covers – Stamped & Die Cast Metal

### Standard Conduit Body Gaskets – Fiber & Neoprene




NG-1V

BWF#	Unit UPC 0-87115	Conduit Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
NG-1V	31156-6	1/2"	Neoprene	Grey	Grey	500	9
NG-2V	31157-3	3/4"	Neoprene	Grey	Grey	500	10
NG-3V	31158-0	1"	Neoprene	Grey	Grey	500	13
NG-4V	31159-7	1-1/4" – 1-1/2"	Neoprene	Grey	Grey	200	11.5
NG-5V	31160-3	2"	Neoprene	Grey	Grey	100	8.5
<b>Boxed</b>							
NG-1	33627-9	1/2"	Neoprene	Grey	Grey	2500	27
NG-2	33628-6	3/4"	Neoprene	Grey	Grey	1000	13
NG-3	33629-3	1"	Neoprene	Grey	Grey	500	11
NG-4	33626-2	1-1/4" – 1-1/2"	Neoprene	Grey	Grey	500	19.5
NG-5	33630-9	2"	Neoprene	Grey	Grey	125	11
NG-6	33631-6	2-1/2" – 3"	Neoprene	Grey	Grey	50	9
NG-7	33632-3	3-1/2" – 4"	Neoprene	Grey	Grey	10	2


### Type LB Dimensions - Threaded & Set Screw

Conduit Size	A	B	C	D	E	F
1/2"	1-11/32"	15-7/64"	1/2"	2-11/64"	4-13/32"	1-5/32"
3/4"	1-35/64"	4-49/64"	3/4"	2-7/16"	5-1/8"	1-3/8"
1"	1-3/4"	5-3/8"	1"	2-3/4"	5-15/16"	1-23/32"
1-1/4"	2-35/64"	7-15/64"	1-1/4"	3-35/64"	7-7/8"	2-15/64"
1-1/2"	2-19/32"	7-17/64"	1-1/2"	3-23/32"	7-7/8"	2-3/8"
2"	3-13/64"	9-33/64"	2"	4-1/4"	10-15/64"	2-29/32"
2-1/2"	4-1/2"	12-3/16"	2-1/2"	5-5/32"	12-3/4"	3-13/32"
3"	4-15/32"	12-17/64"	3"	5-21/32"	12-43/64"	4-1/64"
3-1/2"	5-39/64"	5-1/32"	3-1/2"	6-61/64"	15-35/64"	5-5/32"
4"	5-39/64"	15-1/32"	4"	6-61/64"	15-35/64"	5-5/32"




### Type C Dimensions - Threaded & Set Screw

Conduit Size	A	B	C	D	E	F
1/2"	1-5/16"	3-27/32"	1/2"	1-1/2"	4-27/32"	1-1/8"
3/4"	1-17/32"	4-19/32"	3/4"	1-5/8"	5-41/64"	1-5/16"
1"	1-3/4"	5-11/32"	1"	1-29/32"	6-1/2"	1-1/2"
1-1/4"	2-17/32"	7-1/4"	1-1/4"	2-3/4"	8-1/2"	2-1/4"
1-1/2"	2-17/32"	7-1/4"	1-1/2"	2-3/4"	8-1/2"	2-1/4"
2"	2-7/32"	9-7/16"	2"	3-13/32"	10-3/4"	2-3/4"
2-1/2"	4-1/2"	12-1/4"	2-1/2"	4-1/2"	13"	4-1/2"
3"	4-1/2"	12-1/4"	3"	4-1/2"	13"	4-1/2"
3-1/2"	5-1/2"	15"	3-1/2"	5-9/16"	16-5/16"	5-1/2"
4"	5-1/2"	15"	4"	5-9/16"	16-5/16"	5-1/2"




### Type LL Dimensions - Threaded & Set Screw

Conduit Size	A	B	C	D	E	F
1/2"	1-3/32"	3-7/8"	1/2"	2"	4-9/32"	1-13/32"
3/4"	1-1/4"	4-21/32"	3/4"	2-11/32"	5-1/8"	1-13/32"
1"	1-1/2"	5-23/64"	1"	2-1/2"	5-59/64"	1-7/8"
1-1/4"	2-1/4"	7-17/64"	1-1/4"	3-13/32"	7-55/64"	2-7/8"
1-1/2"	2-1/4"	7-17/64"	1-1/2"	3-13/32"	7-55/64"	2-7/8"
2"	2-3/4"	9-15/32"	2"	3-27/32"	10-13/64"	3-27/64"
2-1/2"	4-5/8"	12-1/4"	2-1/2"	5-3/4"	13"	4-1/2"
3"	4-5/8"	12-1/4"	3"	5-3/4"	13"	4-1/2"
3-1/2"	5-7/16"	15"	3-1/2"	6-1/8"	16-5/16"	5-9/16"
4"	5-7/16"	15"	4"	6-1/8"	16-5/16"	5-9/16"




### Type LR Dimensions - Threaded & Set Screw

Conduit Size	A	B	C	D	E	F
1/2"	1-7/64"	3-7/8"	1/2"	2"	4-9/32"	1-13/32"
3/4"	1-1/4"	4-21/32"	3/4"	2-11/32"	5-1/8"	1-41/64"
1"	1-1/2"	5-23/64"	1"	2-1/2"	5-59/64"	1-7/8"
1-1/4"	2-1/4"	7-17/64"	1-1/4"	3-13/32"	7-55/64"	2-7/8"
1-1/2"	2-1/4"	7-17/64"	1-1/2"	3-13/32"	7-55/64"	2-7/8"
2"	2-3/4"	9-15/32"	2"	3-27/32"	10-13/64"	3-27/64"
2-1/2"	4-7/16"	12-1/4"	2-1/2"	5-13/16"	12-1/4"	4-1/2"
3"	4-5/8"	12-1/4"	3"	5-13/16"	12-1/4"	4-1/2"
3-1/2"	5-7/16"	15"	3-1/2"	6-1/8"	15"	6-1/4"
4"	5-7/16"	15"	4"	6-1/8"	15"	6-1/4"



### Type T Dimensions - Threaded & Set Screw

Conduit Size	A	B	C	D	E	F
1/2"	1-5.16"	3-27.32"	1.2"	1-3.8"	4-27.32"	2-1.16"
3/4"	1-17.16"	4-39.64"	3.4"	1-41.64"	5-19.32"	2-11.32"
1"	1-25.32"	5-3.8"	1"	1-29.32"	6-1.2"	2-19.32"
1-1/4"	2-1.2"	7-1.4"	1-1.4"	2-3.4"	8-1.2"	3-35.64"
1-1/2"	2-1.2"	7-1.4"	1-1.2"	2-3.4"	8-1.2"	3-35.64"
2"	3-1.4"	9-7.16"	2"	3-27.64"	10-13.16"	4-3.64"
2-1/2"	4-1.2"	12-1.4"	2-1.2"	4-1.2"	13"	5-25.32"
3"	4-1.2"	12-1.4"	3"	4-1.2"	13"	5-25.32"
3-1/2"	5-1/2"	15"	3-1/2"	5-9/16"	16-5/16"	6-13/16"
4"	5-1/2"	15"	4"	5-9/16"	16-5/16"	6-13/16"



## Service Entrance Heads

### Service Entrance Heads – Clamp Type



BWF#	Unit UPC 0-87115	Pipe Size	Type	Description	Color	Case Qty.	Case Weight
<b>Show Pak</b>							
180V	75905-4	1/2"	Clamp		Grey	25	12
181V	75910-8	3/4"	Clamp		Grey	20	11.5
182V	75915-3	1"	Clamp		Grey	20	8
183V	75920-7	1-1/4"	Clamp		Grey	10	5.5
184V	75925-2	1-1/2"	Clamp		Grey	8	7
185V	75930-6	2"	Clamp		Grey	3	5
<b>Boxed</b>							
1866	70935-6	2-1/2"	Clamp		Grey	1	4.5
2877	70932-5	3"	Clamp		Grey	1	7
2888	70945-5	3-1/2"	Clamp		Grey	1	6.5
2899	70950-9	4"	Clamp		Grey	1	6.5

### Service Entrance Heads – Threaded Type



BWF#	Unit UPC 0-87115	Pipe Size	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>							
8160	08160-5	1/2"	Threaded		Grey	50	12
8161	08161-2	3/4"	Threaded		Grey	25	11.5
8162	08162-9	1"	Threaded		Grey	10	8
8163	08163-6	1-1/4"	Threaded		Grey	10	8
8164	08164-3	1-1/2"	Threaded		Grey	10	8
8165	08165-0	2"	Threaded		Grey	5	8

### Service Entrance Heads – Mast Type



BWF#	Unit UPC 0-87115	Pipe Size	Head Size	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>							
9366	09366-0	2"	1-1/4"		Grey	4	3
9367	09367-7	2-1/2"	1-1/4"		Grey	2	2
9368	09368-4	2-1/2"	2"		Grey	2	2

### Oval Service Cable Heads



BWF#	Unit UPC 0-87115	Trade Size	Case Qty.	Case Weight
<b>Boxed</b>				
9364	09364-6	3/8 - 1/3	5	1.4
9365	09365-3	1/0-4/0	5	3.3

## Electrical Fittings

### Insulated Bushing

BWF#	Unit UPC 0-87115	Pipe Size	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>							
171	09003-4	1/2"	Insulated	Grey	Grey	1000	6.5
172	70710-9	3/4"	Insulated	Grey	Grey	1000	8
173	70715-4	1"	Insulated	Grey	Grey	500	7.5
174	70720-8	1-1/4"	Insulated	Grey	Grey	250	6
175	70725-3	1-1/2"	Insulated	Grey	Grey	250	6.5
176	70730-7	2"	Insulated	Grey	Grey	125	5
177	70735-2	2-1/2"	Insulated	Grey	Grey	100	6.5
178	70740-6	3"	Insulated	Grey	Grey	50	5
179	70745-1	3-1/2"	Insulated	Grey	Grey	50	6
170	70750-5	4"	Insulated	Grey	Grey	50	6



171

### Steel Lock Nuts

BWF#	Unit UPC 0-87115	Pipe Size	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>							
131	70805-2	3/8"	Steel	Grey	Grey	2500	44
132	70810-6	1/2"	Steel	Grey	Grey	2500	33.5
133	70815-1	3/4"	Steel	Grey	Grey	2500	48
134	70820-5	1"	Steel	Grey	Grey	1000	33.5
149	70825-0	1-1/4"	Steel	Grey	Grey	500	27
150	70830-4	1-1/2"	Steel	Grey	Grey	500	26.5
151	70835-9	2"	Steel	Grey	Grey	400	29
152	70840-3	2-1/2"	Steel	Grey	Grey	300	39.5
153	70845-8	3"	Steel	Grey	Grey	250	44.5
154	70850-2	3-1/2"	Steel	Grey	Grey	125	27.5
155	70855-7	4"	Steel	Grey	Grey	100	27.5
156	70860-1	5"	Steel	Grey	Grey	30	23.5
157	70865-6	6"	Steel	Grey	Grey	30	26.5



131

### Ground Fittings

BWF#	Unit UPC 0-87115	Pipe Size	Type	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>							
L-162C	73205-7	1/2" - 1-1/4"	#4 -#10 AWG	Zinc	Zinc	250	43
L-162-B	73210-1	1/2" - 1-1/4"	Grounding wire	Brass	Brass	250	43
L-163C	73215-6	1/2" - 1-1/4"	#4 -#8 AWG	Zinc	Zinc	250	50
L-163B	73220-0	1/2" - 1-1/4"	Bare amored wire	Brass	Brass	250	50



L-163C



L-162C

## Replacement Parts & Accessories

BWF#	Unit UPC 0-87115	Description	Color	Case Qty.	Case Weight
<b>Boxed</b>					
ML	21020-3	2 Mounting Lugs w/screws	Grey	100	1
RS	30030-0	Porcelain Replacement Socket	Grey	25	3
S11	33593-7	Single Pole 10A/125V Switch	Black	50	15
S13	37030-3	Three Way 10A/125V Switch	Black	50	15
S15	37031-0	Single Pole 20A-120V/277V	Black	50	15
<b>Show Pak</b>					
GV	31166-5	2 pk of Internal Lampholder Gasket	Black	600	2
G-1V	41300-0	External Lampholder Gasket	Black	50	3
UBGV	37020-4	Universal 1 Gang Gasket	Black	50pks	2
RGV	37040-2	Unviersal Round Gasket	Black	50pks	1
BGV	27229-4	1 Gang Gasket, Single & Duplex Cvr	Black	50pks	1
TGBGV	27230-0	Universal 2 Gang Gasket	Black	50pks	1
<b>Closure Plugs</b>					
PL-5/4V	05400-5	4 – 1/2" Closure Plugs	Grey	75pks	6
PL-5/4AV	05403-6	4 – 1/2" Closure Plugs	Bronze	75pks	6
PL-5/4WV	05402-9	4 – 1/2" Closure Plugs	White	75pks	6
PL-75/4V	21012-8	4 – 3/4" Closure Plugs	Grey	50/pks	6
PL-75/4AV	27220-1	4 – 3/4" Closure Plugs	Bronze	50/pks	6
PL-75/4WV	27221-8	4 – 3/4" Closure Plugs	White	50/pks	6
PL/10/4V	27223-2	4 – 1" Closure Plugs	Grey	50/pks	9
PL/10/4/AV	27224-9	4 – 1" Closure Plugs	Bronze	50/pks	9
PL/10/4/WV	27225-6	4 – 1" Closure Plugs	White	50/pks	9
<b>Blister Carded</b>					
50AP-1	05012-0	3 – 1/2" Plugs, 2 Wire Nuts	Grey	12	1
50APAB-1	05016-8	3 – 1/2" Plugs, 2 Wire Nuts	Bronze	12	1
50APW-1	50195-0	3 – 1/2" Plugs, 2 Wire Nuts	White	12	1
75AP-1	07512-3	3 – 3/4" Plugs, 2 Wire Nuts	Grey	12	1.5
75APAB-1	07516-1	3 – 3/4" Plugs, 2 Wire Nuts	Bronze	12	1.5
75APW-1	50200-1	3 – 3/4" Plugs, 2 Wire Nuts	White	12	1.5



# NEW

## NEW PRODUCTS

As Teddico/BWF continues to grow to meet its customers needs, we are also expanding our lines in order to simplify your customers' ordering . We would like to be your one-stop shop. Please take this time to explore the new products that we will soon be offering in your area.

## LESS COMPLICATED

We offer both weatherproof , fittings and lighting products so that you can get your orders filled in one place.

## MORE PRODUCTS TO COME

We plan to continue to grow our lines and expand our offerings to be sure we have what you need for your business and your customers.

To Order Contact:

TEDDICO / BWF  
ELECTRICAL PRODUCTS

1104 PARKWAY VIEW DR  
PITTSBURGH, PA 15205

PHONE: 412-747-4970

FAX: 412-747-4973

WWW.TEDDICOBWF.COM



2 GANG LOCKABLE VERTICAL COVER

SINGLE GANG LOCKABLE VERTICAL COVER



SINGLE GANG LOCKABLE HORIZONTAL COVER



### MULTIPLE USE LOCKABLE COVERS

- The **Single Gang Cover** version replaces 3 types of covers all in one convenient and versatile part while the two gang version replaces 6 variables of the same covers. They replace the GFI Covers, Single Receptacle Covers & Duplex Covers. All are equipped with lockable Hasp.
- They are available in 3 colors: Grey, Bronze and White. This innovative new part has interchangeable inserts that allow you to convert it from one receptacle type to another.
- With these new Covers you will save space and have more shelf room for display area. You will also be able to offer your customer a more versatile part with which they can complete their electrical projects.

Single Gang Vertical

3

CONFIGURATIONS

Make Any of These Configurations:



Single Gang Horizontal

3

CONFIGURATIONS

Make Any of These Configurations:




2 Gang Vertical

6

CONFIGURATIONS

Make Any of These Configurations:





*A Leading Manufacturer of Weatherproof Electrical Products*