

Push Buttons

Low Voltage

600 Series

These low voltage, panel mount push buttons feature large terminals and normally open momentary contacts. Models with an illuminated center for use in unlighted areas are available. They may be used with the 147-1 mounting plate or 147-10 room annunciator mounting plate.

Features and Specifications

- Polished chrome or brass
- Insulated for mounting on metal cabinets
- Snap fit
- Normally open momentary contacts
- Illuminated and non-illuminated models



Ordering Information								
Description	Cat. No.	Switching Voltage	Current		Finish		Hole Size	Hole Depth
			DC	AC	Rim	Center		
Non-Illuminated Push Buttons	620	8V	2.0 A	2.0 A	Chrome	White	5/8" (16mm)	3/4" (19mm)
		24V	0.5 A	0.67 A				
		48V	0.3 A	0.3 A				
	621 ¹	8V	2.0 A	2.0 A	Chrome	White	5/8" (16mm)	3/4" (19mm)
		24V	0.5 A	0.67 A				
		48V	0.3 A	0.3 A				
	620-B	8V	2.0 A	2.0 A	Brass	White	5/8" (16mm)	3/4" (19mm)
		24V	0.5 A	0.67 A				
		48V	0.3 A	0.3 A				
	621-B ¹	8V	2.0 A	2.0 A	Brass	White	5/8" (16mm)	3/4" (19mm)
		24V	0.5 A	0.67 A				
		48V	0.3 A	0.3 A				
Illuminated Push Buttons	620-L	6 -16V AC	-	-	Chrome	White	5/8" (16mm)	3/4" (19mm)
	620-LB	6 -16V AC	-	-	Brass	White	5/8" (16mm)	3/4" (19mm)

¹500 Unit Bulk Pack

Accessories	
Description	Cat. No.
Mounting Plate	147-1
Room Annunciator Mounting Plate	147-10

Weights and Dimensions		
Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
620	0.01	0.03
621	8.00	9.50
620-B	0.02	0.05
621-B	7.80	9.26
620-L	0.02	0.05
620-LB	0.02	0.05
147-1	0.12	0.15
147-10	0.12	0.15



Push Buttons

Low Voltage

600 Series

These low voltage, panel mount push buttons feature large terminals and normally open momentary contacts. Models with an illuminated center for use in unlighted areas are available. They may be used with the 147-1 mounting plate or 147-10 room annunciator mounting plate.

Features and Specifications

- Polished chrome or brass
- Insulated for mounting on metal cabinets
- Snap fit
- Normally open momentary contacts
- Illuminated and non-illuminated models



Ordering Information								
Description	Cat. No.	Switching Voltage	Current		Finish		Hole Size	Hole Depth
			DC	AC	Rim	Center		
Non-Illuminated Push Buttons	620	8V	2.0 A	2.0 A	Chrome	White	5/8" (16mm)	3/4" (19mm)
		24V	0.5 A	0.67 A				
		48V	0.3 A	0.3 A				
	621 ¹	8V	2.0 A	2.0 A	Chrome	White	5/8" (16mm)	3/4" (19mm)
		24V	0.5 A	0.67 A				
		48V	0.3 A	0.3 A				
	620-B	8V	2.0 A	2.0 A	Brass	White	5/8" (16mm)	3/4" (19mm)
		24V	0.5 A	0.67 A				
		48V	0.3 A	0.3 A				
	621-B ¹	8V	2.0 A	2.0 A	Brass	White	5/8" (16mm)	3/4" (19mm)
		24V	0.5 A	0.67 A				
		48V	0.3 A	0.3 A				
Illuminated Push Buttons	620-L	6 -16V AC	-	-	Chrome	White	5/8" (16mm)	3/4" (19mm)
	620-LB	6 -16V AC	-	-	Brass	White	5/8" (16mm)	3/4" (19mm)

¹500 Unit Bulk Pack

Accessories	
Description	Cat. No.
Mounting Plate	147-1
Room Annunciator Mounting Plate	147-10

Weights and Dimensions		
Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
620	0.01	0.03
621	8.00	9.50
620-B	0.02	0.05
621-B	7.80	9.26
620-L	0.02	0.05
620-LB	0.02	0.05
147-1	0.12	0.15
147-10	0.12	0.15

