ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LU100HEC0 100W ED23.5 High Pressure Sodium White Mogul Base

Ge By Current Lamps

Catalog Number	LU100HEC0
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 100 WTT, 2.1 Amp, 9500 LM, 2000 KV, 22 Cri, Mogul Screw (E39) Base, 24000 HR Average Life
Weight per unit	0.3800 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

amperage rating	2.1
average life	24000.0
Base	Mogul Screw (E39)
lumens	9500.0
Wattage	100.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
color temperature	2000.0
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	100W ED23.5 HIGH PRESSURE SODIUM WHITE MOGUL BASE
extra long description	GEL LU100/H/ECO 85369 LUCALOX
Long Description	GE Ecolux®, 100 WTT, 2.1 AMP, 9500 LM, 2000 KV, 22 CRI, Mogul Screw (E39) Base, 24000 HR Average Life
Product Type	85369 Lucalox
Special Features	7.75IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168853699
Manufacturers Part Number	LU100/H/ECO
UPC	043168853699

Taxonomies, Classifications, and Categories

Category Description	SODIUM

Packaging

Carton	1
Package	12
Weight Per each	0.38

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Universal burning position