Specifications

Eaton QC3040H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker,Industrial circuit breaker,40 A,10 kAIC,Three-pole,240 V,Thermal-magnetic,QC,Non-interchangeable

General specifications	
PRODUCT NAME	Eaton QC thermal magnetic circuit breaker
CATALOG NUMBER	QC3040H
UPC	786679240144
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.9 in
PRODUCT WIDTH	3.1 in
PRODUCT WEIGHT	1.2 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified

Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QC
NUMBER OF POLES	Three-pole
TYPE	Industrial circuit breaker

Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	T268
VOLTAGE RATING	240 V - 240 V

Miscellaneous

OPTIONS	Non-interchangeable

Resources

CATALOGS	Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QC3040H

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.