

# Eaton UHTRS101BE

Catalog Number: UHTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UHTRS101BE

### UPC

786685217734

### Product Length/Depth

3.61 in

### Product Height

11.05 in

### Product Width

8.22 in

### Product Weight

6.7 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

Single-position residential service

### Amperage Rating

125A

### Feed type

Overhead

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

NY : Central Hudson Gas & Electric (CHG&E)

OH : Dayton Power and Light (DP&L)

MD : First Energy (Potomac Edison)

VA : First Energy (Potomac Edison)

WV : First Energy (Mon Power)

NJ : First Energy (Jersey Central Power and Light)

OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company)

PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power)

WI : Madison Gas and Electric (MGE)

IN : Northern Indiana Public Service Company (NIPSCO)

WI : WE Energies / Wisconsin Public Service (WPS)

NY : Rochester Gas & Electric (RG&E)

NY : New York State Electric & Gas (NYSEG)

### Line

#8-2/0 AWG

### Load

#8-2/0 AWG

### Number of wires

Three-wire

### Hub type

3-5/16 in hub opening

### Security

Ringless

### Voltage rating

600 V

## Resources

### Brochures

Single Meter Sockets

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - METER SOCKET UHTRH101(X)E 125AMP, 1 ø OH/UG, HORN BYPASS RINGLESS STYLE, HBP

### Specifications and datasheets

Eaton Specification Sheet - UHTRS101BE

Bypass

Horn

Number of sockets

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)