

VDV Scout™ Pro Series

VDV SCOUT™ PRO LT / VDV SCOUT™ PRO




**TESTS VOICE,
DATA & VIDEO
CONNECTIONS**

**KLEIN
TOOLS®**

- Tests continuity on voice, data and video connections.


VDV Scout™ Pro Series

MEASURES CABLE LENGTH



- Simultaneous testing of video and data cables saves time and improves efficiency.

- Includes location ID remotes for locating cable runs to wall outlets.



RJ45 Remotes

F-Connector Remotes

- Integrated tone generator supports multiple tones and control of pins carrying tone.

- Removable F to F Barrel Connector

- Extra Large 2.4 inch Display



Self Storing Remote



RJ45, F-Connector and RJ11/12 Jacks



VDV Scout™ Pro LT Tester Kit*

Kit Includes:

- VDV Scout™ Pro LT Tester
- 19 location RJ45 remotes
- 19 location F-Connector remotes
- 1 F to F Barrel Connector
- 1 Carrying Case

*Measures cable length

Cat. No.	Battery	Height	Width	Depth	Weight with Battery (oz.)
VDV501-814	9V alkaline included	6.3" (160 mm)	2.8" (71.2 mm)	1.70" (43.2 mm)	10 (283 g)
with case		11.5" (292 mm)	8.75" (222 mm)	2.25" (64 mm)	30 (850 g)

VDV Scout™ Pro LT Tester Starter Kit*

Kit Includes:

- VDV Scout™ Pro LT Tester
- 5 location RJ45 remotes
- 5 location F-Connector remotes
- 1 F to F Barrel Connector

*Measures cable length

Cat. No.	Battery	Height	Width	Depth	Weight with Battery (oz.)
VDV501-816	9V alkaline included	6.3" (160 mm)	2.8" (71.2 mm)	1.70" (43.2 mm)	10 (283 g)

Features

Feature	Scout™ Pro LT Tester Kit VDV501-814	Scout™ Pro LT Tester Starter Kit VDV501-816	Scout™ Pro Tester Kit VDV501-809
RJ-45 8-wire Cables	●	●	●
RJ-11/12 6-wire Cables	●	●	●
F-connector Coax Cables	●	●	●
Continuity Testing	●	●	●
Measures Cable Length	●	●	●
Pass TIA-568A/B & Crossover/Uplink	●	●	●
LCD LCD Display	●	●	●
Wiremap	●	●	●
Open Fault	●	●	●
Short Fault	●	●	●
Miswire Fault	●	●	●
Split Pair Fault	●	●	●
ID Cable Identification – Locations Included	19	5	5
Multiple Style Tone Generator	●	●	●
Apo Auto Power Off	●	●	●
Low Battery	●	●	●
Voltage Warning	●	●	●
Shield Detection	●	●	●
Self-Storing Remote	●	●	●
Carrying Case	●	● sold separately	● sold separately

VDV Scout™ Pro Tester Kit†

Kit Includes:

- VDV Scout™ Pro Tester
- 5 location RJ45 remotes
- 5 location F-Connector remotes
- 1 F to F Barrel Connector

†Does not measure cable length

Cat. No.	Battery	Height	Width	Depth	Weight with Battery (oz.)
VDV501-809	9V alkaline included	6.3" (160 mm)	2.8" (71.2 mm)	1.70" (43.2 mm)	10 (283 g)



VDV Scout™ Pro™ Accessories

LanMap™ Kit for VDV Scout™ Pro Testers

- Identify and map twisted-pair infrastructure (RJ45), up to 19 locations.
- For use with VDV Scout™ Pro Testers (Cat. No. VDV501-053, VDV501-809, VDV501-068, VDV501-814, VDV501-816).
- Heavy-duty design for long life and repeated connections.
- Remotes numbered 1 through 19 for fast and accurate identification.

Cat. No.	Height	Width	Depth	Weight (oz.)
VDV526-055	3.0" (76 mm)	3.3" (84 mm)	1.4" (36 mm)	1.9 (56 g)



VDV526-055

CoaxMap™ Kit for VDV Scout™ Pro Testers

- Identify and map coaxial cable infrastructure (F-Connector), up to 19 locations.
- For use with VDV Scout™ Pro Testers (Cat. No. VDV501-053, VDV501-809, VDV501-068, VDV501-814, VDV501-816).
- Heavy-duty design for long life and repeated connections.
- Remotes numbered 1 through 19 for fast and accurate identification.

Cat. No.	Height	Width	Depth	Weight (oz.)
VDV512-056	3.0" (76 mm)	3.3" (84 mm)	1.0" (26 mm)	5.2 (148 g)



VDV512-056

Carrying Case for VDV Scout™ Pro

- Designed for use with:
 - VDV Scout Pro Tester (VDV501-053, VDV501-809)
 - VDV Scout Pro LT Tester (VDV501-068, VDV501-814, VDV501-816)
 - CoaxMap™ Kit (VDV512-056)
 - LanMap™ Kit (VDV526-055)
- Custom designed compartments hold tester and accessories securely.
- EVA foam cushions and protects.
- Extra cavities for additional accessories.
- Products not included.



(Products not included)



VDV770-080

Cat. No.	Height	Width	Depth	Weight (oz.)
VDV770-080	11.5" (292 mm)	8.75" (222 mm)	2.25" (57 mm)	15 (425 g)

PROBEplus – Tone Tracing Probe

- Trace wire paths and identify cables in common wiring systems.
- Amplifier overload LED improves accuracy, warning against misreads.
- Dual mode power button with Power-On LED indicator – tap or hold.
- Recessed buttons prevent accidental operation.
- Designed for use with Klein Tools VDV test tools (Cat. No. VDV500-051, VDV526-054, VDV526-052, VDV501-053, VDV501-809, VDV501-068, VDV501-814, VDV501-816).
- Works with many other manufacturers' analog tone generators.
- Replacement tips available (Cat. No. VDV999-065).



VDV500-060



Cat. No.	Battery	Battery Life	Height	Width	Depth	Weight (oz.) with out battery
VDV500-060	9V	25 hours active 4 years standby	9.9" (252 mm)	2.0" (50 mm)	1.14" (29 mm)	4.4 (112 g) 6.0 (152 g)

▲WARNING: Read, understand and follow all instructions, cautions and warnings attached to and/or packed with all test and measurement devices before each use.

Features	VDV500-060
O.L. Amplifier Overload Indication	●
 — Adjustable digital volume control	●
↔ Tap-Mode Operation	●
⏸ Hold-Mode Operation	●
💡 Power-On LED Indicator	●
👁 Visual Notification	●
Apo Auto Power-Off	●
🔋 Low Battery Indicator	●
🔧 Replaceable Tip	●
🪄 Lanyard Attachment Loop	●