# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## 1R4023 23W CFL R40 Med BS 27K 1150LM

*Technical Consumer Prod.*

| | |
|---|---|
| Catalog Number | 1R4023 |
| Manufacturer | Technical Consumer Prod. |
| Description | Compact Fluorescent Floodlight, R40 Bulb Shape, 6.2 In Length, 4.7 In (Dia.) Width, 120 V Ac, 23 W, Electronic Ballast, White, E26 Base, 2700 K, 82, 1150 LM Brightness (Lumens), 120 ° Beam Angle, 0.38 A, Stainless Steel Housing Material, +160 °F (Maximum) |
| Weight per unit | 0.6800 (lbs/each) |
| Product Category | Fluorescent Floodlights |

### Features

| | |
|---|---|
| amperage rating | 380m A |
| average life | 8000 K |
| Base | E26 |
| Fixture Type | Any IN |
| lumens | 1.15k lm |
| Shape | R40 |
| start type | Instant |
| total harmonic distortion | <100 percent |
| Wattage | 23 W W |

### Material, Color, and Finish

| | |
|---|---|
| color rendering index (cri) | 82 W |

### Dimensions and Weight

| | |
|---|---|
| Diameter | 4.70 inches |
| Length | ROCKER DIMMER, WALL DIMMER TYPE; LIGHT ALMOND FINISH; 3-WAY OPERATION TYPE; UL, CSA APPROVAL; 120 VAC VOLTAGE RATING; 600 W LOAD RATING; ROCKER SWITCH, SIDE SLIDE OPERATOR TYPE; DECORATOR WALL PLATE TYPE; INCANDESCENT LOAD TYPE; TRADESELECT[R] BRAND |

### Descriptions

| | |
|---|---|
| Description | 23W CFL R40 MED BS 27K 1150LM |
| extra long description | TCP 1R4023 23W R40 |

### Manufacturer Information

| | |
|---|---|
| GTIN | 00762148140238 |
| sub brand | CFL Reflectors |
| UPC | 762148140238 |

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Fluorescent |
| Type | R40 |

## Availability

| | |
|---|---|
| Manufacturer Status | Inactive |

## Packaging

| | |
|---|---|
| Carton | 12 |
| Package | 1 |
| Weight Per each | 0.68 |

## Uses, Certifications, and Standards

| | |
|---|---|
| standard | UL and cUL Compliant |