ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

24GR4240D 2X4 Led Lensed Troffer 40K 4200LM

Cooper Lighting Solutions

Catalog Number	24GR4240D
Manufacturer	Cooper Lighting Solutions
Description	Lensed Led Troffer, 277 V Ac, 0.108 A @ 277 V, 30 W, Cold Rolled Steel, Iron Phosphate, 4000 K, 80, >60000 H Average Life, Dimmable, 4200 LM Brightness (Lumens), 47-15/16 In Length, 23-3/4 In Width, 3-1/4 In Height, 20 LB
Weight per unit	27.1 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

amperage rating	0.108 at 277V
Ballast Type	N/A
Lamp Type	LED
Number of Lamps	1

Material, Color, and Finish

Style	(blank)

Descriptions

Description	2X4 LED LENSED TROFFER 40K 4200LM
extra long description	CLS 24GR4240D 24 A LENS LED TR 4200

Manufacturer Information

Brand	METALUX
GTIN	00080083755370
UPC	080083755370

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Recessed Static

Packaging

Carton	1
Weight Per each	27.1

Uses, Certifications, and Standards

Mounting	Surface Mount
standard	UL Recognized;cUL Listed;RoHS Compliant;DLC Qualified