ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



3010 120V 1500W SPST FLUSH MOUNTING W/PLATE

NSI INDUSTRIES

Catalog Number	3010
Manufacturer	NSI INDUSTRIES
Description	Flush Mount, 120 V ac, 1500 W, 1 in Width, 2 in Height, Lexan Housing Material, SPST Switch Type, Cadmium Coated CDS Photocell Sensor, -40 °F Operating Temperature, +140 °F Operating Temperature, Flush Mount, 0.3 lb/EA
Weight per unit	0.3000 (lbs/each)
Product Category	Lighting Photocells

Features

Fixture Type	Photocell Sensor
Mounting Type	Wall
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120
Warranty	1-year Limited
Dimmable	N/A
Indoor/Outdoor	Outdoor

Material, Color, and Finish

Color	Gray
Style	Utilitarian/Commodity

Dimensions and Weight

Height	5.625
Length	3

Descriptions

Description	120V 1500W SPST FLUSH MOUNTING W/PLATE
Long Description	One of the requirements for California Title 24 beginning in 2017 is that every exterior fixture must use a high efficacy source, be controlled by a photocell and be controlled by either a timer switch, motion sensor OR energy management system. The Tork 3010 remote photocell can be used to control one or multiple fixtures up to 2,000 watts.
Product Type	PTORK3010 Photo Control Wall Mount
Short Description	Photocontrol
Extra Long Description	TORK 3010 Button Flush Mount W/Plat

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Coleto Brands, Progress Lighting
	PROGRESS
GTIN	00786261600219
Manufacturers Part Number	PTORK3010
UPC	884739

Taxonomies, Classifications, and Categories

Category Description	SIGNALING EQUIPMENT

Packaging

Carton	1
Weight	0.21
Weight Per Each	0.3000 (lbs/each)