



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T122 Momentary MSHD Pushbutton Red Nonilluminated

Eaton Corp

Catalog Number	10250T122
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, 10250T, 30.5 MM, Heavy-Duty, 40 MM, Nema 3, 3R, 4, 4X, 12, 13, Non-Illuminated, Momentary, Mushroom , Red Actuator, Chrome Bezel, Plastic Actuator
Weight per unit	0.2500 (lbs/each)
Product Category	Push Button Components

Features

actuator	Mushroom
Contact Configuration	1 NO
dimensions	2.0000 IN X 1.9000 IN X 2.2000 IN
media	Yes

Dimensions and Weight

Depth	2.0000
Height	2.2000
Size	40 mm
Width	1.9000

Descriptions

Description	MOMENTARY MSHD PUSHBUTTON RED NONILLUMINATED
extra long description	ETN 10250T122 MSHD PB R
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Momentary, Mushroom , Red actuator, Chrome bezel, Plastic actuator
Product Type	MSHD PB R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113203362
Manufacturers Part Number	10250T122
Model	Pushbutton
UPC	782113203362



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description OILTIGHT OPERATORS.30MM

Type PUSHBUTTON

Packaging

Carton 1

Weight Per each 0.25

Uses, Certifications, and Standards

Application Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

standard UL Listed,CSA Certified,CE Marked