



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 10250T476 II PB 24V Full Volt W/O Lens

Eaton Corp

Catalog Number	10250T476
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, 30.5 MM, Heavy-Duty, Nema 3, 3R, 4, 4X, 12, 13, Illuminated, Three-Position, Momentary Push and Pull, Maintained Intermediate, Incandescent, Full Voltage Light Unit, 24 Vac/DC Light Unit
Weight per unit	0.2500 (lbs/each)
Product Category	Push Button Components

### Features

dimensions	1.0000 IN X 1.0000 IN X 0.8000 IN
media	Yes

### Dimensions and Weight

Size	30.5 MM
------	---------

### Descriptions

Description	IL PB 24V FULL VOLT W/O LENS
extra long description	ETN 10250T476 IL PB 24V FULL VOLT W
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Momentary push and pull, maintained intermediate, Incandescent, full voltage light unit, 24 Vac/dc light unit
Product Type	II PB 24V Full Volt W/O Lens
Special Features	10250T series

### Manufacturer Information

Brand	Eaton
GTIN	00782113226064
Manufacturers Part Number	10250T476
UPC	782113226064

### Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL Listed, CSA Certified, CE Marked