



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10844XSCHC Encl HNGD CVR Encl *Cooper B-Line/Cable Tray*

Catalog Number	10844XSCHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 10" Height, 4" Length, 8" Width, Nema 4X, Hinged Cover, 4XSCHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	6.7 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

dimensions	4.0000 IN X 8.0000 IN X 10.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	8.00 In Width X 4.00 In Depth X 10.00 In Height
------	---

Descriptions

Description	ENCL HNGD CVR ENCL
extra long description	B-LINE 1084-4XSCHC TYPE 4X SSL JIC
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 10" height, 4" length, 8" width, NEMA 4X, Hinged cover, 4XSCHC enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL Jic Continuous Hinge CVR Enc, 10X8X4
Special Features	Cont. piano hinge, panel mount prov., s.s. door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051701845
Manufacturers Part Number	1084-4XSCHC
UPC	782051701845

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	6.669

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - OtherInd Facilities & Factories - Mfg. Process Electrification and ControlCommercial / Institutional Buildings / Structures - Critical PowerInd Facilities & Factories - Facility: Safety and Security SystemsInd Facilities & Factories - Facility: Power Distribution and ControlInd Facilities & Factories - Facility: Automation and MonitoringCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsCommercial / Institutional
Mounting	EXTERNAL FEET, WALL
nema rating	4X
standard	NEMA,CSA C22.2.,UL 50