ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



# 3854 STRAIGHT BLADE RECP 50A 125/250V

*PASS & SEYMOUR/LEGRAND*

| | |
|---|---|
| Catalog Number | 3854 |
| Manufacturer | PASS & SEYMOUR/LEGRAND |
| Description | Straight Blade Receptacle, 50 A, 125/250 V ac, 3 Poles, 4 Wires, Wire Ground Connection, Wall Mount, 2.8 in Length, 2.41 in Width, 5.65 in Height, ThermoPlastic, Black, Arc Resistant, 1.18 lb |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

## Features

| | |
|---|---|
| Outlet Type | STRAIGHT BLADE |
| Poles | 3-way |
| Voltage | 125/250 V |
| Voltage Rating | 125/250 |
| Wall Plate Included | NO |
| Wire Size | 4 |
| Amperage Rating | 50 |
| Connection | Wire Ground |
| Indoor/Outdoor | Indoor |

## Dimensions and Weight

| | |
|---|---|
| Size | 5.7 in |

## Descriptions

| | |
|---|---|
| Description | STRAIGHT BLADE RECP 50A 125/250V |
| Features | Durable |
| | Straight Blade Power Outlet Surface Receptacle, Range50A 125/250V |
| Long Description | Straight Blade Power Outlet Surface Receptacle, Range50A 125/250V |
| Product Type | Straight Blade Recep 50A 125/250V |
| Special Features | Arc-resistant plastic, dead front design & double wire contact |
| Extra Long Description | PAS 3854 STRAIGHT BLADE RECEP 50A 1 |

## Manufacturer Information

| | |
|---|---|
| Brand | Pass and Seymour |
| | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007792508 |
| UPC | 785007 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Residential receptacles |
| Type | Straight Blade Receptacle |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

## Trade Size

| | |
|---|---|
| Amperage | 50.0 |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 25 |
| Weight Per Each | 1.2 (lbs/each) |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Industrial Spec Grade |
| Mounting | WALL |
| Standard | UL, UL 498 |

Pass and Seymour

# 50A 125/250V 14-50R Straight Blade Single Surface Receptacle, 3-Pole, 4-Wire

Part No. 3854




Straight Blade Power Outlet Surface Receptacle, Range50A 125/250V

## Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Black |
| UPC Number | 785007792508 | Country Of Origin | China |
| Number of Receptacles | 1 | Features | Durable |
| Outlet Type | Straight Blade | Application Sector | Multi-Dwelling Unit, Residential |
| Wall Plate Included | No | Standard | UL 498 |
| Warranty Type | 1-Year Limited Warranty | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 2.8 in | Product Depth US | 2.41 in |
| Product Height US | 5.65 in | | |

### Technical Information

| | | | |
|---|---|---|---|
| Number of Wires | 4 | Amperage | 50 A |

| | | | |
|---|---|---|---|
| Number of Poles | 3-Way | Indoor/Outdoor | Indoor |
| NEMA Configuration Code | 14-30 | Voltage | 125/250 V |