ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

4WNLEDLD440SLFUN 4WNLED-LD4-40SL-F-Unv-L840-CD1-U

Cooper Lighting Solutions

Catalog Number	4WNLEDLD440SLFUN
Manufacturer	Cooper Lighting Solutions
Description	Utility Led Wraparound, 120 to 277 V Ac, 130 Ma, 36 W, Cold Rolled Steel, White, 4000 K, 80, 60000 H Average Life, Dimmable, White Enamel, 4000 LM Brightness (Lumens), 48 In Length, 2-1/2 In Width, 7-5/8 In Height, 9 LB
Weight per unit	11.0 (lbs/each)
Product Category	Led Surface Architectural & SP

Features

amperage rating	0.13 (at 277V)
Ballast Type	N/A
Lamp Type	LED
Number of Lamps	1
Socket Type	N/A

Material, Color, and Finish

Style	(blank)

Descriptions

Description	4WNLEDLD440SLFUNVL840CD1U
extra long description	CLS 4WNLED-LD4-40SL-F-UNV-L840-CD1-
Special Features	4 ft. and 2 ft. product configurations

Manufacturer Information

Brand	METALUX
GTIN	00080083756889
Manufacturers Part Number	4WNLED-LD4-40SL-F-UNV-L840-CD1
UPC	080083756889

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Wraparound

Packaging

Carton	1
Weight Per each	11

Uses, Certifications, and Standards

Mounting	Surface Mount
standard	UL/cUL Listed - Damp Location;RoHS Compliant