ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

50MR16TFL35C(EXN 50W 12V Hal MR16 GU5.3 Bi-Pin Base Reflector Cover

Sylvania-Ledvance

Catalog Number	50MR16TFL35C(EXN
Manufacturer	Sylvania-Ledvance
Description	Tungsten Halogen Tru Aim MR16 Titan Axial Filament Uv Filter Hard Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 50WATT 12VOLT Flood Beam
Weight per unit	0.0900 (lbs/each)
Product Category	Halogen Reflector Ar, BR, JDR,

Features

average life	4000
Base	GU5.3 Bipin
beam angle	36
dimmable	Yes
Lamp Type	MR16
lumens	900
Shape	MR16
start type	Instant
Voltage	12.00 V
Voltage Rating	12
Wattage	50

Material, Color, and Finish

color rendering index (cri)	100
color temperature	3000

Descriptions

Description	50W 12V HAL MR16 GU5.3 BI-PIN BASE REFLECTOR COVER
extra long description	SYL 50MR16TFL35CEXN-12V/58309 50MR1
Long Description	Tungsten Halogen Tru Aim MR16 TITAN Axial Filament UV Filter Hard Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 50Watt 12Volt Flood Beam
Product Type	50MR16TFL35CEXN 12V 20/CS 1/Sku

Manufacturer Information

Brand	Sylvania (Usc)
GTIN	00046135583094
Manufacturers Part Number	50MR16/T/FL35/C(EXN)-12V/58309
sub brand	TRU-AIM TITAN
UPC	046135583094

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	QUARTZ
Type	HALOGEN

Packaging

Carton	1
Package	20
Weight Per each	0.09

Uses, Certifications, and Standards

Application	Medium Screwbase or bi-pin
standard	EXN