



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 168020 1/2" Super Hawg (Tool Only)

*Milwaukee Electric Tool*

Catalog Number	168020
Manufacturer	Milwaukee Electric Tool
Description	The 1/2 In. Super Hawg Has Power and Speed For Drilling Holes Of All Sizes In Wood Frame Construction. The 13 Amp Motor Has Two Operating Speeds Of 1750 and 450 RPM With A Clutch In The Low Gear Range. Speed Shifting Is Easy. The Comfort Grip Roto-Lok Handle Features 3 Positions With 90 Degree Left-Right Rotation For Maximum Operator Comfort For All Applications.
Weight per unit	16.3 (lbs/each)
Product Category	Power Tools - Corded

### Features

Cord Length	8.0
idea granular category code	2288
Switch Type	Trigger
Voltage	120.0

### Material, Color, and Finish

Handle Material	Metal
Housing Material	Metal

### Dimensions and Weight

Height	5.25
Length	8.0
Width	25.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	1/2" SUPER HAWG (TOOL ONLY)
extra long description	MILW 1680-20 Super Hawg Drill
Features	1/2 in. Super Hawg Drill
Long Description	The 1/2 in. Super Hawg has power and speed for drilling holes of all sizes in wood frame construction. The 13 amp motor has two operating speeds of 1750 and 450 RPM with a clutch in the low gear range. Speed shifting is easy. The comfort grip Roto-Lok handle features 3 positions with 90 degree left-right rotation for maximum operator comfort for all applications.
Product Type	Super Hawg Drill
Short Description	Super Hawg Drill
Special Features	Features: Clutch In Low Speed; High Operating Speeds For Maximum Productivity; 90 DEG Left-Right; Roto-Lok Handle For Maximum Operating Comfort; Easy Turn Gear Shift Knob; Comfort Grip Switch Handle And Gear Case With Front T-Bar Handle; Chuck Type: Keyed; Cord Type: 8 FT Fixed; Tool Weight: 14.700 LB; Capacity In Wood: 6 IN Hole Saw; Spindle Lock: No; Metal Capacity: 1/2 IN Twist Bit; Spindle Size: 5/8-16 IN; Gear Train: Triple; Construction Type: Grounded; Length: 22 IN; Clutch:

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242001972
Manufacturers Part Number	1680-20
UPC	045242001972

## Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	Super Hawg Drill

## Packaging

Carton	1
Weight	14.7
Weight Per each	16.335

## Uses, Certifications, and Standards

Application	For Drilling Holes Of All Sizes In Wood Frame Construction
-------------	--