ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



5233J 1/4 X 3 MH SL/PH COMBO TOGGLE BOLT ZINC

PECO FASTENERS, INC.

Catalog Number	5233J
Manufacturer	PECO FASTENERS, INC.
Description	Toggle Bolt, Steel, Mushroom Head, 3 in Length, Zinc Plated, 1/4 in Diameter, 1.86 lb
Weight per unit	0.0744 (lbs/each)
Product Category	Screws, Nuts, Bolts, Washers

Features

Head Type	Mushroom

Material, Color, and Finish

Finish	Zinc

Dimensions and Weight

Diameter	1/4
Length	3
Size	1/4 IN X 3 IN

Descriptions

Description	1/4 X 3 MH SL/PH COMBO TOGGLE BOLT ZINC
Long Description	PECO FASTENERS 1/4 X 3 MUSHROOM HEAD SLOT/PHIL COMBO TOGGLE BOLT ZINC PLATED
Product Type	1/4X3 Mushroom HD Toggle Bolt ZC 96426
Extra Long Description	PECO 5233J 1/4X3 MUSHROOM HD TOGGLE

Manufacturer Information

Brand	Peco Fasteners
GTIN	00705591964266
UPC	893815

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Toggle Bolt

Availability

Minimum Qty	25

Packaging


Carton	25
Package	150
Weight Per Each	0.0744 (lbs/each)

Peco Fasteners & Electrical Products

Atlanta, Georgia

Phone 800-521-7326 Fax 770-745-1333

Toggle Bolt



Toggle bolts are spring wing type hollow wall anchors designed for light duty use in block, gypsum wallboard, and other hollow base materials. The part is a two component assembly consisting of a machine screw and a spring wing toggle.

Anchor Size	Thread Size	Drill Bit Size	M		S		R		D		W	Allowable Load Capacity			
			Mushroom Head Height		Mushroom Hd Diameter		Round Head Height		Round Hd Diameter		Wing Clearance	In 1/2" Wallboard		Hollow Block	
			Max	Min	Max	Min	Max	Min	Max	Min		Tensile (lbs.)	Shear (lbs.)	Tensile (lbs.)	Shear (lbs.)
1/8	6-32	3/8	0.086	0.074	0.321	0.303	0.103	0.091	0.260	0.240	1-1/16	40	35	40	35
3/16	10-24	1/2	0.128	0.113	0.448	0.425	0.137	0.123	0.359	0.334	1-3/8	45	50	70	70
1/4	1/4-20	5/8	0.150	0.133	0.573	0.546	0.175	0.160	0.472	0.443	1-1/2	60	60	70	120
5/16	5/16-18	7/8	0.183	0.162	0.698	0.666	0.216	0.198	0.590	0.557	2-1/8	65	70	85	135
3/8	3/8-16	7/8	0.215	0.191	0.823	0.787	0.256	0.237	0.708	0.670	2-1/8	65	75	195	140
1/2	1/2-13	1-1/4	0.280	0.250	1.073	1.028	0.355	0.332	0.813	0.766	3"	80	80	230	160

Toggle Wings Are Manufactured From AISI 1010 Carbon Steel
Screw Is Manufactured From ANSI B16.6.3 Carbon Steel
We Can Also Offer Select Sizes of Toggle Bolts in 18-8/300 Series Stainless Steel

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.

10/1/15